

NPN Silicon Epitaxial Planar Transistor

MMBT4401


FEATURES

- Epitaxial planar die construction
- Complementary PNP product available - MMBT4403
- MSL Class 1 compatible

HF

APPLICATIONS

- General purpose in desktop & handheld systems
- Ideal for medium-power signal amplification and switching



ORDERING INFORMATION

Part Number	Marking	Package
MMBT4401	2X	SOT-23

MAXIMUM RATING (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	60	V
Collector-Emitter Voltage	V_{CEO}	40	V
Emitter-Base Voltage	V_{EBO}	6	V
Collector Current (Continuous)	I_C	600	mA
Power Dissipation (Collector)	P_C	350	mW
Thermal Resistance (Junction-to-Ambient)	$R_{\theta JA}$	357	$^\circ\text{C/W}$
Thermal Resistance (Junction-to-Case)	$R_{\theta JC}$	250	$^\circ\text{C/W}$
Junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

NPN Silicon Epitaxial Planar Transistor

MMBT4401







ELECTRICAL CHARACTERISTICS (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 100\mu\text{A}$, $I_E = 0$	60			V
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 1\text{mA}$, $I_B = 0$	40			V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 100\mu\text{A}$, $I_C = 0$	6			V
Collector Cut-off Current	I_{CEX}	$V_{CE} = 35\text{V}$, $V_{BE} = -0.4\text{V}$			0.1	μA
Base Cut-off Current	I_{BL}	$V_{CE} = 35\text{V}$, $V_{BE} = 0.4\text{V}$			0.1	μA
DC Current Gain	h_{FE}	$V_{CE} = 1\text{V}$, $I_C = 0.1\text{mA}$	20			
		$V_{CE} = 1\text{V}$, $I_C = 1.0\text{mA}$	40			
		$V_{CE} = 1\text{V}$, $I_C = 10\text{mA}$	80			
		$V_{CE} = 1\text{V}$, $I_C = 150\text{mA}$	100		300	
		$V_{CE} = 2\text{V}$, $I_C = 500\text{mA}$	40			
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 150\text{mA}$, $I_B = 15\text{mA}$			0.4	V
		$I_C = 500\text{mA}$, $I_B = 50\text{mA}$			0.75	
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 150\text{mA}$, $I_B = 15\text{mA}$	0.75		0.95	V
		$I_C = 500\text{mA}$, $I_B = 50\text{mA}$			1.2	
Transition Frequency	f_T	$V_{CE} = 10\text{V}$, $I_C = 20\text{mA}$ $f = 100\text{MHz}$	250			MHz
Collector-Base Capacitance	C_{CB}	$V_{CB} = 5\text{V}$, $I_E = 0$, $f = 1\text{MHz}$			6.5	pF

NPN Silicon Epitaxial Planar Transistor

MMBT4401

TYPICAL CHARACTERISTICS (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




NPN Silicon Epitaxial Planar Transistor


MMBT4401

PACKAGE OUTLINE (Unit: mm)

Plastic surface mounted package



MOUNTING PAD LAYOUT (Unit: mm)



PACKAGE INFORMATION

Part Number	Package	Shipping Quantity
MMBT4401	SOT-23	3000pcs / Tape & Reel

NPN Silicon Epitaxial Planar Transistor

MMBT4401**IMPORTANT NOTICE**

Changzhou Galaxy Century Microelectronics (GME) reserves the right to make changes without further notice to any product information (copyrighted) herein to make corrections, modifications, improvements, or other changes. GME does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.