



Main

Device short name	G
Enclosure type	Standard environment enclosure indoor
Product Specific Application	Control electrically driven water pumps and air compressors
Range of Product	Square D Pumptrol

Complementary

Adjustable range on rising pressure	65...200 psi (448.16...1378.95 kPa)
Control type	Standard
Depth	3.68 in (93.47 mm)
Electrical connection	Screw clamp terminal
Fixing Mode	By brackets
Fluid connection type	0.125 inch NPSF internal
Height	5.72 in (145.29 mm)
Material	Zinc plated steel: flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	300 psig
Maximum Horse Power Rating	5 Hp 460/575 V AC, single phase 5 Hp 460/575 V AC, three phase 3 Hp 230 V AC, single phase 5 Hp 230 V AC, three phase 2 Hp 115 V AC, single phase 3 hp 115 V AC, three phase
Number of poles	2
Permissible voltage	575 V AC
Pressure actuator	Diaphragm
Pressure setting range	110...125 psi (758.42...861.84 kPa)
Net Weight	2.25 lb(US) (1.02 kg)
Range on decreasing pressure	40...170 psi (275.79...1172.11 kPa)
Scale type	Adjustable differential
Switch function	DPST
Value of setting	20...40 psi
Width	3.44 in (87.38 mm)

Environment

NEMA Degree of Protection	NEMA 1
Product Certifications	CSA file LR25490[RETURN]UL listed file E12158 CCN NKPZ

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	US1CP7G21536
Discount Schedule	CP7G
GTIN	785901461425
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.90 in (9.9 cm)
Package 1 Width	4.41 in (11.2 cm)
Package 1 Length	5.59 in (14.2 cm)
Package 1 Weight	29.76 oz (843.7 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	630
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1185.00 lb(US) (537.507 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------