

HPCR0819AK10RST

ACTIVE


CGS | CGS HPCR

TE Internal #: 2176471-4
10 Ω , Ceramic Composition, Power Resistor, 10 %, 19.1 x 7.9 mm, 2 Termination, Reel/Box, 2 W, +0 / -800 ppm/°C, Copper Termination, CGS HPCR

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Passive Component Dimensions: **19.1 x 7.9 mm**
Number of Terminations: **2**
Packaging Method: **Reel/Box**
Passive Component Tolerance: **10 %**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Ceramic Composition

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	10 %
Resistance Class	Up to 1k Ω
Resistance Value	10 Ω
Power Rating	2 W

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Number of Terminations	2
------------------------	---



Termination Area Base Material

Copper

Dimensions

Passive Component Dimensions	19.1 x 7.9 mm
------------------------------	---------------

Usage Conditions

Temperature Coefficient	+0 / -800 ppm/°C
-------------------------	------------------

Packaging Features

Packaging Method	Reel/Box
------------------	----------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

HPCR0819AK10RST

10 Ω , Ceramic Composition, Power Resistor, 10 %, 19.1 x 7.9 mm, 2 Termination, Reel /Box, 2 W, +0 / -800 ppm/°C, Copper Termination, CGS HPCR



TE Part # 1623720-3
CCR2 10R 10%

TE Part # 1-1623720-4
CCR2 10R 10% TAPED

TE Part # 2176471-5
HPCR 0819 A 10% 12R Std T&R

TE Part # 2176471-3
HPCR 0819 A 10% 8R2 Std T&R

TE Part # 3-2176471-4
HPCR 0819 A 10% 10R Std T&R HV

Also in the Series | CGS HPCR

Through-Hole Resistors(31)

Customers Also Bought

TE Part #206438-1
CPC RECPT ASSEMBLY SIZE 23-57

TE Part #6339160-1
MJ,RJ45,SMT,SHLD,PANEL GRD

TE Part #1734303-1
SHIELD FINGER 4025B-T

TE Part #3-1879216-4
CPF0402 180K 0.1% 25PPM 1K RL

TE Part #160650-2
250 FASTON,PCB TAB,TNBR

TE Part #1-2176471-6
HPCR 0819 A 10% 100R Std T&R

TE Part #2-2176471-0
HPCR 0819 A 10% 220R Std T&R



Documents

Product Drawings

[HPCR 0819 A 10% 10R Std T&R](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2176471-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176471-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176471-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Bulk Ceramic Resistors - Type HPCR Series - Tyco Electronics Passives](#)

English