




Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Number of Terminations: **2**
Package Size Code: **0612**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **1 %**

Features

Product Type Features

Resistor Type	Power Resistor
Package Size Code	0612
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	300 Ω
Power Rating	1.5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.55 mm[.022 in]
Product Length	1.55 mm[.061 in]
Product Width	3 mm[.118 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-2176556-1
3430 B2 1% 300R 100ppm 5k RL

Also in the Series | CGS 3430

Surface Mount Resistors(1168)

Customers Also Bought

TE Part #8-215083-0
MICRO-MATCH MOW.10P

TE Part #1-2176339-3
CRGCQ 0603 100R 1%

TE Part #2176339-1
CRGCQ 0603 10R 1%

TE Part #5-2176558-2
3430 B2 1% 120R 100ppm 1k RL

TE Part #5-2176558-3
3430 B2 1% 130R 100ppm 1k RL

TE Part #5-2176558-4
3430 B2 1% 150R 100ppm 1k RL

TE Part #5-2176558-6
3430 B2 1% 180R 100ppm 1k RL

TE Part #6-2176558-2
3430 B2 1% 330R 100ppm 1k RL

TE Part #6-2176558-7
3430 B2 1% 510R 100ppm 1k RL

TE Part #7-2176558-0
3430 B2 1% 680R 100ppm 1k RL



Documents

Product Drawings

3430 B2 1% 300R 100ppm 1k RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_6-2176558-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-2176558-1_BA.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_6-2176558-1_BA.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - CGS 3430 Series

English

Automotive Grade Wide Terminal Chip Resistor - Type 3430 Series

English