

Features

- Fast switching
- Low forward voltage drop
- Ultra-small surface mount package

HF

Applications


- For general purpose switching applications

Mechanical Data


- Case: SOT-523
- Molding compound: UL flammability classification rating 94V-0
- Terminals: Tin-plated; solderability per MIL-STD-202, Method 208




BAT54T




BAT54AT



BAT54CT



BAT54ST



SOT-523

Ordering Information

Part Number	Package	Shipping Quantity	Marking Code
BAT54T	SOT-523	3000 pcs / Tape & Reel	L1
BAT54AT	SOT-523	3000 pcs / Tape & Reel	L2
BAT54CT	SOT-523	3000 pcs / Tape & Reel	L3
BAT54ST	SOT-523	3000 pcs / Tape & Reel	L4

Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	V _{RRM}	30	V
Working Peak Reverse Voltage	V _{RWM}	30	V
DC Reverse Voltage	V _R	30	V
Continuous Forward Current	I _F	200	mA
Repetitive Peak Forward Current	I _{FRM}	300	mA
Peak Forward Surge Current (t _p = 1s)	I _{FSM}	600	mA

Thermal Characteristics

Parameter	Symbol	Value	Unit
Power Dissipation	P_D	150	mW
Thermal Resistance Junction-to-Air ^{*1}	$R_{\theta JA}$	160	°C/W
Thermal Resistance Junction-to-Case ^{*1}	$R_{\theta JC}$	90	°C/W
Thermal Resistance Junction-to-Lead ^{*1}	$R_{\theta JL}$	80	°C/W
Operating Junction Temperature Range	T_J	-55 ~ +125	°C
Storage Temperature Range	T_{STG}	-55 ~ +150	°C

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Reverse Breakdown Voltage	$V_{(BR)R}$	$I_R = 100\mu\text{A}$	30	-	-	V
Forward Voltage ^{*2}	V_F	$I_F = 0.1\text{mA}$	-	-	0.24	V
		$I_F = 1\text{mA}$	-	-	0.32	V
		$I_F = 10\text{mA}$	-	-	0.40	V
		$I_F = 30\text{mA}$	-	-	0.50	V
		$I_F = 100\text{mA}$	-	-	0.60	V
Maximum Peak Reverse Current ^{*3}	I_R	$V_R = 25\text{V}$	-	-	2	μA
Capacitance Between Terminals	C_J	$V_R = 1\text{V}, f = 1\text{MHz}$	-	-	10	pF
Reverse Recovery Time	t_{rr}	$I_F = I_R = 10\text{mA}$ $I_{rr} = 0.1X I_R, R_L = 100\Omega$	-	-	5	ns

Notes:

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper
2. Pulse test, $t_p \leq 300\mu\text{s}$
3. Pulse test, $t_p \leq 5\text{ms}$

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Typical Reverse Characteristic




Fig 2 Typical Forward Characteristics




Fig 3 Capacitance Characteristics





Fig 4 Power Derating Curve


Package Outline Dimensions (Unit: mm)



SOT-523		
Dimension	Min.	Max.
A	1.50	1.70
B	0.75	0.85
C	0.60	0.80
D	0.15	0.30
E	0.30	0.40
F	0.25	0.40
G	0.90	1.10
H	0.02	0.10
J	0.08	0.18
K	1.45	1.75

Mounting Pad Layout (Unit: mm)

SOT-523



Important Notice

Changzhou Galaxy Century Microelectronics (GME) reserves the right to make changes without further notice to any product information (copyrighted) herein to make corrections, modifications, improvements, or other changes. GME does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.