

■ PRODUCT CHARACTERISTICS




VDSS	650V
R _{DS(on)} Typ(@V _{GS} = 10 V)	1.2Ω
Qg@type	28nC
ID	8A

■ APPLICATIONS

- High efficiency switch mode power supplies
- Electronic lamp ballasts based on half bridge
- LED power supplies

■ FEATURES

- * Ultra low gate charge
- * Low reverse transfer Capacitance
- * Fast switching capability
- * Avalanche energy tested
- * Improved dv/dt capability, high ruggedness



■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT8N65MD	TO-252	2500 pieces /Reel
N/A	MOT8N65MC	TO-251	70 pieces/Tube

■ ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Drain-Source Voltage	V _{DSS}	650	V
Gate-Source Voltage	V _{GSS}	±30	V
Avalanche Current (Note 2)	I _{AR}	8	A
Drain Current	Continuous I _D	8	A
	Pulsed (Note 2) I _{DM}	32	A
Avalanche Energy	Single Pulsed (Note 3) E _{AS}	230	mJ
	Repetitive (Note 2) E _{AR}	14.7	mJ
Peak Diode Recovery dv/dt (Note 4)	dv/dt	4.5	V/ns
Power Dissipation	P _D	55	W
Junction Temperature	T _J	+150	°C
Operating Temperature	T _{OPR}	-55 ~ +150	°C
Storage Temperature	T _{STG}	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by T_J

3. L = 7.1mH, I_{AS} = 8A, V_{DD} = 50V, R_G = 25 Ω, Starting T_J = 25°C

4. I_{SD} ≤ 8A, di/dt ≤ 200A/μs, V_{DD} ≤ BV_{DSS}, Starting T_J = 25°C



■ ELECTRICAL CHARACTERISTICS (T_C=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Off characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0 V, I _D = 250 μA	650	-	-	V
Drain-Source Leakage Current	I _{DSS}	V _{DS} = 650 V, V _{GS} = 0 V	-	-	10	μA
Gate-Source Leakage Current	Forward	V _{GS} = 30 V, V _{DS} = 0 V	-	-	100	nA
	Reverse	V _{GS} = -30 V, V _{DS} = 0 V	-	-	-100	nA
Breakdown Voltage Temperature Coefficient	△BV _{DSS} /△T _J	I _D = 250 μA, Referenced to 25°C	-	0.7	-	V/°C
On characteristics						
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} = V _{GS} , I _D = 250 μA	2.0	-	4.0	V
Static Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} = 10 V, I _D = 4 A	-	1.2	1.3	Ω
Dynamic characteristics						
Input Capacitance	C _{ISS}	V _{DS} = 25 V, V _{GS} = 0 V, f = 1 MHz	-	965	-	pF
Output Capacitance	C _{OSS}		-	105	-	pF
Reverse Transfer Capacitance	C _{RSS}		-	12	-	pF
Switching characteristics						
Turn-On Delay Time	t _{D(ON)}	V _{DD} = 325 V, I _D = 8 A, R _G = 25 Ω (Note 1, 2)	-	16.5	-	ns
Turn-On Rise Time	t _R		-	60.5	-	ns
Turn-Off Delay Time	t _{D(OFF)}		-	81	-	ns
Turn-Off Fall Time	t _F		-	64.5	-	ns
Total Gate Charge	Q _G	V _{DS} = 520 V, I _D = 8 A, V _{GS} = 10 V (Note 1, 2)	-	28	-	nC
Gate-Source Charge	Q _{GS}		-	4.5	-	nC
Gate-Drain Charge	Q _{GD}		-	12	-	nC
Drain-source diode characteristics and maximum ratings						
Drain-Source Diode Forward Voltage	V _{SD}	V _{GS} = 0 V, I _S = 8 A	-	-	1.4	V
Maximum Continuous Drain-Source Diode Forward Current	I _S		-	-	8	A
Maximum Pulsed Drain-Source Diode Forward Current	I _{SM}		-	-	32	A
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, I _S = 8 A, dI _F /dt = 100 A/μs (Note 2)	-	365	-	ns
Reverse Recovery Charge	Q _{RR}		-	3.4	-	μC







Notes: 1. Pulse Test: Pulse width ≤300μs, Duty cycle≤2%

2. Essentially independent of operating temperature







■ TYTEST CIRCUITS AND WAVEFORMS


Peak Diode Recovery dv/dt Test Circuit

Peak Diode Recovery dv/dt Waveforms






■ TEST CIRCUITS AND WAVEFORMS(Cont.)


Switching Test Circuit
Switching Waveforms

Gate Charge Test Circuit
Gate Charge Waveform

Unclamped Inductive Switching Test Circuit

Unclamped Inductive Switching Waveforms


■ TYPICAL CHARACTERISTICS



■ TYPICAL CHARACTERISTICS(Cont.)



■ TO-251 PACKAGE OUTLINE DIMENSIONS



■ TO-252 PACKAGE OUTLINE DIMENSIONS

