



Poles	PART NO	DIM A	DIM B
2	PH-2A	2.0	6.1
3	PH-3A	4.0	8.1
4	PH-4A	6.0	10.1
5	PH-5A	8.0	12.1
6	PH-6A	10.0	14.1
7	PH-7A	12.0	16.1
8	PH-8A	14.0	18.1
9	PH-9A	16.0	20.1
10	PH-10A	18.0	22.1
11	PH-11A	20.0	24.1
12	PH-12A	22.0	26.1
13	PH-13A	24.0	28.1
14	PH-14A	26.0	30.1
15	PH-15A	28.0	32.1
16	PH-16A	30.0	34.1



- 1.Pin pitch: 2.0
- 2.Rated voltage: 250V DC/AC
- 3.Contact resistance:  $\leq 20\text{m}\Omega$
- 4.Insulation resistance:  $\geq 1000\text{M}\Omega$
- 5.Operating temperature:  $-25^{\circ}\text{C}\sim +85^{\circ}\text{C}$

②	PIN	—	—	Brass	Sn Plated	—
①	Base	—	1	PA66	Natural	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE																			
DRAWN	LIUCAN	2021.10.22					TITLE:	Bar Connector Series													
CHECKED				PART NO.	PH-nA																
APPROVALS				TOLERANCES ARE	<table border="1"> <tr> <td>30~以上</td> <td><math>\pm 0.30</math></td> <td rowspan="2">ANGLE</td> <td rowspan="2">UNIT: mm</td> <td rowspan="2">SCALE: 1:1</td> <td rowspan="2">PROJ: </td> </tr> <tr> <td>10~30</td> <td><math>\pm 0.20</math></td> </tr> <tr> <td>5~10</td> <td><math>\pm 0.15</math></td> <td rowspan="2"><math>\pm 2'</math></td> <td rowspan="2">DRAWING NO.</td> <td rowspan="2">SHEET</td> <td rowspan="2">1 OF 1</td> </tr> <tr> <td>~ 5</td> <td><math>\pm 0.10</math></td> </tr> </table>	30~以上	$\pm 0.30$	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:	10~30	$\pm 0.20$	5~10	$\pm 0.15$	$\pm 2'$	DRAWING NO.	SHEET	1 OF 1	~ 5	$\pm 0.10$
30~以上	$\pm 0.30$	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:																
10~30	$\pm 0.20$																				
5~10	$\pm 0.15$	$\pm 2'$	DRAWING NO.	SHEET	1 OF 1																
~ 5	$\pm 0.10$																				

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.