


D8634CF

650uA 9MHz Rail-to-Rail I/O CMOS Operational Amplifier

Description

The D8634CF(quad) is low noise, low voltage, and low power operational amplifier, that can be designed into a wide range of applications. The D8634CF have a high gain-bandwidth product of 9MHz, a slew rate of 8V/ μ s, and a quiescent current of 650 μ A/ amplifier at 5V.



The D8634CF is designed to provide optimal performance in low voltage and low noise systems. It provide s rail-to-rail output swing into heavy loads. The input common-mode voltage range includes ground, and the maximum input offset voltage are 3.5m V for D8634CF.

It is specified over the extended industrial temperature range (-40°C to + 125 °C). The operating range is from 2.5V to 5.5V.

D8634CF is available in SOP14 package.

Features

- Low Cost
- Rail-to-Rail Input and Output: 0.8m V Typical VOS
- High Gain- Bandwidth Product: 9 MHz
- High Slew Rate: 8.0V/ μ s
- Settling Time to 0.1% with 2V Step: 1.2 μ s
- Overload Recovery Time: 0.4 μ s
- Low Noise : 8nV/ $\sqrt{\text{HZ}}$
- Operates on 2.5V to 5.5V Supplies
- Input Voltage Range = -0.1V to +5.6V with VS =5.5V
- Low Power: 650 μ A/Amplifier Typical Supply Current

Package Information

Part NO.	Package Description	Package Marking	Package Option
D8634CF	SOP14	CHMC SXXXX D8634CF	50/Tube 4000/Reel

CHMC:Trademark


D8634CF:Part NO.

SXXXX:Lot NO.

Applications

- Sensors
- Audio
- Active Filters
- A/D Converters
- Communications
- Test Equipment
- Cellular and Cordless Phones
- Laptops and PDAs
- Photodiode Amplification
- Battery-Powered Instrumentation

Pin Connection



D8563CF(SOP14)

Absolute Maximum Ratings

Characteristic		Value	Unit
Supply Voltage		7.5	V
Common-m Mode Input Voltage		$(-V_s)-0.5V \sim (+V_s)+0.5V$	V
Operating Temperature		$-55 \sim +150$	°C
Storage Temperature		$-65 \sim +150$	°C
Junction Temperature		160	°C
Lead Temperature Range (soldering 10sec)		260	°C
ESD Susceptibility	HBM	1500	V
	MM	400	V

Electrical Characteristics (unless otherwise specified: $V_{CM} = V_S/2, R_L = 600\ \Omega, T_A = 25\ ^\circ\text{C}, V_S = +5\text{V}$)

PARAMETER	CONDITION	TYP	MIN/MAX OVER TEMPERATURE					MIN/MAX
		+25℃	+25℃	0℃ to 70℃	-40℃ to 85℃	-40℃ to 125℃	UNITS	
INPUT CHARACTERISTICS								
Input Offset Voltage (V _{OS})	V _S = 5.5V V _S = 5.5V, V _{CM} = - 0.1V to 4 V V _S = 5.5V, V _{CM} = - 0.1V to 5.6 V R _L = 600Ω, V _o = 0.15V to 4.85V R _L =10KΩ, V _o = 0.05V to 4.95V	1	4	4.5	4.75	5	mV	MAX
Input Bias Current (I _B)		1					pA	TYP
Input Offset Current (I _{OS})		1					pA	TYP
Common-Mode Voltage Range (V _{CM})		-0.1 to +5.6					V	TYP
Common-Mode Rejection Ratio(CMRR)		91	75	74	73	72.5	dB	MIN
		86	64	64	63	62	dB	MIN
Open-Loop Voltage Gain(A _{OL})		90	84	81	80	72	dB	MIN
	100	95	90	88	77	dB	MIN	
Input Offset Voltage Drift (ΔV _{OS} /ΔT)		2.1					μV/℃	TYP
OUTPUT CHARACTERISTICS								
Output Voltage Swing from Rail	R _L = 600Ω	0.1					V	TYP
	R _L = 10KΩ	0.015					V	TYP
Output Current (I _{OUT})		57	53	52	50	45	mA	MIN
Closed-Loop Output Impedance	F = 1MHz, G = +1	5.7					Ω	TYP
POWER-DOWN DISABLE								
Turn-On Time		2.2					μs	TYP
Turn-Off Time		0.8					μs	TYP
<u>DISABLE</u> Voltage-Off			0.8				V	MAX
<u>DISABLE</u> Voltage-On			2				V	MIN
POWER SUPPLY								
Operating Voltage Range			2.5	2.5	2.5	2.5	V	MIN
			5.5	5.5	5.5	5.5	V	MAX
Power Supply Rejection Ratio (PSRR)	V _s = +2.5 V to + 5.5 V V _{CM} = (-V _S) + 0.5V	100	80	79	78	77	dB	MIN
Quiescent Current/ Amplifier (I _Q)	I _{OUT} = 0	0.65	0.8	0.9	0.92	1.02	mA	MAX
DYNAMIC PERFORMANCE								
Gain-Bandwidth Product (GBP)	R _L = 600Ω	9.0					MHz	TYP
Phase Margin(φ _o)		63.5					degrees	TYP
Full Power Bandwidth(BW _P)	<1% distortion	400					KHz	TYP
Slew Rate (SR)	G = +1, 2 V Output Step	8.0					V/μs	TYP
Settling Time to 0.1%(t _s)	G = +1, 2 V Output Step	0.36					μs	TYP
Overload Recovery Time	V _{IN} ·Gain = Vs	0.4					μs	TYP
NOISE PERFORMANCE								
Voltage Noise Density (e _n)	f = 1kHz	8					nV/√Hz	TYP
	f = 10kHz	6.4					nV/√Hz	TYP
Current Noise Density(i _n)	f = 1kHz	10					fA/√Hz	TYP

Application Summary

Driving Capacitive Loads

The D8634CF can directly drive 1000pF in unity-gain without oscillation. The unity-gain follower (buffer) is the most sensitive configuration to capacitive loading. Direct capacitive loading reduces the phase margin of amplifiers and this results in ringing or even oscillation.




Figure 1. Indirectly Driving Heavy Capacitive Load

Applications that require greater capacitive drive capability should use an isolation resistor between the output and the capacitive load like the circuit in Figure 1.

The isolation resistor R_{ISO} and the load capacitor C_L form a zero to increase stability. The bigger the R_{ISO} resistor value, the more stable V_{OUT} will be. Note that this method results in a loss of gain accuracy because R_{ISO} forms a voltage divider with the R_{LOAD} .

An improvement circuit is shown in Figure 2.

It provides DC accuracy as well as AC stability. R_F provides the DC accuracy by connecting the inverting signal with the output. C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving phase margin in the overall feedback loop.




Figure 2. Indirectly Driving Heavy Capacitive Load with DC Accuracy

For no-buffer configuration, there are two others ways to increase the phase margin: (a) by increasing the amplifier's gain or (b) by placing a capacitor in parallel with the feedback resistor to counteract the parasitic capacitance associated with inverting node.

Power-Supply Bypassing and Layout

The D8634CF family operates from either a single +2.5 V to +5.5V supply or dual $\pm 1.25V$ to $\pm 2.75V$ supplies. For single-supply operation, bypass the power supply V_{DD} with a $0.1\mu F$ ceramic capacitor which should be placed close to the V_{DD} pin. For dual-supply operation, both the V_{DD} and the V_{SS} supplies should be bypassed to ground with separate $0.1\mu F$ ceramic capacitors. $2.2\mu F$ tantalum capacitor can be added for better performance.

Good PC board layout techniques optimize performance by decreasing the amount of stray capacitance at the op amp's inputs and

output. To decrease stray capacitance, minimize trace lengths and widths by placing external components as close to the device as possible. Use surface-mount components whenever possible.

For the operational amplifier, soldering the part to the board directly is strongly recommended. Try to keep the high frequency big current loop area small to minimize the EMI (electromagnetic interfacing).




Figure 3. Amplifier with Bypass Capacitors Grounding

Grounding

A ground plane layer is important for D8634CF circuit design. The length of the current path speed currents in an inductive ground return will create an unwanted voltage noise. Broad ground plane areas will reduce the parasitic inductance.

Input-to-Output Coupling

To minimize capacitive coupling, the input and output signal traces should not be parallel. This helps reduce unwanted positive feedback.

Differential Amplifier

The circuit shown in Figure 4 performs the difference function. If the resistors ratios are equal ($R_4/R_3 = R_2/R_1$), then $V_{OUT} = (V_p - V_n) \times R_2/R_1 + V_{REF}$.




Figure 4. Differential Amplifier

Instrumentation Amplifier

The circuit in Figure 5 performs the same function as that in Figure 4 but with the high input impedance.




Figure 5. Instrumentation Amplifier Low Pass Active Filter

Low Pass Active Filter

The low pass filter shown in Figure 6 has a DC gain of $(-R_2/R_1)$ and the -3dB corner frequency is $1/2\pi R_2 C$. Make sure the filter is within the bandwidth of the amplifier. The Large values of feedback resistors can couple with parasitic capacitance and cause undesired effects such as ringing or oscillation in high- speed amplifiers. Keep resistors value as low as possible and consistent with output loading consideration.




























Figure 6. Low Pass Active Filter

Typical Curve (At $T_A = 25^\circ\text{C}$, $V_{CM} = V_S/2$, $R_L = 600\ \Omega$, unless otherwise noted)










Outline Dimensions

SOP14

Unit: mm



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	8.360	8.760	0.329	0.345
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°

Statement

- Silicore Technology reserves the right to make changes without further notice to any products or specifications herein. Before customers place an order, customers need to confirm whether datasheet obtained is the latest version, and to verify the integrity of the relevant information.
- Failure or malfunction of any semiconductor products may occur under particular conditions, customers shall have obligation to comply with safety standards when customers use Silicore Technology products to do their system design and machine manufacturing, and take corresponding safety measures in order to avoid potential risk of failure that may cause personal injury or property damage.
- The product upgrades without end, Silicore Technology will wholeheartedly provide customers integrated circuits that have better performance and better quality.