



Features

- High DC current gain
- Complimentary to SS8050

HF

Mechanical Data

- Case: SOT-23
- Molding compound: UL flammability classification rating 94V-0
- Terminals: Tin-plated; solderability per MIL-STD-202, Method 208



SOT-23

Ordering Information

Part Number	Package	Shipping Quantity	Marking Code
SS8550	SOT-23	3000 pcs / Tape & Reel	Y2

Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Collector-Base Breakdown Voltage	V _{CBO}	-40	V
Collector-Emitter Breakdown Voltage	V _{CEO}	-25	V
Emitter-Base Breakdown Voltage	V _{EBO}	-6	V
Collector Current (Continuous)	I _C	-1.5	A
Collector Current (Peak)	I _{CM}	-2	A
Base Current (Continuous)	I _B	-0.15	A
Power Dissipation	P _D	0.3	W
Junction Temperature Range	T _J	-55 ~ +150	°C
Storage Temperature Range	T _{STG}	-55 ~ +150	°C

Thermal Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
Thermal Resistance Junction-to-Air *1	R _{θJA}	-	-	350	°C/W
Thermal Resistance Junction-to-Case *1	R _{θJC}	-	-	150	°C/W
Thermal Resistance Junction-to-Lead *1	R _{θJL}	-	-	125	°C/W

Note 1: The data tested by surface mounted on a minimum recommended FR-4 board

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = -100\mu\text{A}, I_E = 0$	-40	-	-	V
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = -0.1\text{mA}, I_B = 0$	-25	-	-	V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = -100\mu\text{A}, I_C = 0$	-6	-	-	V
Collector Cut-off Current	I_{CBO}	$V_{CB} = -35\text{V}, I_E = 0$	-	-	-0.1	μA
Collector Cut-off Current	I_{CEO}	$V_{CE} = -20\text{V}, I_B = 0$	-	-	-0.1	μA
Emitter Cut-off Current	I_{EBO}	$V_{EB} = -6\text{V}, I_C = 0$	-	-	-0.1	μA
DC Current Gain	h_{FE}	$V_{CE} = -1\text{V}, I_C = -0.1\text{A}$	120	-	400	-
		$V_{CE} = -1\text{V}, I_C = -0.8\text{A}$	40	-	-	-
Collector-emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = -0.8\text{A}, I_B = -0.08\text{A}$	-	-0.28	-0.5	V
Base-emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = -0.8\text{A}, I_B = -0.08\text{A}$	-	-0.98	-1.2	V
Base-emitter on Voltage	$V_{BE(on)}$	$V_{CE} = -1\text{V}, I_C = -10\text{mA}$	-	-0.66	-1	V
Transition Frequency	f_T	$I_C = -50\text{mA}, V_{CE} = -10\text{V}$	100	-	-	MHz
Collector Output Capacitance	C_{OB}	$V_{CB} = -10\text{V}, I_E = 0, f = 1\text{MHz}$	-	15	-	pF

CLASSIFICATION OF h_{FE}

Rank	L	H	J
Range	120-200	200-350	300-400

Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 h_{FE} vs. I_C (H)




Fig 2 $V_{CE(sat)}$ vs. I_C




Fig 3 $V_{BE(sat)}$ vs. I_C




Fig 4 $V_{BE(on)}$ vs. I_C




Fig 5 I_C vs. V_{CE}





Fig 6 Steady State Power Derating


Package Outline Dimensions (Unit: mm)



SOT-23		
Dimension	Min.	Max.
A	2.70	3.10
B	1.10	1.50
C	0.90	1.10
D	0.30	0.50
E	0.35	0.48
G	1.80	2.00
H	0.02	0.10
J	0.05	0.15
K	2.20	2.60

Package Outline Dimensions (Unit: mm)

SOT-23



IMPORTANT NOTICE

Changzhou Galaxy Century Microelectronics (GME) reserves the right to make changes without further notice to any product information (copyrighted) herein to make corrections, modifications, improvements, or other changes. GME does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.