



芯科半导体

ELECTRONIC  
PRODUCT  
浙江芯科半导体有限公司


## Features

- ✓ Zero forward recovery voltage
- ✓ Zero reverse recovery current
- ✓ Excellent surge current capability
- ✓ Temperature independent switching
- ✓ Positive temperature coefficient on  $V_F$
- ✓ High frequency operation

Part NO.	KXJW120C20T2
$V_{RRM}$	= 1200 V
$I_F(T_C=150^\circ C)$	= 25 A
$Q_C$	= 88 nC

## Applications

- ✓ Motor drives
- ✓ Uninterruptible power supplies
- ✓ Photovoltaic inverter
- ✓ Switch mode power supplies (SMPS)



## Key performance parameters

Symbol	Parameter	Test conditions	Value	Unit	Note
$V_{RRM}$	Repetitive peak reverse voltage	$T_C = 25^\circ C$	1200	V	
$V_{RSM}$	Surge peak reverse voltage (DC)	$T_C = 25^\circ C$	1200	V	
$I_F$	Continuous forward current	$T_C = 25^\circ C, D=1$ $T_C = 135^\circ C, D=1$ $T_C = 155^\circ C, D=1$	61 31 22	A	Fig.2
$I_{FRM}$	Repetitive forward surge current	$t_p = 10 \text{ ms, Half sine wave}$ $T_C = 25^\circ C$ $T_C = 100^\circ C$	96 62	A	
$I_{FSM}$	Non-repetitive forward surge current	$t_p = 10 \text{ ms, Half sine wave}$ $T_C = 25^\circ C$ $T_C = 150^\circ C$	100 88	A	
$\int i^2 dt$	$i^2 t$ value	$t_p = 10 \text{ ms, }$ $T_C = 25^\circ C$ $T_C = 150^\circ C$	46 19	$A^2 s$	
$P_{tot}$	Total power dissipation	$T_C = 25^\circ C$	299.40	W	Fig.1
$T_j$	Operating junction temperature		-55 ~ 175	$^\circ C$	
$T_{stg}$	Storage temperature		-55 ~ 175	$^\circ C$	

## Static electrical characteristics

Symbol	Parameter	Test conditions	Value			Unit	Note
			Min.	Typ.	Max.		
$V_{DC}$	DC blocking voltage	$I_R = 50 \mu A, T_j = 25^\circ C$	1250	-	-	V	
$V_F$	Diode forward voltage	$I_F = 20 A, T_j = 25^\circ C$ $I_F = 20 A, T_j = 150^\circ C$	- -	1.5 2.38	1.6 -	V	Fig.3
$I_R$	Reverse current	$V_R = 1200 V, T_j = 25^\circ C$ $V_R = 1200 V, T_j = 150^\circ C$	- -	1 128	100 200	$\mu A$	Fig.4
C	Total capacitance	$V_R = 0.1 V, T_j = 25^\circ C, f = 1 MHz$ $V_R = 400 V, T_j = 25^\circ C, f = 1 MHz$ $V_R = 800 V, T_j = 25^\circ C, f = 1 MHz$	- - -	1091 84 65	- - -	pF	Fig.8
$Q_C$	Total capacitive charge	$V_R = 800 V, T_j = 25^\circ C$	-	88	-	nC	Fig.5
$E_C$	Capacitance stored energy	$V_R = 800 V, T_j = 25^\circ C$	-	45	-	$\mu J$	Fig.7
$T_{RR}$	Reverse recovery time	$V_R = 800 V, I_F = 23 A, di/dt = 1000 A/\mu s$	-	12.53	-	ns	
$Q_{RR}$	Reverse recovery Charge		-	58	-	nC	

## Thermal characteristics

Symbol	Parameter	Value		Unit	Note
		Typ	Max		
$R_{\theta JC}$	Thermal resistance from junction to case	0.501	-	°C/W	Fig.6
$R_{\theta JA}$	Thermal resistance from junction to ambient	33.66	-	°C/W	



芯科半导体

SiC Schottky Diode #KXJW120C20T2




Figure.1 Power dissipation




Figure.2 Diode forward current




Figure.3 Typical forward characteristics




Figure.4 Reverse current vs. reverse voltage



芯科半导体

SiC Schottky Diode #KXJW120C20T2




Figure.5 Capacitance charge vs. reverse voltage




Figure.6 Transient thermal impedance




Figure.7 Capacitance stored energy




Figure.8 Capacitance vs. reverse voltage



芯科半导体

SiC Schottky Diode #KXJW120C20T2

## Package outlines

