



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**  
Number of Terminations: **2**  
Package Size Code: **2512**  
Packaging Method: **Taped & Reeled**  
Passive Component Tolerance: **1 %**

Features

Product Type Features

|                   |                |
|-------------------|----------------|
| Resistor Type     | Power Resistor |
| Package Size Code | 2512           |
| Element Type      | Thin Film      |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                   |
|-----------------------------|-------------------|
| Operating Voltage           | 100 V             |
| Passive Component Tolerance | 1 %               |
| Resistance Class            | Up to 1k $\Omega$ |
| Resistance Value            | 432 $\Omega$      |
| Power Rating                | 6 W               |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Number of Terminations                  | 2      |
| Surface Mount Resistor Termination Type | Solder |



Dimensions

|                |                 |
|----------------|-----------------|
| Product Height | .43 mm[.017 in] |
| Product Length | 6.3 mm[.248 in] |
| Product Width  | 3.1 mm[.122 in] |

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±50 ppm/°C   |

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>


|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.                                                                          |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 9-2176532-0

3504G 3A 432R 1% 4K RL

Also in the Series | CGS 3504



Surface Mount Resistors(534)

Customers Also Bought




TE Part #2318770-3

TWO-PIECE POKE-IN, 5MM HEADER, 3 POS




TE Part #2199248-5

SHIELD FINGER, LOOSE PIECE, TYPE A, 1.3H




TE Part #2-2176530-7

3504G 3A 1K02 1% 1K RL




TE Part #4-2176530-3

3504G 3A 1K5 1% 1K RL




TE Part #5-2176530-5

3504G 3A 2K0 1% 1K RL




TE Part #6-2176530-4

3504G 3A 2K49 1% 1K RL




TE Part #7-2176530-1

3504G 3A 2K94 1% 1K RL



TE Part #9-2176529-4

3504G 3A 475R 1% 1K RL



TE Part #9-2176529-8

3504G 3A 523R 1% 1K RL



Documents

Product Drawings

3504G 3A 432R 1% 1K RL

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_9-2176529-0\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_9-2176529-0\_A.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_9-2176529-0\_A.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1773270-5

English