

FDMF5076

35A Smart Power Stage (SPS) Modules with Integrated Current and Temperature Monitors

Product Overview

For complete documentation, see the data sheet.

Features

- Up to 35A Instantaneous Peak Current Handling Capability
- High-Performance, Universal Footprint, Copper-Clip 4 mm x 5 mm PQFN Package
- . ON Semiconductor's PowerTrench® MOSFETs for Clean Voltage Waveforms and Reduced Ringing
- 30V / 25V Breakdown Voltage MOSFETs for Higher Long Term Reliability
- Optimized FET Pair for Highest Efficiency at 10% ~ 15% Duty Cycle
- Optimized for Switching Frequencies up to 1 MHz
- Integrated Current Monitor Compliant with Intel's VR13 Accuracy Requirements
- Integrated Temperature Monitor (TMON)
- · Catastrophic Fault Detection
- Thermal Flag (OTP) for Over-Temperature Condition
 For more features, see the data sheet

Applications

- CPU and Memory Voltage Regulators in VR13 Purley Systems
- Communications Infrastructure Systems

FDMF5076

Part Electrical Specifications													
Product	Status	Compilance	V _{CIN} (V) Typ	V _{IN} (V) Typ	PWM Level	I _o (A) Max	f _{max} (MHz) Max	Packa ge Type	Case Outline	MSL Type	MSL Temp (°C)	Contai ner Type	Contai ner Qty.
FDMF5076	Active	H _{Pb}	5	12	3.3V, 5V	35	1	PQFN- 24	483BV .PDF	1	260	REEL	3000