## Test Procedure for the NCP1060FLBKGEVB



The following steps detail the test procedure for all these boards:

Necessary Equipment:

1 Current limited 90 ÷ 265Vrms AC source (current limited to avoid board destruction in case of a defective part) (e.g. AGILENT 6811)

1 AC Volt-Meter able to measure up to 300V AC. (e.g. KEITHLEY 2000)

1 AC Amp-Meter able to measure up to 3A AC. (e.g. KEITHLEY 2000)

4 DC Volt-Meter able to measure up to 50V DC. (e.g. KEITHLEY 2000)

4 DC Amp-Meter able to measure up to 5A DC. (e.g. KEITHLEY 2000)

4 DC Electronic Load 0 - 60A (e.g. AGILENT 6060B)



Figure 1: Test Setup for Flyback Convertor

**Test Procedure (Flyback convertor):** 

- 1. Connect the test setup as shown in Figure 1.
- 2. Apply an input voltage, Uin =90 265Vac
- 3. Apply Iout(load) = 0A
- 4. Check that Uout is 12V
- 5. Increate Iout(load) load to: 0,4 A
- 6. Check that Uout is 12V
- 7. Increate Iout(load) load to: 0,7 A
- 8. Check that Uout is 0V (output is skipping in 400 ms period)
- 9. Power down the load
- 10. Power down Uin
- 11. End of test