



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #826632-7
7P AMPMODU II PIN HDR.



TE Part #828548-3
3P AMP QUICK STLEI



TE Part #828548-2
2P AMP QUICK STLEI



TE Part #2176349-9
CRGCQ 2512 47R 1%



<p>TE Part #1-2176349-0 CRGCQ 2512 56R 1%</p>	<p>TE Part #828548-4 4P AMP QUICK STLEI</p>	<p>TE Part #828549-4 4P AMP-QUICK STLEI</p>	<p>TE Part #828549-3 3P AMP-QUICK STLEI</p>
<p>TE Part #928205-4 4P TELFIX BU-GEH</p>	<p>TE Part #928205-3 3P TELFIX BU-GEH</p>		

Documents

Product Drawings

2P AMP-QUICK STLEI

English

CAD Files

Customer View Model

ENG_CVM_CVM_828549-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_828549-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_828549-2_E.3d_stp.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.