


# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224  
<https://www.phoenixcontact.com/us/products/1940224>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 1.5 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: FK-MCP 1,5/..-STF, pitch: 3.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

## Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Intuitive operation due to color-coded actuating push button
- Screwable flange for superior mechanical stability
- Quick and convenient testing using integrated test option

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1940224             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales key                            | AA02                |
| Product key                          | AABFMB              |
| Catalog page                         | Page 199 (C-1-2013) |
| GTIN                                 | 4017918877453       |
| Weight per piece (including packing) | 14.892 g            |
| Weight per piece (excluding packing) | 13.389 g            |
| Customs tariff number                | 85366990            |
| Country of origin                    | DE                  |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Type                  | Standard              |
| Product line          | COMBICON Connectors S |
| Product type          | PCB connector         |
| Product family        | FK-MCP 1,5/...-STF    |
| Number of positions   | 15                    |
| Pitch                 | 3.5 mm                |
| Number of connections | 15                    |
| Number of rows        | 1                     |
| Mounting flange       | Screw flange          |
| Number of potentials  | 15                    |

### Electrical properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 8 A    |
| Nominal voltage $U_N$       | 160 V  |
| Degree of pollution         | 3      |
| Contact resistance          | 2 mΩ   |
| Rated voltage (III/3)       | 160 V  |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 320 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Connection data

#### Connection technology

|                         |                     |
|-------------------------|---------------------|
| Type                    | Standard            |
| Connector system        | COMBICON MC 1,5     |
| Nominal cross section   | 1.5 mm <sup>2</sup> |
| Contact connection type | Socket              |

#### Interlock

|                   |                         |
|-------------------|-------------------------|
| Locking type      | Screw locking mechanism |
| Mounting flange   | Screw flange            |
| Tightening torque | 0.3 Nm                  |

#### Conductor connection

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Connection method                  | Push-in spring connection                    |
| Conductor/PCB connection direction | 0 °                                          |
| Conductor cross section rigid      | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section flexible   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section AWG        | 26 ... 16                                    |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

|                                                                       |                                              |
|-----------------------------------------------------------------------|----------------------------------------------|
| Conductor cross section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| Cylindrical gauge a x b / diameter                                    | 2.4 mm x 1.5 mm / -                          |
| Stripping length                                                      | 9 mm                                         |

## Specifications for ferrules without insulating collar

|                                                              |                                                              |
|--------------------------------------------------------------|--------------------------------------------------------------|
| recommended crimping tool                                    | 1212034 CRIMPFOX 6                                           |
| ferrules without insulating collar, according to DIN 46228-1 | Cross section: 0.25 mm <sup>2</sup> ; Length: 7 mm           |
|                                                              | Cross section: 0.34 mm <sup>2</sup> ; Length: 7 mm           |
|                                                              | Cross section: 0.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm  |
|                                                              | Cross section: 0.75 mm <sup>2</sup> ; Length: 8 mm ... 10 mm |
|                                                              | Cross section: 1 mm <sup>2</sup> ; Length: 8 mm ... 10 mm    |
|                                                              | Cross section: 1.5 mm <sup>2</sup> ; Length: 10 mm           |

## Specifications for ferrules with insulating collar

|                                                           |                                                             |
|-----------------------------------------------------------|-------------------------------------------------------------|
| recommended crimping tool                                 | 1212034 CRIMPFOX 6                                          |
| ferrules with insulating collar, according to DIN 46228-4 | Cross section: 0.14 mm <sup>2</sup> ; Length: 8 mm          |
|                                                           | Cross section: 0.25 mm <sup>2</sup> ; Length: 8 mm          |
|                                                           | Cross section: 0.34 mm <sup>2</sup> ; Length: 8 mm          |
|                                                           | Cross section: 0.5 mm <sup>2</sup> ; Length: 8 mm ... 10 mm |
|                                                           | Cross section: 0.75 mm <sup>2</sup> ; Length: 10 mm         |

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface terminal point (top layer) | Tin (4 - 8 µm Sn)                                                                |
| Metal surface contact area (top layer)   | Tin (4 - 8 µm Sn)                                                                |

### Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | green (6021) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

### Material data – actuating element

|                           |               |
|---------------------------|---------------|
| Color (Actuating element) | orange (2003) |
|---------------------------|---------------|

# FK-MCP 1,5/15-STF-3,5 - PCB connector




1940224

<https://www.phoenixcontact.com/us/products/1940224>

|                                        |     |
|----------------------------------------|-----|
| Insulating material                    | POM |
| Insulating material group              | I   |
| CTI according to IEC 60112             | 600 |
| Flammability rating according to UL 94 | HB  |

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 3.5 mm                                                                             |
| Width [w]           | 62.8 mm                                                                            |
| Height [h]          | 12.4 mm                                                                            |
| Length [l]          | 20.8 mm                                                                            |

## Mounting

|                   |        |
|-------------------|--------|
| Flange            |        |
| Tightening torque | 0.3 Nm |

## Mechanical tests

|                      |                     |
|----------------------|---------------------|
| Conductor connection |                     |
| Specification        | IEC 60999-1:1999-11 |
| Result               | Test passed         |

|                                          |                     |
|------------------------------------------|---------------------|
| Test for conductor damage and slackening |                     |
| Specification                            | IEC 60999-1:1999-11 |
| Result                                   | Test passed         |

|                                       |                     |
|---------------------------------------|---------------------|
| Repeated connection and disconnection |                     |
| Specification                         | IEC 60999-1:1999-11 |
| Result                                | Test passed         |

|                                                                             |                                          |
|-----------------------------------------------------------------------------|------------------------------------------|
| Pull-out test                                                               |                                          |
| Specification                                                               | IEC 60999-1:1999-11                      |
| Conductor cross section/conductor type/tractive force setpoint/actual value | 0.14 mm <sup>2</sup> / solid / > 10 N    |
|                                                                             | 0.14 mm <sup>2</sup> / flexible / > 10 N |
|                                                                             | 1.5 mm <sup>2</sup> / solid / > 40 N     |
|                                                                             | 1.5 mm <sup>2</sup> / flexible / > 40 N  |

|                                     |             |
|-------------------------------------|-------------|
| Insertion and withdrawal forces     |             |
| Result                              | Test passed |
| No. of cycles                       | 25          |
| Insertion strength per pos. approx. | 7 N         |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

|                                    |     |
|------------------------------------|-----|
| Withdraw strength per pos. approx. | 5 N |
|------------------------------------|-----|

## Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

## Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

## Environmental and real-life conditions

### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Sweep speed            | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |

### Durability test

|                                        |                     |
|----------------------------------------|---------------------|
| Specification                          | IEC 60512-5:1992-08 |
| Impulse withstand voltage at sea level | 2.95 kV             |
| Contact resistance $R_1$               | 2 m $\Omega$        |
| Contact resistance $R_2$               | 2.2 m $\Omega$      |
| Insertion/withdrawal cycles            | 25                  |

### Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 1.39 kV                                                                   |

### Shocks

|                 |                                   |
|-----------------|-----------------------------------|
| Specification   | IEC 60068-2-27:2008-02            |
| Pulse shape     | Semi-sinusoidal                   |
| Acceleration    | 30g                               |
| Shock duration  | 18 ms                             |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 20                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | $10^{12} \Omega$      |

### Temperature cycles

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 160 V               |
| Rated surge voltage (III/3)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm              |
| minimum creepage distance (III/3)                      | 2 mm                |
| Rated insulation voltage (III/2)                       | 160 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |
| minimum creepage distance (III/2)                      | 1.5 mm              |
| Rated insulation voltage (II/2)                        | 320 V               |
| Rated surge voltage (II/2)                             | 2.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 1.5 mm              |
| minimum creepage distance (II/2)                       | 1.6 mm              |


## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


1940224

<https://www.phoenixcontact.com/us/products/1940224>

Drawings



Type: FK-MCP 1,5/...-STF-3,5 with MCV 1,5/...-GF-3,5




Type: FK-MCP 1,5/...-STF-3,5 with MCV 1,5/...-GF-3,5 P...THR

# FK-MCP 1,5/15-STF-3,5 - PCB connector


1940224

<https://www.phoenixcontact.com/us/products/1940224>

Dimensional drawing



Diagram



Type: FK-MCP 1,5/...-STF-3,5 with MC 1,5/...-GF-3,5

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1940224>

|                                                                                                                                           |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>cULus Recognized</b><br>Approval ID: E60425-19920306 |                       |                       |                   |                             |
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                               |                       |                       |                   |                             |
|                                                                                                                                           | 300 V                 | 8 A                   | 28 - 16           | -                           |

|                                                                                                                                          |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40011723 |                       |                       |                   |                             |
|                                                                                                                                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                          | 160 V                 | 8 A                   | -                 | 0.2 - 1.5                   |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460202 |
| ECLASS-12.0 | 27460202 |
| ECLASS-13.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## Accessories

### SZS 0,4X2,5 VDE - Screwdriver

1205037

<https://www.phoenixcontact.com/us/products/1205037>



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

---

### SK U/2,8 WH:UNBEDRUCKT - Marker card

0803883

<https://www.phoenixcontact.com/us/products/0803883>



Marker card, Din A4, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, for terminal block width: 210 mm, lettering field size: 186 x 2.8 mm, Number of individual labels: 3600

## FK-MCP 1,5/15-STF-3,5 - PCB connector

1940224

<https://www.phoenixcontact.com/us/products/1940224>



## SK 3,5/2,8:FORTL.ZAHLEN - Marker card

0804073

<https://www.phoenixcontact.com/us/products/0804073>



Marker card, Sheet, white, labeled, horizontal: consecutive numbers 1 ... 10, 11 .  
.. 20, etc. up to 91 ... 99, mounting type: adhesive, for terminal block width: 3.5  
mm, lettering field size: 3.5 x 2.8 mm, Number of individual labels: 14

---

## MPS-MT 1-S - Test plug

1944372

<https://www.phoenixcontact.com/us/products/1944372>

Test plug, consisting of 1.0 mm Ø test pin and 2.0 mm Ø socket



# FK-MCP 1,5/15-STF-3,5 - PCB connector



1940224

<https://www.phoenixcontact.com/us/products/1940224>

## CRIMPFOX 6 - Crimping pliers

1212034

<https://www.phoenixcontact.com/us/products/1212034>




Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm<sup>2</sup> ... 6.0 mm<sup>2</sup>, lateral entry, trapezoidal crimp

---

## MCV 1,5/15-GF-3,5 - PCB header

1843350

<https://www.phoenixcontact.com/us/products/1843350>



PCB headers, nominal cross section: 1.5 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Pin, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: MCV 1,5/..-GF, pitch: 3.5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.4 mm, number of solder pins per potential: 1, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting: Threaded flange, type of packaging: packed in cardboard

# FK-MCP 1,5/15-STF-3,5 - PCB connector




1940224

<https://www.phoenixcontact.com/us/products/1940224>

## MC 1,5/15-GF-3,5 - PCB header

1843923

<https://www.phoenixcontact.com/us/products/1843923>



PCB headers, nominal cross section: 1.5 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Pin, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: MC 1,5/...-GF, pitch: 3.5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.4 mm, number of solder pins per potential: 1, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting: Threaded flange, type of packaging: packed in cardboard

## MC 1,5/15-GF-3,5 P20 THR - PCB header

1713372

<https://www.phoenixcontact.com/us/products/1713372>



PCB headers, nominal cross section: 1.5 mm<sup>2</sup>, color: black, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Pin, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: MC 1,5/...-GF-THR, pitch: 3.5 mm, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 2 mm, number of solder pins per potential: 1, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting: Threaded flange, type of packaging: packed in cardboard

# FK-MCP 1,5/15-STF-3,5 - PCB connector




1940224

<https://www.phoenixcontact.com/us/products/1940224>

## MCV 1,5/15-GF-3,5 P20 THR - PCB header

1713393

<https://www.phoenixcontact.com/us/products/1713393>



PCB headers, nominal cross section: 1.5 mm<sup>2</sup>, color: black, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Pin, number of potentials: 15, number of rows: 1, number of positions: 15, number of connections: 15, product range: MCV 1,5/-GF-THR, pitch: 3.5 mm, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 2 mm, number of solder pins per potential: 1, plug-in system: COMBICON MC 1,5, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting: Threaded flange, type of packaging: packed in cardboard

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)