

ROX05SJ3R6

✓ ACTIVE

Neohm | Neohm ROX

TE Internal #: 1-1676123-6

3.6  $\Omega$ , Metal Oxide Film, General Purpose Resistor, 5 %, 7.2 x 2.5 mm, 2 Termination, Ammo Packed, .5 W,  $\pm 200$  ppm/ $^{\circ}\text{C}$ , Copper Termination, Neohm ROX

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Passive Component Dimensions: **7.2 x 2.5 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Passive Component Tolerance: **5 %**

Features

Product Type Features

|               |                          |
|---------------|--------------------------|
| Resistor Type | General Purpose Resistor |
| Element Type  | Metal Oxide Film         |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                   |
|-----------------------------|-------------------|
| Operating Voltage           | 250 V             |
| Passive Component Tolerance | 5 %               |
| Resistance Class            | Up to 1k $\Omega$ |
| Resistance Value            | 3.6 $\Omega$      |
| Power Rating                | .5 W              |

Body Features

|           |              |
|-----------|--------------|
| Lead Type | Axial-Leaded |
|-----------|--------------|

Termination Features

|  |  |
|--|--|
|  |  |
|--|--|



|                                |        |
|--------------------------------|--------|
| Number of Terminations         | 2      |
| Termination Area Base Material | Copper |

Dimensions

|                              |              |
|------------------------------|--------------|
| Passive Component Dimensions | 7.2 x 2.5 mm |
|------------------------------|--------------|

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±200 ppm/°C  |

Packaging Features

|                  |             |
|------------------|-------------|
| Packaging Method | Ammo Packed |
|------------------|-------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX05SJ3R6

3.6  $\Omega$ , Metal Oxide Film, General Purpose Resistor, 5 %, 7.2 x 2.5 mm, 2 Termination, Ammo Packed, .5 W,  $\pm 200$  ppm/ $^{\circ}\text{C}$ , Copper Termination, Neohm ROX





TE Part # 2-1625892-1  
3W SM M/OX 5% 1K0



TE Part # 4-1625886-1  
1W SM M/OX 5% 820K



TE Part # 6-1676123-7  
1/2W SM M/OX 5% 470R



TE Part # 1625881-2  
1W STD M/OX 2% 220R



TE Part # 1625893-5  
5W SM M/OX 5% 47K

Also in the Series | **Neohm ROX**



Through-Hole Resistors(798)

Customers Also Bought



TE Part #CX7199-000  
RHW-130/35-1200/ADH-0



TE Part #1546670-3  
3P .437" DR BARRIER,W/BND SCRWB



TE Part #2-1676123-8  
1/2W SM M/OX 5% 11R



TE Part #4-1676123-7  
1/2W SM M/OX 5% 68R



TE Part #2-1676123-2  
1/2W SM M/OX 5% 6R2



TE Part #2-1676123-5  
1/2W SM M/OX 5% 8R2



TE Part #5-1676123-0  
1/2W SM M/OX 5% 91R



TE Part #NB07402001  
HTAT-12/3-0-STK

ROX05SJ3R6

3.6 Ω, Metal Oxide Film, General Purpose Resistor, 5 %, 7.2 x 2.5 mm, 2 Termination, Ammo Packed, .5 W, ±200 ppm/°C, Copper Termination, Neohm ROX



Documents

Product Drawings

1/2W SM M/OX 5% 3R6

English

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English