

Sensors > Pressure Sensors > Board Mount Pressure Sensors > Ultra-low Pressure Digital Sensor

Board Level Pressure Sensor Type: [Digital Pressure and Altimeter Sensor Modules](#)Board Level Pressure Sensor Style: [Gauge](#)Pressure: [2.5 mbar](#)Proof Pressure Range: [.07 bar](#)Output/Span: [16 bit I2C](#)[All Ultra-low Pressure Digital Sensor \(24\)](#)

Features

Product Type Features

Board Level Pressure Sensor Type	Digital Pressure and Altimeter Sensor Modules
Board Level Pressure Sensor Style	Gauge

Configuration Features

Tubes	Barb Tube
-------	-----------

Electrical Characteristics

Board Level Pressure Sensor Supply Voltage	5 V
--	-----

Dimensions

Dimensions	10.26 x 10.31 mm [.40 x .41 in]
------------	---------------------------------

Usage Conditions

Operating Temperature Range	-20 – 85 °C [-4 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Output Interface	I ² C
Pressure	2.5 mbar
Proof Pressure Range	.07 bar
Output/Span	16 bit I2C

Board Level Pressure Sensor Accuracy

 $\pm 3\%$ F.S**Packaging Features**

Package Style

Dual Vertical

Board Level Pressure Sensor Package

SOIC-16

Other

Sensor Options

No Option

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-BLPS0062
Ultra-low Pressure Digital Sensor

Also in the Series | SMI 9000



Board Mount Pressure Sensors(24)

Customers Also Bought

TE Part #206708-1
Circular Connector, Environmentally
Sealed, CPC Series 6

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_9233-BCE-S-250-002_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9233-BCE-S-250-002_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9233-BCE-S-250-002_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SM9000

English