


1200V Silicon Carbide Power MOSFET 1200V G1 (N Channel Enhancement)

Features

- High speed switching
- Very low switching losses
- IGBT-compatible driving voltage (18V for turn-on)
- Fully controllable dv/dt
- High blocking voltage with low on-resistance
- Fast intrinsic diode with low reverse recovery(Qrr)
- Temperature independent turn-off switching losses
- Halogen free, RoHS compliant



Benefits

- Cooling effort reduction
- Efficiency improvement
- Reduced cooling requirements
- Increased power density
- Increased system switching frequency

TO-247-3L



Applications

- On-board charger/PFC
- EV battery chargers
- Booster/DC-DC converter
- Switch mode power supplies

Table 1 Key performance and package parameters

Type	V _{DS}	I _{DS} (T _C = 25°C, R _{th (j-c,max)})	R _{D(S(ON), typ} (V _{GS} = 18 V, I _D = 20 A, T _J = 25°C)	T _{j,max}	Marking	Package
S1M075120D1	1200 V	38 A	75 mΩ	175 °C	S1M075120D1	TO247-3L

Table of contents

Table of contents	
Features	1
Benefits	1
Applications	1
Table of contents	2
1、 Maximum ratings	3
2、 Thermal characteristics	3
3、 Electrical characteristics	4
3.1 Static characteristics	4
3.2 Dynamic characteristics	4
3.3 Switching characteristics	5
4、 Electrical characteristic diagrams	6
5、 Package drawing	11
6、 Test conditions	12
Revision history	13
Attention	13

1、Maximum ratings

Table 2 Maximum rating (T_c = 25°C unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
V _{DS,max}	Drain source voltage	1200	V	V _{GS} = 0 V, I _D = 100 μA	
V _{GS,max}	Gate source voltage	-8 /+22	V	Absolute maximum values	Note1
V _{GSop}	Gate source voltage	-4 /+18	V	Recommended operational values	
I _D	Continuous drain current	38	A	V _{GS} = 18 V, T _C = 25°C	Fig.19
		27		V _{GS} = 18 V, T _C = 100°C	
I _{D(pulse)}	Pulsed drain current	80	A	Pulse width t _P limited by T _{j,max}	Fig.22
P _D	Power dissipation	214	W	T _C = 25°C, T _J = 175°C	Fig.20
T _J , T _{stg}	Operating Junction and storage temperature	-55 to +175	°C		
T _L	Soldering temperature	260	°C	1.6mm (0.063") from case for 10s	
T _M	Mounting torque	1 8.8	Nm lbf-in	M3 or 6-32 screw	

Note 1: when using MOSFET Body Diode V_{GS,max} = -4 / +22V

2、Thermal characteristics

Table 3 Thermal characteristics¹

Symbol	Parameter	Value	Unit	Test Conditions	Note
R _{th(j-c)}	Thermal resistance from junction to case	0.7	°C/W		Fig.21
R _{th(j-a)}	Thermal resistance from junction to ambient	35			

¹ Not subject to production test. Parameter verified by design/characterization.

3、Electrical characteristics

3.1 Static characteristics

Table 4 Static characteristics (T_c = 25°C unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
V _{(BR)DSS}	Drain-source breakdown voltage	1200	-	-	V	V _{GS} = 0V, I _D = 100μA	
V _{GS(th)}	Gate threshold voltage	2.3	2.8	3.6	V	V _{DS} = V _{GS} , I _D = 5mA	Fig.11
		-	2.1	-	V	V _{DS} = V _{GS} , I _D = 5mA, T _J = 175°C	
I _{DSS}	Zero gate voltage drain current	-	1	10	μA	V _{DS} = 1200V, V _{GS} = 0V	
I _{GSS}	Gate source leakage current	-	-	100	nA	V _{GS} = 18V, V _{DS} = 0V	
R _{DS(on)}	Current drain-source on-state resistance	-	70	85	mΩ	V _{GS} = 18V, I _D = 20A	Fig.4,5 ,6
		-	125	-		V _{GS} = 18V, I _D = 20A, T _J = 175°C	
g _{fs}	Transconductance	-	10	-	S	V _{DS} = 20V, I _D = 20A	Fig.7
		-	9.2	-		V _{DS} = 20V, I _D = 20A, T _J = 175°C	
R _{g,int}	Internal gate resistance	-	1.5	-	Ω	V _{AC} = 25mV, f = 1MHz	
V _{SD}	Diode forward voltage	-	4.3	-	V	V _{GS} = -4V, I _{SD} = 10A	Fig.8,9, 10
		-	3.8	-		V _{GS} = -4V, I _{SD} = 10A, T _J = 175°C	

3.2 Dynamic characteristics

Table 5 Dynamic characteristics (T_c = 25°C unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
C _{iss}	Input capacitance	-	920	-	pF	V _{DS} = 1000V, V _{GS} = 0V T _J = 25°C, V _{AC} = 25mV f = 1MHz	Fig.17,18
C _{oss}	Output capacitance	-	57	-			
C _{rss}	Reverse capacitance	-	3.9	-			
E _{oss}	Coss stored energy	-	35	-	μJ		Fig.16
Q _{gs}	Gate source charge	-	7	-	nC	V _{DS} = 800V, V _{GS} = -4/+18V I _D = 20A	Fig.12
Q _{gd}	Gate drain charge	-	19	-			
Q _g	Gate charge	-	40	-			

3.3 Switching characteristics

Table 6 Dynamic characteristics($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
E_{on}	Turn on switching energy	-	320	-	μJ	$V_{DD} = 800\text{V}, V_{GS} = -4/+15\text{V}$ $I_D = 20\text{A}, R_g = 0\Omega$ $L = 120\text{uH}$	Fig.25
E_{off}	Turn off switching energy	-	49	-			
$t_{d(on)}$	Turn on delay time	-	19	-			
t_r	Rise time	-	21	-			
$t_{d(off)}$	Turn off delay time	-	15	-			
t_f	Fall time	-	17	-			

Table 7 Body diode characteristics

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode forward voltage	-	4.3	-	V	$V_{GS} = -4\text{V}, I_{SD} = 10\text{A}$	Fig.8,9, 10
		-	3.8	-	V	$V_{GS} = -4\text{V}, I_{SD} = 10\text{A}$ $T_J = 175^\circ\text{C}$	
I_S	Continuous diode forward current	-	38	-	A	$T_c = 25^\circ\text{C}$	Note1
t_{rr}	Reverse recovery time	-	41	-	nS	$V_R = 800\text{V}, V_{GS} = -4\text{V}$ $I_D = 20\text{A}$ $di/dt = 700\text{A}/\mu\text{s}$ $T_J = 150^\circ\text{C}$	
Q_{rr}	Reverse recovery charge	-	405	-	nC		
I_{rrm}	Peak reverse recovery current	-	20	-	A		

Note 1: When using SiC Body Diode the maximum recommended $V_{GS} = -4 \text{ V}$

4、Electrical characteristic diagrams




Figure 1. Output characteristics $T_J = -40^\circ\text{C}$




Figure 2. Output characteristics $T_J = 25^\circ\text{C}$




Figure 3. Output characteristics $T_J = 175^\circ\text{C}$




Figure 4. Normalized on-resistance vs. temperature




Figure 5. On-resistance vs. drain current
for various temperatures




Figure 6. On-resistance vs. temperature
for various gate voltage




Figure 7. Transfer characteristic for
various junction temperatures




Figure 8. Body diode characteristic at $T_J = -40^{\circ}C$




Figure 9. Body diode characteristic at $T_J = 25^{\circ}C$




Figure 10. Body diode characteristic at $T_J = 175^{\circ}C$




Figure 11. Threshold voltage vs. temperature




Figure 12. Gate charge characteristic




Figure 13. 3rd quadrant characteristic at $T_J = -40^\circ\text{C}$




Figure 14. 3rd quadrant characteristic at $T_J = 25^\circ\text{C}$




Figure 15. 3rd quadrant characteristic at $T_J = 175^\circ\text{C}$




Figure 16. Output capacitor stored energy

S1M075120D1

SICHAIN




Figure 17. Capacitances vs. drain-source voltage (0 - 200V)




Figure 18. Capacitances vs. drain-source voltage (0 - 1200V)




Figure 19. Continuous drain current derating vs. case temperature




Figure 20. Maximum power dissipation derating vs. case temperature




Figure 21. Transient thermal impedance
(junction - case)




Figure 22. Safe operating area

S1M075120D1

 SICHAIN




Figure 23. Clamped Inductive switching energy vs. drain current ($V_{DD} = 600V$)




Figure 24. Clamped inductive switching energy vs. drain current ($V_{DD} = 800V$)




Figure 25. Clamped inductive switching energy vs. R_G(ext)




Figure 26. Clamped inductive switching energy vs. temperature




Figure 27. Switching times vs. R_G(ext)





Figure 28. Reverse characteristics vs. T_J

5、Package drawing (TO-247-3L)



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	4.850	5.150	0.191	0.200
A1	2.200	2.600	0.087	0.102
b	1.000	1.400	0.039	0.055
b1	2.800	3.200	0.110	0.126
b2	1.800	2.200	0.071	0.087
c	0.500	0.700	0.020	0.028
c1	1.900	2.100	0.075	0.083
D	15.450	15.750	0.608	0.620
E1	3.500 REF		0.138 REF	
E2	3.600 REF		0.142 REF	
L	40.900	41.300	1.610	1.626
L1	24.800	25.100	0.976	0.988
L2	20.300	20.600	0.799	0.811
Φ	7.100	7.300	0.280	0.287
e	5.450 TYP		0.215 TYP	
H	5.980 REF		0.235 REF	
h	0.000	0.300	0.000	0.012

6、Test conditions




Figure A. Definition of switching times




Figure B. Dynamic test circuit




Figure C. Definition of diode switching characteristics

Figure C. Definition of body diode switching characteristics

Revision history

Document version	Date of release	Description of changes
V01_00	2022-03-03	---
V02_00	2022-09-13	---
V03_00	2023-09-15	---

Attention

1. RoHS compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/ EC (RoHS2), as implemented January 2, 2013.

2. REACH compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Sichain representative to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

3. With respect to information regarding the application of the product, Sichain hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

4. Any information given in this documents subject to customer's compliance with its obligations and any applicable legal requirements, norms and standards concerning any use of the product of Sichain in any customer's applications.

5. Specifications of any and all products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment.

6. Due to technical requirements products may contain dangerous substances. For information on the types in question please contact Sichain office.

7. Except as otherwise explicitly approved by Sichain in a written document signed by authorized representatives of Sichain, Sichain's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.
8. For use of our products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a Sichain representatives, for example but not limited to: transportation equipment, primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.