



## Features

- High Blocking Voltage with Low On-Resistance
- High Speed Switching with Low Capacitances
- Easy to Parallel and Simple to Drive
- Resistant to Latch-Up
- Halogen Free, RoHS Compliant

## Benefits



- Higher System Efficiency
- Reduced Cooling Requirements
- Increased Power Density
- Increased System Switching Frequency

## Applications

- Solar Inverters
- Switch Mode Power Supplies
- High Voltage DC/DC converters
- Battery Chargers
- Motor Drives
- Pulsed Power Applications

Part Number	Package	Marking
C2M0040120D	TO-247-3	C2M0040120

<b>V<sub>DS</sub></b>	1200 V
<b>I<sub>D</sub> @ 25°C</b>	55 A
<b>R<sub>DS(on)</sub></b>	40 mΩ



## Maximum Ratings ( $T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
$V_{DS\max}$	Drain - Source Voltage	1200	V	$V_{GS} = 0 \text{ V}$ , $I_D = 100 \mu\text{A}$	
$V_{GS\max}$	Gate - Source Voltage	-10/+25	V	Absolute maximum values	
$V_{GSop}$	Gate - Source Voltage	-5/+20	V	Recommended operational values	
$I_D$	Continuous Drain Current	55	A	$V_{GS} = 20 \text{ V}$ , $T_c = 25^\circ\text{C}$	Fig. 19
		36		$V_{GS} = 20 \text{ V}$ , $T_c = 100^\circ\text{C}$	
$I_{D(pulse)}$	Pulsed Drain Current	160	A	Pulse width $t_p$ limited by $T_{jmax}$	Fig. 22
$P_D$	Power Dissipation	278	W	$T_c = 25^\circ\text{C}$ , $T_j = 150^\circ\text{C}$	Fig. 20
$T_j$ , $T_{stg}$	Operating Junction and Storage Temperature	-55 to +150	°C		
$T_L$	Solder Temperature	260	°C	1.6mm (0.063") from case for 10s	
$M_d$	Mounting Torque	1 8.8	Nm lbf-in	M3 or 6-32 screw	

**Electrical Characteristics** ( $T_c = 25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	1200			V	$V_{\text{GS}} = 0 \text{ V}, I_D = 100 \mu\text{A}$	
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	2.0	3.2	4	V	$V_{\text{DS}} = V_{\text{GS}}, I_D = 10 \text{ mA}$	Fig. 11
			2.4		V	$V_{\text{DS}} = V_{\text{GS}}, I_D = 10 \text{ mA}, T_J = 150^\circ\text{C}$	
$I_{\text{DSS}}$	Zero Gate Voltage Drain Current		1	100	$\mu\text{A}$	$V_{\text{DS}} = 1200 \text{ V}, V_{\text{GS}} = 0 \text{ V}$	
$I_{\text{GSS}}$	Gate-Source Leakage Current			250	nA	$V_{\text{GS}} = 20 \text{ V}, V_{\text{DS}} = 0 \text{ V}$	
$R_{\text{DS}(\text{on})}$	Drain-Source On-State Resistance		44	52	$\text{m}\Omega$	$V_{\text{GS}} = 20 \text{ V}, I_D = 40 \text{ A}$	Fig. 4,5,6
			82			$V_{\text{GS}} = 20 \text{ V}, I_D = 40 \text{ A}, T_J = 150^\circ\text{C}$	
$g_{\text{fs}}$	Transconductance		18.2		S	$V_{\text{DS}} = 20 \text{ V}, I_{\text{DS}} = 40 \text{ A}$	Fig. 7
			17.2			$V_{\text{DS}} = 20 \text{ V}, I_{\text{DS}} = 40 \text{ A}, T_J = 150^\circ\text{C}$	
$C_{\text{iss}}$	Input Capacitance		2440		$\text{pF}$	$V_{\text{GS}} = 0 \text{ V}$ $V_{\text{DS}} = 1000 \text{ V}$ $f = 1 \text{ MHz}$ $V_{\text{AC}} = 25 \text{ mV}$	Fig. 17,18
$C_{\text{oss}}$	Output Capacitance		171				
$C_{\text{rss}}$	Reverse Transfer Capacitance		11				
$E_{\text{oss}}$	$C_{\text{oss}}$ Stored Energy		89				
$E_{\text{ON}}$	Turn-On Switching Energy (Body Diode)		1.7		$\text{mJ}$	$V_{\text{DS}} = 800 \text{ V}, V_{\text{GS}} = -5/20 \text{ V}$ $I_D = 40 \text{ A}, R_{\text{G(ext)}} = 2.5 \Omega, L = 99 \mu\text{H}$	Fig. 25
$E_{\text{OFF}}$	Turn Off Switching Energy (Body Diode)		0.4				
$E_{\text{ON}}$	Turn-On Switching Energy (External SiC Diode)		1.3				
$E_{\text{OFF}}$	Turn Off Switching Energy (External SiC Diode)		0.4				
$t_{\text{d(on)}}$	Turn-On Delay Time		13		$\text{ns}$	$V_{\text{DD}} = 800 \text{ V}, V_{\text{GS}} = -5/20 \text{ V}$ $I_D = 40 \text{ A}$ $R_{\text{G(ext)}} = 2.5 \Omega, R_L = 20 \Omega$ Timing relative to $V_{\text{DS}}$ Per IEC60747-8-4 pg 83	Fig. 27
$t_r$	Rise Time		61				
$t_{\text{d(off)}}$	Turn-Off Delay Time		25				
$t_f$	Fall Time		13				
$R_{\text{G(int)}}$	Internal Gate Resistance		1.8		$\Omega$	$f = 1 \text{ MHz}, V_{\text{AC}} = 25 \text{ mV}$	
$Q_{\text{gs}}$	Gate to Source Charge		34		$\text{nC}$	$V_{\text{DS}} = 800 \text{ V}, V_{\text{GS}} = -5/20 \text{ V}$ $I_D = 40 \text{ A}$ Per IEC60747-8-4 pg 21	Fig. 12
$Q_{\text{gd}}$	Gate to Drain Charge		42				
$Q_g$	Total Gate Charge		120				

**Reverse Diode Characteristics**

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$V_{SD}$	Diode Forward Voltage	4.0		V	$V_{GS} = -5 V, I_{SD} = 20 A, T_J = 25^\circ C$	Fig. 8, 9, 10
		3.6		V	$V_{GS} = -5 V, I_{SD} = 20 A, T_J = 150^\circ C$	
$I_S$	Continuous Diode Forward Current		60	A	$T_C = 25^\circ C$	Note 1
$I_{S,pulse}$	Diode Pulse Current		160	A	$V_{GS} = -5 V,$ Pulse width $t_P$ limited by $T_{Jmax}$	
$t_{rr}$	Reverse Recovery Time	54		ns	$V_{GS} = -5 V, I_{SD} = 40 A, T_J = 25^\circ C$ $VR = 800 V$ $dif/dt = 1000 A/\mu s$	Note 1
$Q_{rr}$	Reverse Recovery Charge	283		nC		
$I_{rrm}$	Peak Reverse Recovery Current	15		A		

Note (1): When using SiC Body Diode the maximum recommended  $V_{GS} = -5V$

**Thermal Characteristics**

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.33	0.45	°C/W		Fig. 21
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient		40			







**Typical Performance**

 Figure 1. Output Characteristics  $T_j = -55^\circ\text{C}$ 

 Figure 2. Output Characteristics  $T_j = 25^\circ\text{C}$ 

 Figure 3. Output Characteristics  $T_j = 150^\circ\text{C}$ 


Figure 4. Normalized On-Resistance vs. Temperature


 Figure 5. On-Resistance vs. Drain Current  
 For Various Temperatures

 Figure 6. On-Resistance vs. Temperature  
 For Various Gate Voltage

## Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at  $-55^\circ\text{C}$




Figure 9. Body Diode Characteristic at  $25^\circ\text{C}$




Figure 10. Body Diode Characteristic at  $150^\circ\text{C}$




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics

**Typical Performance**




Figure 13. 3rd Quadrant Characteristic at  $-55^\circ\text{C}$




Figure 14. 3rd Quadrant Characteristic at  $25^\circ\text{C}$




Figure 15. 3rd Quadrant Characteristic at  $150^\circ\text{C}$




Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0-200 V)




Figure 18. Capacitances vs. Drain-Source Voltage (0-1000 V)


**Typical Performance**


Figure 19. Continuous Drain Current Derating vs.  
Case Temperature




Figure 20. Maximum Power Dissipation Derating vs.  
Case Temperature




Figure 21. Transient Thermal Impedance  
(Junction - Case)




Figure 22. Safe Operating Area




Figure 23. Clamped Inductive Switching Energy vs.  
Drain Current ( $V_{DD}$  = 600V)




Figure 24. Clamped Inductive Switching Energy vs.  
Drain Current ( $V_{DD}$  = 800V)



**Typical Performance**

 Figure 25. Clamped Inductive Switching Energy vs.  $R_G(\text{ext})$ 


Figure 26. Clamped Inductive Switching Energy vs. Temperature




 Figure 27. Switching Times vs.  $R_G(\text{ext})$ 


Figure 28. Switching Times Definition

### Test Circuit Schematic






Figure 29. Clamped Inductive Switching Waveform Test Circuit

### ESD Ratings

ESD Test	Resulting Classification
ESD-HBM	3A (4000V - 8000V)
ESD-CDM	C3 (>=1000V)

### Package Dimensions

Package TO-247-3




Pinout Information:

- Pin 1 = Gate
- Pin 2, 4 = Drain
- Pin 3 = Source

POS	Inches		Millimeters	
	Min	Max	Min	Max
A	.190	.205	4.83	5.21
A1	.090	.100	2.29	2.54
A2	.075	.085	1.91	2.16
b	.042	.052	1.07	1.33
b1	.075	.095	1.91	2.41
b2	.075	.085	1.91	2.16
b3	.113	.133	2.87	3.38
b4	.113	.123	2.87	3.13
c	.022	.027	0.55	0.68
D	.819	.831	20.80	21.10
D1	.640	.695	16.25	17.65
D2	.037	.049	0.95	1.25
E	.620	.635	15.75	16.13
E1	.516	.557	13.10	14.15
E2	.145	.201	3.68	5.10
E3	.039	.075	1.00	1.90
E4	.487	.529	12.38	13.43
e	.214 BSC		5.44 BSC	
N	3		3	
L	.780	.800	19.81	20.32
L1	.161	.173	4.10	4.40
ØP	.138	.144	3.51	3.65
Q	.216	.236	5.49	6.00
S	.238	.248	6.04	6.30
T	9°	11°	9°	11°
U	9°	11°	9°	11°
V	2°	8°	2°	8°
W	2°	8°	2°	8°

### Recommended Solder Pad Layout



TO-247-3