

FP 0,8/ 52-FV-SH 4,85 - SMD female connector
shielded

1043713
<https://www.phoenixcontact.com/us/products/1043713>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shielded SMD female connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Socket, mounting: SMD soldering

Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Reliable mechanical and electrical connections, thanks to the double-sided ScaleX contact system
- Robustness: ScaleX technology for high tolerance compensation and protection of contacts
- Flexible device design: various numbers of positions, designs, and stack heights with high wipe lengths

Commercial data

Item number	1043713
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	AA23
Product key	AAWDDB
GTIN	4055626612393
Weight per piece (including packing)	2.777 g
Weight per piece (excluding packing)	2.258 g
Customs tariff number	85366930
Country of origin	CZ

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

Technical data

Product properties

Product type	Shielded SMD female connector
Product family	FP 0,8/...-FV-SH 4,85
Number of positions	52
Pitch	0.8 mm
Number of rows	2
Number of potentials	52
Pin layout	Linear pad geometry
Electrical characteristic	shielded

Electrical properties

Nominal current I_N	1.7 A (at 20°C 80-pos.)
Degree of pollution	3
Contact resistance	15 mΩ
Test voltage	500 V AC IEC 60512-4-1:2003
Electrical characteristic	shielded

Mounting

Mounting type	SMD soldering
Pin layout	Linear pad geometry

Processing notes

Process	Reflow soldering
Moisture Sensitive Level	MSL 1
Classification temperature T_c	260 °C

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Selective coating
Metal surface contact area (top layer)	Gold (Au)
Metal surface contact area (middle layer)	Nickel (Ni)
Metal surface soldering area (top layer)	Tin (Sn)
Metal surface soldering area (middle layer)	Nickel (Ni)

Material data - housing

Color (Housing)	black (9005)
Insulating material	LCP
Insulating material group	IIIb
CTI according to IEC 60112	150

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

Flammability rating according to UL 94

V0

Notes

Notes on operation


The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1.

Details for soldering processes

The items are suitable for assembly on both sides and for overhead soldering.

Dimensions

Dimensional drawing



Pitch

0.8 mm

Width [w]

25.58 mm

Height [h]

5.45 mm

Length [l]

7.1 mm

Installed height

4.85 mm

Application

Contact cover

0.8 mm

Center offset

± 0.7 mm in longitudinal and transverse direction

Stack height

6 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 1,15)

7.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 2,65)

12 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 7,15)

13.5 mm Tolerance: +1,5 mm (in combination with Range of articles:FP 0,8/...-MV-SH 8,65)

Wipe length

1.5 mm

Angular tolerance

± 5 ° in longitudinal and transverse direction (when plugging in)

± 5 ° in longitudinal and transverse direction (when plugged in)

Axial offset in X direction (longitudinal)

± 0.3 mm (Tolerance compensation when plugged in)

Axial offset in Y direction (transversal)

± 0.3 mm (Tolerance compensation when plugged in)

PCB design

Pad geometry

0.5 x 1.1 mm

Electrical tests

Thermal test | Test group C

Specification

IEC 60512-5-2:2002-02

Tested number of positions

80

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	$\geq 5 \text{ G}\Omega$

Air clearances and creepage distances |

Insulating material group	IIIb
Minimum value for clearance and creepage distance	0.25 mm

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 2000 - 10 Hz
Sweep speed	1 octave/min
Amplitude	1.5 mm (10 Hz ... 60.1 Hz)
Sweep speed	200 m/s ² (58 Hz ... 2000 Hz)
Test duration per axis	2.5 h

Durability test

Specification	IEC 60512-9-1:2010-03 (following)
Impulse withstand voltage at sea level	0.8 kV
Contact resistance R_1	15 m Ω
Contact resistance R_2	15 m Ω
Insertion/withdrawal cycles	500
Insulation resistance, neighboring positions	$\geq 5 \text{ G}\Omega$

Climatic test

Specification	IEC 60512-11-7:2003-05
Corrosive stress	Method 1, 10 days
Power-frequency withstand voltage	500 V AC

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	490 m/s ²
Shock duration	11 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions


Ambient temperature (operation)	-55 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Packaging specifications

FP 0,8/ 52-FV-SH 4,85 - SMD female connector
shielded



1043713
<https://www.phoenixcontact.com/us/products/1043713>

Dimensional drawing	
Type of packaging	44 mm wide tape
[W] tape width	44 mm
[W2] coil overall dimension	50 mm
[A] coil diameter	330 mm
Outer packaging type	Transparent-Bag
ESD level	(D) electrostatically conductive
Specification	DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07


FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded

1043713

<https://www.phoenixcontact.com/us/products/1043713>


Drawings

Diagram



Type: FP 0,8/...-MV-SH 7,15 with FP 0,8/...-FV-SH 4,85 - contacts

Schematic diagram




FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded




1043713

<https://www.phoenixcontact.com/us/products/1043713>



Type: FP 0,8/...-MV-SH 2,65 with FP 0,8/...-FV-SH 4,85



Type: FP 0,8/...-MV-SH 7,15 with FP 0,8/...-FV-SH 4,85 - shroud

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1043713>



cULus Recognized

Approval ID: E118976-20190703



EAC

Approval ID: B.00511/19

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

Classifications

ECLASS

ECLASS-11.0	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201

ETIM

ETIM 8.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FP 0,8/ 52-FV-SH 4,85 - SMD female connector
shielded



1043713
<https://www.phoenixcontact.com/us/products/1043713>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713


<https://www.phoenixcontact.com/us/products/1043713>

Mandatory accessories

FP 0,8/ 52-MH-SH - SMD male connector, shielded

1043793

<https://www.phoenixcontact.com/us/products/1043793>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

FP 0,8/ 52-MV-SH 1,15 - SMD male connector, shielded

1043789

<https://www.phoenixcontact.com/us/products/1043789>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

FP 0,8/ 52-MV-SH 2,65 - SMD male connector, shielded

1043756

<https://www.phoenixcontact.com/us/products/1043756>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

FP 0,8/ 52-MV-SH 7,15 - SMD male connector, shielded

1154008

<https://www.phoenixcontact.com/us/products/1154008>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

FP 0,8/ 52-MV-SH 8,65 - SMD male connector, shielded

1154122

<https://www.phoenixcontact.com/us/products/1154122>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

Accessories

FP 0,8/ 52-MV-SH 1,15 - SMD male connector, shielded

1043789

<https://www.phoenixcontact.com/us/products/1043789>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC, number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold, contact connection type: Pin, mounting: SMD soldering

FP 0,8/ 52-FV-SH 4,85 - SMD female connector shielded



1043713

<https://www.phoenixcontact.com/us/products/1043713>

FP 0,8/ 52-MV-SH 8,65 - SMD male connector, shielded

1154122

<https://www.phoenixcontact.com/us/products/1154122>



shielded SMD male connector, nominal current: 1.7 A, Test voltage: 500 V AC,
number of positions: 52, pitch: 0.8 mm, color: black, contact surface: Gold,
contact connection type: Pin, mounting: SMD soldering

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com