

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Potential distributors, nom. voltage: 250 V, nominal current: 17.5 A, connection method: Push-in connection, 1st, 2nd, 3rd and 4th level, Rated cross section: 1.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 2.5 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: gray, color of connection elements: red

## Your advantages

- Tool-free wiring in a confined space thanks to compact size
- Distributor terminal block in red for 24 V DC power supplies
- High contact quality thanks to push-in technology as a replacement for Wire-Wrap®, TERMI-POINT®, etc.
- Bridgeable potential distributor

## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 3270222            |
| Packing unit                         | 10 pc              |
| Minimum order quantity               | 10 pc              |
| Sales key                            | BE62               |
| Product key                          | BE6211             |
| Catalog page                         | Page 48 (C-1-2019) |
| GTIN                                 | 4055626186382      |
| Weight per piece (including packing) | 21.54 g            |
| Weight per piece (excluding packing) | 21.54 g            |
| Customs tariff number                | 85369010           |
| Country of origin                    | PL                 |

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Potential distributor |
| Number of positions   | 2                     |
| Number of connections | 16                    |
| Number of rows        | 4                     |
| Potentials            | 1                     |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 4 kV   |
| Maximum power dissipation for nominal condition | 0.56 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 4                   |
| Nominal cross section           | 1.5 mm <sup>2</sup> |

#### 1st, 2nd, 3rd and 4th level

|                                                                   |                                                                     |
|-------------------------------------------------------------------|---------------------------------------------------------------------|
| Stripping length                                                  | 8 mm ... 10 mm                                                      |
| Connection in acc. with standard                                  | IEC 60947-7-1                                                       |
| Conductor cross section rigid                                     | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                        |
| Cross section AWG                                                 | 26 ... 14 (converted acc. to IEC)                                   |
| Conductor cross section flexible                                  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                        |
| Conductor cross section, flexible [AWG]                           | 26 ... 16 (converted acc. to IEC)                                   |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                        |
| Flexible conductor cross section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                        |
| Nominal current                                                   | 17.5 A (with 1.5 mm <sup>2</sup> conductor cross section)           |
| Maximum load current                                              | 24 A (per chamber with 2.5 mm <sup>2</sup> conductor cross section) |
| Maximum total current                                             | 37 A (per potential distributor)                                    |
| Nominal voltage                                                   | 250 V                                                               |
| Nominal cross section                                             | 1.5 mm <sup>2</sup>                                                 |

#### 1st, 2nd, 3rd and 4th level Connection cross sections directly pluggable

|                                                                   |                                              |
|-------------------------------------------------------------------|----------------------------------------------|
| Conductor cross section rigid                                     | 0.34 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section, rigid [AWG]                              | 20 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Flexible conductor cross section (ferrule with plastic sleeve)    | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |

### Dimensions

|                    |         |
|--------------------|---------|
| Width              | 8.3 mm  |
| Height             | 64 mm   |
| Depth on NS 35/7,5 | 55.5 mm |

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

|                   |       |
|-------------------|-------|
| Depth on NS 35/15 | 63 mm |
|-------------------|-------|

## Material specifications

|                                                                         |             |
|-------------------------------------------------------------------------|-------------|
| Color                                                                   | gray        |
| Color of connection elements                                            | red         |
| Flammability rating according to UL 94                                  | V0          |
| Insulating material group                                               | I           |
| Insulating material                                                     | PA          |
| Static insulating material application in cold                          | -60 °C      |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C      |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C      |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg  |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed      |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed      |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed      |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 4.8 kV      |
| Result                | Test passed |

### Temperature-rise test

|                                                  |                                     |
|--------------------------------------------------|-------------------------------------|
| Requirement temperature-rise test                | Increase in temperature $\leq$ 45 K |
| Result                                           | Test passed                         |
| Short-time withstand current 1.5 mm <sup>2</sup> | 0.18 kA                             |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                              |
| Result                                           | Test passed                         |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.5 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 1 N         |
| Result                  | Test passed |

## Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross section/weight | 0.14 mm <sup>2</sup> / 0.2 kg |
|                                | 1.5 mm <sup>2</sup> / 0.4 kg  |
|                                | 2.5 mm <sup>2</sup> / 0.7 kg  |
| Result                         | Test passed                   |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                |
|------------------------|------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2008-03            |
| Spectrum               | Service life test category 2, bogie-mounted    |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g                                          |
| Test duration per axis | 5 h                                            |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 30g                                 |
| Shock duration                 | 18 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|                                         |                                                                           |
|-----------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)         | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

|                                          |                 |
|------------------------------------------|-----------------|
| Ambient temperature (assembly)           | -5 °C ... 70 °C |
| Ambient temperature (actuation)          | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations


|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

## Drawings

Circuit diagram



# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3270222>

### DNV

Approval ID: TAE000016Y



### CSA

Approval ID: 2030668

|             | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------------|-----------------------|-----------------------|-------------------|-----------------------------|
| Use group B |                       |                       |                   |                             |
|             | 300 V                 | 10 A                  | 26 - 14           | -                           |
| Use group D |                       |                       |                   |                             |
|             | 300 V                 | 10 A                  | 26 - 14           | -                           |



### IECEE CB Scheme

Approval ID: NL-58817

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 250 V                 | 17.5 A                | -                 | -                           |



### EAC

Approval ID: RU C-DE.BL08.B.00682



### cULus Recognized

Approval ID: E60425



### KEMA-KEUR

Approval ID: 71-102890

|                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| Only flexible conductors | 250 V                 | 17.5 A                | -                 | 0.14 - 1.5                  |
| Only rigid conductors    | 250 V                 | 17.5 A                | -                 | 0.14 - 2.5                  |



### cULus Recognized

Approval ID: E60425



### cULus Recognized

Approval ID: E60425

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27141120 |
| ECLASS-13.0 | 27250119 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## Accessories

**i** Note: Applying some accessories below might limit this product.

### FBST 500-PLC RD - Continuous plug-in bridge

2966786

<https://www.phoenixcontact.com/us/products/2966786>



Continuous plug-in bridge, length: 500 mm, color: red

**i** Max. current carrying capacity: 32 A

---

### FBST 500-PLC GY - Continuous plug-in bridge

2966838

<https://www.phoenixcontact.com/us/products/2966838>



Continuous plug-in bridge, length: 500 mm, color: gray

**i** Max. current carrying capacity: 32 A

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## FBST 500-PLC BN - Continuous plug-in bridge

2967976

<https://www.phoenixcontact.com/us/products/2967976>



Continuous plug-in bridge, length: 500 mm, color: brown


 Max. current carrying capacity: 32 A

---

## FBST 500-PLC BU - Continuous plug-in bridge

2966692

<https://www.phoenixcontact.com/us/products/2966692>



Continuous plug-in bridge, length: 500 mm, color: blue

 Max. current carrying capacity: 32 A

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## DP-PTRV 4 - Spacer plate

3270163

<https://www.phoenixcontact.com/us/products/3270163>



Spacer plate, depth: 54 mm, width: 8.3 mm, height: 63.6 mm, color: gray

---

## CDC-PTRV - Retaining bracket

3270167

<https://www.phoenixcontact.com/us/products/3270167>



Retaining bracket, via four PTRV single modules, pitch: 8.3 mm, depth: 71.5 mm, width: 35.6 mm, height: 71.5 mm, color: gray

## PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

### RPS - Reducing plug

0201647

<https://www.phoenixcontact.com/us/products/0201647>



Reducing plug, number of positions: 1, color: gray

---

### FBST 50-PLC RD - Plug-in bridge

1081050

<https://www.phoenixcontact.com/us/products/1081050>



Plug-in bridge, length: 50 mm, color: red

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## FBST 50-PLC BU - Plug-in bridge

1081051

<https://www.phoenixcontact.com/us/products/1081051>



Plug-in bridge, length: 50 mm, color: blue

---

## FBST 50-PLC GY - Plug-in bridge

1081053

<https://www.phoenixcontact.com/us/products/1081053>



Plug-in bridge, length: 50 mm, color: gray

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## ZB 8,3:UNBEDRUCKT - Zack marker strip

0803444

<https://www.phoenixcontact.com/us/products/0803444>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.3 mm, lettering field size: 10.5 x 8.3 mm

---

## ZB 8,3,LGS:FORTL.ZAHLEN - Zack marker strip

0803480

<https://www.phoenixcontact.com/us/products/0803480>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.3 mm, lettering field size: 10.5 x 8.3 mm

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## ZB 8,3,QR:FORTL.ZAHLEN - Zack marker strip

0803479

<https://www.phoenixcontact.com/us/products/0803479>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.3 mm, lettering field size: 10.5 x 8.3 mm

---

## ZB 8,3 CUS - Zack marker strip

8191573

<https://www.phoenixcontact.com/us/products/8191573>



Zack marker strip, Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.3 mm, lettering field size: 10.5 x 8.3 mm

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## TM-PTRV 4,QR:1-4 - Marker for terminal blocks

0803464

<https://www.phoenixcontact.com/us/products/0803464>



Marker for terminal blocks, white, labeled, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 2.4 x 9.2 mm

---

## TM-PTRV 4,QR:4-1 - Marker for terminal blocks

0803465

<https://www.phoenixcontact.com/us/products/0803465>



Marker for terminal blocks, white, labeled, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 2.4 x 9.2 mm

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## TM-PTRV 4,QR:A-D - Marker for terminal blocks

0803466

<https://www.phoenixcontact.com/us/products/0803466>



Marker for terminal blocks, white, labeled, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 2.4 x 9.2 mm

---

## TM-PTRV 4,QR:D-A - Marker for terminal blocks

0803467

<https://www.phoenixcontact.com/us/products/0803467>



Marker for terminal blocks, white, labeled, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 2.4 x 9.2 mm

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## D-PTRV 4 WH - End cover

3270151

<https://www.phoenixcontact.com/us/products/3270151>

End cover, depth: 48.9 mm, width: 3.8 mm, height: 63.6 mm, color: white



---

## D-PTRV 4 WH 1-4 - End cover

3270152

<https://www.phoenixcontact.com/us/products/3270152>

End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white



# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## D-PTRV 4 WH 1-4 LGS - End cover

3270234

<https://www.phoenixcontact.com/us/products/3270234>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

---

## D-PTRV 4 WH 4-1 - End cover

3270236

<https://www.phoenixcontact.com/us/products/3270236>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## D-PTRV 4 WH 4-1 LGS - End cover

3270238

<https://www.phoenixcontact.com/us/products/3270238>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

---

## D-PTRV 4 WH A-D - End cover

3270153

<https://www.phoenixcontact.com/us/products/3270153>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## D-PTRV 4 WH A-D LGS - End cover

3270235

<https://www.phoenixcontact.com/us/products/3270235>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

---

## D-PTRV 4 WH D-A - End cover

3270237

<https://www.phoenixcontact.com/us/products/3270237>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

## PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

### D-PTRV 4 WH D-A LGS - End cover

3270239

<https://www.phoenixcontact.com/us/products/3270239>



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

---

### NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/us/products/0801733>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/us/products/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

---

## NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/us/products/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/us/products/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

---

## NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/us/products/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/us/products/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

---

## NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/us/products/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/us/products/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

---

## NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/us/products/1206560>



DIN rail end piece, for DIN rail NS 35/7.5

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## CLIPFIX 35 - End bracket

3022218

<https://www.phoenixcontact.com/us/products/3022218>

Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray



---

## CLIPFIX 35-5 - End bracket

3022276

<https://www.phoenixcontact.com/us/products/3022276>

Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray



# PTRVB 4-PV /RD - Potential distributors



3270222


<https://www.phoenixcontact.com/us/products/3270222>

## E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/us/products/0800886>

End clamp, width: 9.5 mm, color: gray



---

## E/UK - End bracket

1201442

<https://www.phoenixcontact.com/us/products/1201442>

End bracket, Mounting on a DIN rail NS 32 or NS 35, material: PA, color: gray



# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## E/UK 1 - End bracket

1201413

<https://www.phoenixcontact.com/us/products/1201413>



End clamps, for supporting the ends of double-level and three-level terminal blocks, width: 10 mm, color: gray

---

## MPS-MT - Test plug

0201744

<https://www.phoenixcontact.com/us/products/0201744>



Test plug, with solder connection up to 1 mm<sup>2</sup> conductor cross section, number of positions: 1, color: gray

# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## MPS-IH WH - Insulating sleeve

0201663

<https://www.phoenixcontact.com/us/products/0201663>

Insulating sleeve, color: white



---

## MPS-IH RD - Insulating sleeve

0201676

<https://www.phoenixcontact.com/us/products/0201676>

Insulating sleeve, color: red



# PTRVB 4-PV /RD - Potential distributors



3270222


<https://www.phoenixcontact.com/us/products/3270222>

## MPS-IH BU - Insulating sleeve

0201689

<https://www.phoenixcontact.com/us/products/0201689>

Insulating sleeve, color: blue



---

## MPS-IH YE - Insulating sleeve

0201692

<https://www.phoenixcontact.com/us/products/0201692>

Insulating sleeve, color: yellow



## PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

### MPS-IH GN - Insulating sleeve

0201702

<https://www.phoenixcontact.com/us/products/0201702>

Insulating sleeve, color: green



---

### MPS-IH GY - Insulating sleeve

0201728

<https://www.phoenixcontact.com/us/products/0201728>

Insulating sleeve, color: gray



# PTRVB 4-PV /RD - Potential distributors



3270222

<https://www.phoenixcontact.com/us/products/3270222>

## MPS-IH BK - Insulating sleeve

0201731

<https://www.phoenixcontact.com/us/products/0201731>

Insulating sleeve, color: black



---

## ST-BW 0 - Actuation tool

1200135

<https://www.phoenixcontact.com/us/products/1200135>

Actuation tool, for all 1.5 mm<sup>2</sup> spring cages from PT 1,5/S and FT 1,5/S



---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)