




■ Features

- High Current Capability
- Low Forward Voltage Drop
- Extremely Fast Switching Speed

■ Mechanical Data


- package:SOT-23
- Flammability rating of epoxy resin: UL 94V-0
- Mounting Position: Any



■ Ordering Information

Part Number	Package	Marking	Packing	Quantity per reel	Reel Size
BAT54	SOT-23	KL1	Tape & Reel	3,000 PCS	7 inches
BAT54A	SOT-23	KL2	Tape & Reel	3,000 PCS	7 inches
BAT54C	SOT-23	KL3	Tape & Reel	3,000 PCS	7 inches
BAT54S	SOT-23	KL4	Tape & Reel	3,000 PCS	7 inches

■ Pin Configuration



**■ Maximum Ratings & Thermal Characteristics(Ratings at 25°C ambient temperature unless otherwise specified.)**

Parameters	Symbol	Limit	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	30	V
Maximum RMS voltage	V _{RMS}	21	V
Maximum DC blocking voltage	V _{DC}	30	V
Maximum average forward rectified current	I _{FM}	200	mA
Peak forward surge current 8.3 ms single half sine-wave	I _{FSM}	600	mA
Typical thermal resistance	R _{θJA}	500	°C/W
Power Dissipation	P _D	200	mW
Junction Temperature	T _j	125	°C
Storage temperature range	T _{STG}	-50~+150	°C


■ Electrical Characteristics(Ratings at 25°C ambient temperature unless otherwise specified)

Parameters	Symbol	Test conditions	Min	Typ	Max	Unit
Maximum forward voltage	VF1	IF = 0.1mA			240	mV
	VF2	IF = 1.0mA			320	
	VF3	IF = 10mA			400	
	VF4	IF = 30mA			500	
	VF5	IF = 100mA			1000	
Maximum reverse breakdown voltage	V _R	IR=100uA	30			V
Maximum reverse current	I _R	VR=25V			2.0	uA
Type junction capacitance	C _j	VR = 1.0V, f = 1MHz			10	pF
Reverse Recovery time	t _{rr}	IF=IR=10mA I _{rr} =0.1XIR, R _L =100 Ω			5	ns




■ Typical Characteristics


Forward Characteristics




Reverse Characteristics



Capacitance Characteristics




Power Derating Curve





■ SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°		8°	