



1 2 3 4 5 6 7 8 9

F



E



D

C

Specifications
 Current Rating: 2.0Amp
 Insulation Resistance: 1000M Ω Min.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20m Ω Max.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Phosphor Bronze
 Insulator Material:
 PBT (Not resistant to high temperature),
 Nylon (High temperature resistance),
 LCP (High temperature resistance),
 UL 94V-0
 All materials must meet Greenconn
 hazardous substances control standards.

F


E

D

C

B

A



No. of PIN/ROW	Dimension Information	
	M	L
02	2.00	4.50
03	4.00	6.50
04	6.00	8.50
05	8.00	10.50
06	10.00	12.50
07	12.00	14.50
08	14.00	16.50
09	16.00	18.50
10	18.00	20.50
11	20.00	22.50
12	22.00	24.50
13	24.00	26.50
14	26.00	28.50
15	28.00	30.50
16	30.00	32.50
17	32.00	34.50
18	34.00	36.50
19	36.00	38.50
20	38.00	40.50
21	40.00	42.50
22	42.00	44.50
23	44.00	46.50
24	46.00	48.50
25	48.00	50.50
26	50.00	52.50
27	52.00	54.50
28	54.00	56.50
29	56.00	58.50
30	58.00	60.50
31	60.00	62.50
32	62.00	64.50
33	64.00	66.50
34	66.00	68.50
35	68.00	70.50
36	70.00	72.50
37	72.00	74.50
38	74.00	76.50
39	76.00	78.50
40	78.00	80.50

Ordering Information

CSFB203 - XX XX A XXX C 1 S X

Plastic specifications
 1=Single row
 2=Dual row
 3=Tripe row
 4=Quadruple

Water code

Positioning column information
 A=No locating post
 B=Round post
 C=Square post

Pin length
 See the drawing

Color
 1=Black
 2=White
 3=Yellow
 E=Beige

Packing code
 A=Box
 B=Tray
 C=Tube
 D=Tape&Reel
 G=Acetate Tape+Tube
 H=Acetate Tape+Tape&Reel


No. of Pins per Row
 02~40

Plating code
 01=Tin
 02=Gold Flash
 05=Gold Flash/Tin
 22=Matte Tin

Contact Material
 A/S/K/T=Phosphor Bronze

Insulator Material
 A=PBT
 R=Nylon(Halogen Free)
 C=LCP

Recommended P.C.Board Layout (Tolerance: ± 0.05)



A

格稜股份有限公司 Greenconn Corporation				GENERAL TOLERANCE		DESIGNED:	DATE:	DWG. NO. CSFB203-CAXX	TITLE. 2.00 FEMALE HEADER DUAL ROW (R/A) TYPE SIDE ENTRY
				X.* $\pm 5.0^{\circ}$	X. ± 0.30				
REV. 01	UNIT. mm	SCALE. 4:1	PAGE. 1/1	.X.* $\pm 3.0^{\circ}$.X. ± 0.25	CO SIGNED:	DATE:	PART NO. CSFB203-XXXX AXXX X1SX	
				.XX* $\pm 2.0^{\circ}$.XX ± 0.15	APPROVED:	DATE:		
				.XXX* $\pm 1.0^{\circ}$.XXX ± 0.10				

1 2 3 4 5 6 7 8 9