intel.

Intel[®] Celeron[®] Processor - Low Power for Applied Computing

Product Highlights

■ 300 MHz and 400 MHz:

- Built on the Intel 0.18 micron process
- 128K Full speed on-die L2 cache operating at core frequency
- Low profile, surface mount BGA package
- BGA (31 x 27 x 2.5mm), (BGA2)
- 495 leads in area array
- Tcase: 0 to 100C
- 650 MHz:
 - Built on the Intel 0.13 micron process
 - 256K Full speed on-die L2 cache operating at core frequency
 - Low profile, surface mount µFCBGA package
 - µFCBGA package (35 x 35 mm)
 - 479 balls in area array
 - Tcase: 0 to 100C
- Functional features
 - MMX technology
 - Floating Point Unit (FPU)
- Dynamic Execution Micro-Architecture
- On-Die L2 Cache with Error Checking and Correcting (ECC)

Low Power 400 MHz

- 400 MHz processor speed
- 100 MHz processor side bus
- 10.1W TDP (max). 6.5 W TDP (typ)
- Supported with the Intel* 815, Intel* 815E, Intel* 440BX AGPset and Intel* 440MX Chipsets

Ultra-Low Power 300 MHz

- 300 MHz processor speed
- 100 MHz processor side bus
- 5.7W TDP (max), 4.2 W TDP (typ)
- Supported with the Intel 815, Intel 815E, and the Intel 440MX Chipsets



Ultra-Low Voltage 650 MHz

- 650 MHz processor speed
- 100 MHz processor side bus
- 8.3W TDP (max), 7.0W TDP (typ)
- Supported with Intel 440MX and Intel 815E chipsets

Product Overview

The Intel[®] Celeron[®] processors - Low Power, Ultra Low Power and Ultra Low Voltage now provide an exceptional value for thermally sensitive and space constrained applied computing applications by combining the optimal balance of cost, performance, and low power. Available in the small form factor BGA package at 300 and 400 MHz with 128K of on-die L2 cache or the μ FCBGA package at 650 MHz with 256K of on-die L2 cache. These features make it ideal for value-based, lowprofile, low-power applied computing applications, such as data communications, telecommunications, industrial automation and transaction terminals.

The 300 MHz processor, at just 1.1V and 5.7 W TDP (max), and the 650 MHz processor, also at 1.1V and with a 8.3W TDP (max), are ideal solutions for communication appliances such as set-top boxes, network attached storage, web pads and other applications with lower power envelopes and BOM requirements.

Product Description

The Embedded Intel[®] Architecture low power family features a 100 MHz processor side bus, designed for a faster transfer of data, to yield an increase in performance. The 128K/256K of on-die L2 cache combined with the efficiencies of the 0.18 and 0.13 micron manufacturing processes offers good low power processor performance for value based systems. The compact form factor results in a low profile, meeting small space requirement. This enables a variety of value-based designs for thermally sensitive and space constrained environments.

INTEL® CELERON® PROCESSORS - LOW POWER, ULTRA LOW POWER, & Ultra low voltage

PRODUCT NUMBER	CORE SPEED (MHz)	EXTERNAL BUS SPEED (MHz)	L2 Cache	THERMAL DESIGN POWER (MAX)	VOLTAGE	TCASE	PACKAGE
RJ80530VY650256	650	100	256K	8.3 watts	1.1V	0-100C	479 µFCBGA
KC80526LY400128	400	100	128K	10.1 watts	1.35V	0-100C	495 BGA
KC80526LL300128	300	100	128K	5.7 watts	1.1V	0-100C	495 BGA

Intel Access

Developer's Site	developer.intel.com	
Embedded Intel® Architecture Home Page	developer.intel.com/design/intarch	
Other Intel Support:	developer.intel.com/design/litcentr	
Intel Literature Center	(800) 548-4725 7 a.m. to 7 p.m. CST (U.S. and Canada) International locations please contact your local sales office.	
General Information Hotline	(800) 628-8686 or (916) 356-3104 5 a.m. to 5 p.m. PST	
Information in this document is provided in connection with Intel products. No license, express or implied, by estoppel or ot to any intellectual property rights is granted by this document. Except as provided in Intel's Terms and Conditions of Sale for s products, Intel assumes no liability whatsoever, and Intel disclaims any express or implied warranty, relating to sale and/or use		

to any intellectual property rights is granted by this document. Except as provided in Intel's Terms and Conditions of Sale for such products, Intel assumes no liability whatsoever, and Intel disclaims any express or implied warranty, relating to sale and/or use of Intel products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. Intel products are not intended for use in medical, life saving, or life sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

Designers must not rely on the absence or characteristics of any features or instructions marked "reserved" or "undefined." Intel reserves these for future definition and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to them.

Intel, the Intel logo, and Celeron are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States or other countries.

*Other names and brands may be claimed as the property of others.

For more information, visit the Intel Web site at: developer.intel.com

UNITED STATES AND CANADA Intel Corporation Robert Noyce Bldg. 2200 Mission College Blvd. P.O. Box 58119 Santa Clara, CA 95052-8119 USA

EUROPE Intel Corporation (UK) Ltd. Pipers Way Swindon Wiltshire SN3 1RJ UK ASIA-PACIFIC Intel Semiconductor Ltd. 32/F Two Pacific Place 88 Queensway, Central Hong Kong, SAR JAPAN Intel Kabushiki Kaisha P.O. Box 115 Tsukuba-gakuen 5-6 Tokodai, Tsukuba-shi Ibaraki-ken 305 Jaoan

SOUTH AMERICA Intel Semicondutores do Brazil Rue Florida, 1703-2 and CJ22 CEP 04565-001 Sao Paulo-SP Brazil

inte