

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484 EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

## INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

# CS15-01P95-03-1X

Rev. 1-2022 RoHS3 & REACH IP67 Front Face Mobile Speakers



#### **Operating Characteristics** ELECTRICAL 104 102 100 Rated Power 1.0 W 98 96 94 92 90 88 86 84 82 80 78 76 74 72 70 68 66 64 62 60 58 56 54 52 50 **Short Term** 1.3 W Max Power $8 \Omega \pm 15 \%$ Impedance 2000 Hz; 1.0 W ACOUSTIC: 1CC Sealed Enclosure 950 Hz ± 20 % fo 950 to 20000 Hz Freq. Range $97 \pm 3 \, dB$ Rated SPL 800, 1000, 1500, 2000 Hz; 1 W; 10 cm; <10 % Distortion 2000 Hz; 1.0 W


# Physical Characteristics MATERIALS

RIALS		
Housing	PPA	
Cone	PEEK	
Magnet	NdFeB	
Solder Pad	Tin-Plated Stainless Steel	

## TEMPERATURE RANGES

Operating -20 to +70 °C
Storage -40 to +80 °C

Weight 1.5 g



Frequency (Hz)

General tolerance =  $\pm 0.2$  mm and all measurements in mm unless otherwise noted.

Revision	Description	Ву	Date
0-2020	Original Specification	SP	2020-06-16
1-2022	Added minimum diaphragm clearance requirement callout to the mechanical drawing. Added product photo.	CT	2022-05-12

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.