



**HARRIS**

# IRFP140R, IRFP141R IRFP142R, IRFP143R

**N-Channel Power MOSFETs  
Avalanche Energy Rated**

August 1991

### Features


- 27A and 31A, 80V - 100V
- $r_{DS(on)} = 0.077\Omega$  and  $0.099\Omega$
- Single Pulse Avalanche Energy Rated
- SOA is Power-Dissipation Limited
- Nanosecond Switching Speeds
- Linear Transfer Characteristics
- High Input Impedance

### Description

The IRFP140R, IRFP141R, IRFP142R, and IRFP143R are advanced power MOSFETs designed, tested and guaranteed to withstand a specified level of energy in the breakdown avalanche mode of operation. These are n-channel enhancement-mode silicon-gate power field-effect transistors designed for applications such as switching regulators, switching converters, motor drivers, relay drivers, and drivers for high-power bipolar switching transistors requiring high speed and low gate-drive power. These types can be operated directly from integrated circuits.


The IRFP types are supplied in the JEDEC TO-247 plastic package.

### Package



### Terminal Diagram

N-CHANNEL ENHANCEMENT MODE



### Absolute Maximum Ratings ( $T_C = +25^\circ\text{C}$ ), Unless Otherwise Specified


	IRFP140R	IRFP141R	IRFP142R	IRFP143R	UNITS
Drain-Source Voltage (1) .....	$V_{DS}$ 100	80	100	80	V
Drain-Gate Voltage ( $R_{GS} = 20k\Omega$ ) (1) .....	$V_{DGR}$ 100	80	100	80	V
Continuous Drain Current					
$T_C = +25^\circ\text{C}$ .....	$I_D$ 31	31	27	27	A
$T_C = +100^\circ\text{C}$ .....	$I_D$ 22	22	19	19	A
Pulsed Drain Current (3) .....	$I_{DM}$ 120	120	110	110	A
Gate-Source Voltage .....	$V_{GS}$ $\pm 20$	$\pm 20$	$\pm 20$	$\pm 20$	V
Maximum Power Dissipation					
$T_C = +25^\circ\text{C}$ .....	$P_D$ 180	180	180	180	W
Linear Derating Factor .....	1.2	1.2	1.2	1.2	W/ $^\circ\text{C}$
Single Pulse Avalanche Energy Rating (4) .....	$E_{as}$ 100	100	100	100	mJ
Operating and Storage Junction Temperature Range .....	$T_J, T_{STG}$ -55 to +175	-55 to +175	-55 to +175	-55 to +175	$^\circ\text{C}$
Maximum Lead Temperature for Soldering (0.063" (1.6mm) from case for 10s) .....	$T_L$ 300	300	300	300	$^\circ\text{C}$

#### NOTES:

- $T_J = +25^\circ\text{C}$  to  $+150^\circ\text{C}$ .
- Pulse Test: Pulse width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .
- Repetitive Rating: Pulse width limited by max. junction temperature. See Transient Thermal Impedance Curve (Figure 5).
- $V_{DD} = 25\text{V}$ , starting  $T_J = +25^\circ\text{C}$ ,  $L = 160\mu\text{H}$ ,  $R_{GS} = 50\Omega$ ,  $I_{PEAK} = 31\text{A}$ . See Figures 14 and 15.

# Specifications IRFP140R, IRFP141R, IRFP142R, IRFP143R

**Electrical Characteristics**  $T_C = +25^\circ\text{C}$ , Unless Otherwise Specified

CHARACTERISTIC	SYMBOL	TEST CONDITIONS	LIMITS			UNITS	
			MIN	TYP	MAX		
Drain-Source Breakdown Voltage IRFP140R, IRFP142R IRFP141R, IRFP143R	BV <sub>DSS</sub>	$V_{GS} = 0V, I_D = 250\mu A$	100	-	-	V	
			80	-	-	V	
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{DS} = V_{GS}, I_D = 250\mu A$	2.0	-	4.0	V	
Gate-Source Leakage Forward	I <sub>GSS</sub>	$V_{GS} = 20V$	-	-	100	nA	
Gate-Source Leakage Reverse	I <sub>GSS</sub>	$V_{GS} = -20V$	-	-	-100	nA	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS} = \text{Max Rating}, V_{GS} = 0V$	-	-	250	$\mu A$	
		$V_{DS} = \text{Max Rating} \times 0.8, V_{GS} = 0V, T_J = +125^\circ\text{C}$	-	-	1000	$\mu A$	
On-State Drain Current (Note 2) IRFP140R, IRFP141R IRFP142R, IRFP143R	I <sub>D(ON)</sub>	$V_{DS} > I_{D(ON)} \times r_{DS(ON)} \text{ Max}, V_{GS} = 10V$	31	-	-	A	
			27	-	-	A	
Static Drain-Source On-State Resistance (Note 2) IRFP140R, IRFP141R IRFP142R, IRFP143R	r <sub>DS(ON)</sub>	$V_{GS} = 10V, I_D = 19A$	-	0.055	0.077	$\Omega$	
			-	0.077	0.099	$\Omega$	
Forward Transconductance (Note 2)	g <sub>fs</sub>	$V_{DS} \geq 50V, I_D = 19A$	9.3	14	-	S(f)	
Input Capacitance	C <sub>ISS</sub>	$V_{GS} = 0V, V_{DS} = 25V, f = 1.0\text{MHz}$ See Figure 10	-	1275	-	pF	
Output Capacitance	C <sub>OSS</sub>		-	550	-	pF	
Reverse Transfer Capacitance	C <sub>RSS</sub>		-	160	-	pF	
Turn-On Delay Time	t <sub>d(ON)</sub>	$V_{DD} = 50V, I_D \approx 28A, R_G = 9.1\Omega, R_D = 1.8\Omega$ See Figure 16. (MOSFET switching times are essentially independent of operating temperature)	-	15	23	ns	
Rise Time	t <sub>r</sub>		-	72	110	ns	
Turn-Off Delay Time	t <sub>d(OFF)</sub>		-	40	60	ns	
Fall Time	t <sub>f</sub>		-	50	75	ns	
Total Gate Charge (Gate-Source + Gate-Drain)	Q <sub>g</sub>		$V_{GS} = 10V, I_D = 34A, V_{DS} = 0.8 \text{ Max Rating}$ . See Figure 17 for test circuit. (Gate charge is essentially independent of operating temperature.)	-	38	59	nC
Gate-Source Charge	Q <sub>gs</sub>		-	10	-	nC	
Gate-Drain ("Miller") Charge	Q <sub>gd</sub>		-	21	-	nC	
Internal Drain Inductance	L <sub>D</sub>	Measured between the contact screw on header that is closer to source and gate pins and center of die.		-	5.0	-	nH
Internal Source Inductance	L <sub>S</sub>	Measured from the source lead, 6mm (0.25") from header and source bonding pad.		-	12.5	-	nH
Junction-to-Case	R <sub>θJC</sub>		-	-	0.83	$^\circ\text{C/W}$	
Case-to-Sink	R <sub>θCS</sub>	Mounting surface flat, smooth and greased	-	0.1	-	$^\circ\text{C/W}$	
Junction-to-Ambient	R <sub>θJA</sub>	Free air operation	-	-	30	$^\circ\text{C/W}$	

## Source Drain Diode Ratings and Characteristics

Continuous Source Current (Body Diode)	I <sub>S</sub>	Modified MOSFET symbol showing the integral reverse P-N junc. rectifier.	-	-	31	A
Pulse Source Current (Body Diode) (Note 3)	I <sub>SM</sub>		-	-	120	A
Diode Forward Voltage (Note 2)	V <sub>SD</sub>	$T_J = +25^\circ\text{C}, I_S = 31A, V_{GS} = 0V$	-	-	2.5	V
Reverse Recovery Time	t <sub>rr</sub>	$T_J = +25^\circ\text{C}, I_F = 28A, dI_F/dt = 100A/\mu s$	70	150	300	ns
Reverse Recovered Charge	Q <sub>RR</sub>	$T_J = +25^\circ\text{C}, I_F = 28A, dI_F/dt = 100A/\mu s$	0.44	0.91	1.9	$\mu\text{C}$
Forward Turn-on Time	t <sub>ON</sub>	Intrinsic turn-on time is negligible. Turn-on speed is substantially controlled by L <sub>S</sub> + L <sub>D</sub> .	-	-	-	-

NOTES: 1.  $T_J = +25^\circ\text{C}$  to  $+150^\circ\text{C}$

2. Pulse Test: Pulse width  $\leq 300\mu s$ , Duty Cycle  $\leq 2\%$


3. Repetitive Rating: Pulse width limited by max. junction temperature. See Transient Thermal Impedance Curve (Figure 5)

4.  $V_{DD} = 25V$ , Start  $T_J = +25^\circ\text{C}$ ,  $L = 160\mu H$ ,  $R_G = 50\Omega$ ,  $I_{PEAK} = 31A$ . (See Figures 14 & 15)


4

N-CHANNEL  
POWER MOSFETS


**IRFP140R, IRFP141R, IRFP142R, IRFP143R**




**FIGURE 1. TYPICAL OUTPUT CHARACTERISTICS**




**FIGURE 2. TYPICAL TRANSFER CHARACTERISTICS**



**FIGURE 3. TYPICAL SATURATION CHARACTERISTICS**



**FIGURE 4. MAXIMUM SAFE OPERATING AREA**



**FIGURE 5. MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs PULSE DURATION**

IRFP140R, IRFP141R, IRFP142R, IRFP143R




FIGURE 6. TYPICAL TRANSCONDUCTANCE vs DRAIN CURRENT




FIGURE 7. TYPICAL SOURCE-DRAIN DIODE FORWARD VOLTAGE




FIGURE 8. BREAKDOWN VOLTAGE vs TEMPERATURE




FIGURE 9. NORMALIZED ON-RESISTANCE vs TEMPERATURE




FIGURE 10. TYPICAL CAPACITANCE vs DRAIN-TO-SOURCE VOLTAGE






FIGURE 11. TYPICAL GATE CHARGE vs GATE-TO-SOURCE VOLTAGE

4  
N-CHANNEL  
POWER MOSFETs


**IRFP140R, IRFP141R, IRFP142R, IRFP143R**




**FIGURE 12. TYPICAL ON-RESISTANCE VS DRAIN CURRENT**




**FIGURE 13. MAXIMUM DRAIN CURRENT VS CASE TEMPERATURE**




**FIGURE 14. UNCLAMPED ENERGY TEST CIRCUIT**



**FIGURE 15. UNCLAMPED ENERGY WAVEFORMS**



**FIGURE 16. SWITCHING TIME TEST CIRCUIT**



**FIGURE 17. GATE CHARGE TEST CIRCUIT**