

Antenna YFGA001AA Datasheet

Antenna Services

Version: 2.1

Date: 2021-06-25

Status: Released



Our aim is to provide customers with timely and comprehensive service. For any assistance, please contact our company headquarters:

Quectel Wireless Solutions Co., Ltd.

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233, China

Tel: +86 21 5108 6236 Email: info@quectel.com

Or our local office. For more information, please visit:

http://www.quectel.com/support/sales.htm.

For technical support, or to report documentation errors, please visit:

http://www.quectel.com/support/technical.htm

Or email to support@quectel.com.

General Notes

Quectel offers the information as a service to its customers. The information provided is based upon customers' requirements. Quectel makes every effort to ensure the quality of the information it makes available. Quectel does not make any warranty as to the information contained herein, and does not accept any liability for any injury, loss or damage of any kind incurred by use of or reliance upon the information. All information supplied herein is subject to change without prior notice.

Disclaimer

While Quectel has made efforts to ensure that the functions and features under development are free from errors, it is possible that these functions and features could contain errors, inaccuracies and omissions. Unless otherwise provided by valid agreement, Quectel makes no warranties of any kind, implied or express, with respect to the use of features and functions under development. To the maximum extent permitted by law, Quectel excludes all liability for any loss or damage suffered in connection with the use of the functions and features under development, regardless of whether such loss or damage may have been foreseeable.

Duty of Confidentiality

The Receiving Party shall keep confidential all documentation and information provided by Quectel, except when the specific permission has been granted by Quectel. The Receiving Party shall not access or use Quectel's documentation and information for any purpose except as expressly provided herein. Furthermore, the Receiving Party shall not disclose any of the Quectel's documentation and information to any third party without the prior written consent by Quectel. For any noncompliance to the above requirements, unauthorized use, or other illegal or malicious use of the documentation and information, Quectel will reserve the right to take legal action.

Antenna_Datasheet 1 / 15



Copyright

The information contained here is proprietary technical information of Quectel. Transmitting, reproducing, disseminating and editing this document as well as using the content without permission are forbidden. Offenders will be held liable for payment of damages. All rights are reserved in the event of a patent grant or registration of a utility model or design.

Copyright © Quectel Wireless Solutions Co., Ltd. 2021. All rights reserved.

Antenna_Datasheet 2 / 15



About the Document

Revision History

Version	Date	Author	Note
-	2021-05-25	Kenny YIN/ Aria CHU	Creation of the document
1.0	2021-05-25	Kenny YIN/ Aria CHU	First official release
2.0	2021-06-17	Aria CHU	Updated all test data in this datasheet.
2.1	2021-06-25	Aria CHU	Updated the antenna picture in Chapter 2.

Antenna_Datasheet 3 / 15



Contents

Ab	out the Doci	ument	3
Co	ntents		4
1	Product De	escription	5
2	Product Fe	eatures	5
3	Product Sp	pecifications	6
4	Overall Per	rformance	7
	4.1. Test	Environment	7
	4.2. VSW	VR	8
		iency	
		٠ ٦	
		iation Pattern	
	4.5.1.	1175 MHz	11
	4.5.2.	1227 MHz	
	4.5.3.	1278 MHz	
	4.5.4.	1560 MHz	
	4.5.5.	1575 MHz	13
	4.5.6.	1602 MHz	
5	Product Si	ize	15



1 Product Description

The antenna is designed for superior performance, and can be widely used for wireless applications.

We provide comprehensive antenna design support such as simulation, testing and manufacturing for custom antenna solutions to meet your specific application needs.

2 Product Features

- GPS L1/L2/L5/L6
- High efficiency
- Excellent performance



Antenna_Datasheet 5 / 15



3 Product Specifications

Passive Electrical Specifications					
Frequency Range	1160–1270 MHz; 1560–1605 MHz				
Input Impendence	50 Ω				
VSWR	≤ 2.0				
Gain	≤ 3.6 dBi				
Polarization Type	Linear				
Mechanical Specifications					
Antenna Size	74.56 mm × 24.5 mm				
Casing	FPC				
Connector Type	IPEX MHF I				
Working Temperature	-40 °C to +85 °C				
Radome Color	Black				

Antenna_Datasheet 6 / 15



4 Overall Performance

4.1. Test Environment


- KEYSIGHT VNA Network Analyzer E5063A 100 kHz 8.5 GHz
- RayZone® 2800 Chamber 5G (FR1) SISO/MIMO, 400 MHz 8.0 GHz



Antenna_Datasheet 7 / 15



4.2. **VSWR**




Frequency (MHz)	1176	1227	1278	1561	1575	1602
VSWR	1.91	1.45	1.24	2.04	1.63	1.35

Antenna_Datasheet 8 / 15



4.3. Efficiency




Frequency (MHz)	1175	1225	1280	1560	1575	1602
Efficiency (%)	69.5	73.2	66.2	54.8	56	60

Antenna_Datasheet 9 / 15



4.4. Gain




Frequency (MHz)	1175	1225	1280	1560	1575	1602
Gain (dBi)	2.65	3.34	2.8	1.75	1.85	1.95


Antenna_Datasheet 10 / 15




4.5. Radiation Pattern



4.5.1. 1175 MHz








Antenna_Datasheet 11 / 15




4.5.2. 1227 MHz













4.5.3. 1278 MHz












Antenna_Datasheet 12 / 15




4.5.4. 1560 MHz













4.5.5. 1575 MHz












Antenna_Datasheet 13 / 15




4.5.6. 1602 MHz











Antenna_Datasheet 14 / 15



5 Product Size





Antenna_Datasheet 15 / 15