

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Rectangular Connectors: 6-Way Shielded Plug

Connector Product Type: **Connector Assembly**Connector & Housing Type: **Plug**Mating Alignment: **With**Mating Alignment Type: **Keyed**Mating Retention: **With**[All Rectangular Connectors: 6-Way Shielded Plug \(2\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Triple-Seal
Connector Shell Size	06
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Insertion Force Type	Normal
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Cavities	6
Contacts Preloaded	Yes
Number of Power Positions	6
Number of Columns	3
Number of Signal Positions	6
Number of Positions	6
Number of Rows	2

Electrical Characteristics

Operating Voltage	400 VAC
-------------------	---------

Body Features

Connector Seal Color	Natural
Seal Type	Grommet Seal, Interfacial Seal
Cable Exit Angle	180°
Shell Plating Material	Nickel
Seal Material	Fluorosilicone
Connector & Keying Code	N

Contact Features

Contact Size	Size 22
Contact Type	Pin
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Button Latch

Housing Features

Shell Material	Composite
Housing Material	Composite
Housing Color	Black
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Compatible Insulation Diameter Range	.71 – 1.37 mm[.028 – .054 in]

Usage Conditions

Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Shielded

Yes

Circuit Application

Power & Signal

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # YD369-MR66-NS00000
369 6 WAY SHIELDED REC, NO
CONTACTS,SKT

Also in the Series | [DEUTSCH 369 Shielded Connector](#)



Standard Rectangular Connectors(15)

Customers Also Bought

TE Part #1-2823447-1
M12 A-M-8 CRIMP ST ,CAT7 RADOX
8.2MM,H&STE Part #205205-7
CRIMP SNAP RCPT ASSY,SIZE 2TE Part #205206-9
CRIMP SNAP PLUG ASSY,SIZE 2TE Part #794942-1
10P MINI UMNL CAP HSGTE Part #1-770987-0
MINI UMNL PIN 22-18 AWG AU LPTE Part #90759-2
PROCRIMP DIE MINI UNIV MNLTE Part #3-2213766-9
AV19 SPL 5A POWER LED BLUE 24VTE Part #YDTS26W15-35SNV001
PLUG ASSYTE Part #321298
TERMINAL,SOLIS R 6 10TE Part #2176467-1
TLRP 1206 1.0W R008 1% 50PPM 5K RL

Documents

Product Drawings

[369 6 WAY SHIELDED PLUG, NO CONTACTS,PIN](#)

English