


PICTURE



DIMENSIONS



Drawings not to scale
 All dimensions in mm nominal

DETAILS

Weather resistant white Polycarbonate housing

92Db at 1 metre.

Anti tamper switch.

Strong Mylar cone.

Left, Right and bottom wire entry points .

Grade 3.

Features Include

- 92Db sound level.
- Durable Mylar cone.
- Sturdy Polycarbonate construction resists weathering.
- Tamper switch protection.

Specifications

- Environmental class 2.
- Grade 3.
- Tamper switch for cover.
- 16Ohm resistance.
- Quick clip cover, no screws.

Did you know we also sell?



Rev. No.

Revision Note

Date

Signature

1

Datasheet

18-09-15

ML



ISO 9001:2008
 Certificate No. FM21080

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone : +44 (0)1255 862236

www.comus-intl.com

Fax: +44 (0)1255 862014