

[Sensors > Pressure Sensors > Media Isolated Pressure Sensors > 19MM MV OUTPUT PRESSURE SENSOR](#)

Pressure: [ 30 psi ]

Media Isolated Pressure Sensor Type: **Media Isolated mV Output Pressure Sensors**Media Isolated Pressure Sensor Style: **Gauge**Output/Span: **100mV**Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**[All 19MM MV OUTPUT PRESSURE SENSOR \(38\)](#)

## Features

### Product Type Features

Media Isolated Pressure Sensor Type

Media Isolated mV Output Pressure Sensors

Media Isolated Pressure Sensor Style

Gauge

### Configuration Features

Electrical Connection

Ribbon Cable

### Electrical Characteristics

Supply Current

1.5 mA

### Dimensions

Dimensions

Dia 18.97 x 13.8 mm [Dia .746 x .54 in]

### Usage Conditions

Operating Temperature Range

-40 – 125 °C [ -40 – 257 °F ]

### Operation/Application

Proof Pressure Range

3X

30 psi

Output/Span

100mV

### Packaging Features

## Media Isolated Pressure Sensor Package

## O-Ring Mount

## Other

Non-Linearity	± .1 %
Sensor Options	No Tube

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (1% in Component a) <small>Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



## Compatible Parts



## Also in the Series | MEAS 154 Series



## Customers Also Bought



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_154N-030G-R\\_F1.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_154N-030G-R\\_F1.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_154N-030G-R\\_F1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### 154NC

English