



Terminals & Splices > Automotive Terminals



Terminal Type: **Receptacle**
Mating Tab Width: **.8 mm [.031 in]**
Mating Tab Thickness: **.64 mm [.025 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **18 AWG**

Features

Product Type Features

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Clean Body

Body Features

Terminal Seal Type	Family Seal
--------------------	-------------

Contact Features

Contact Size	.64mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	10 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	.8 mm[.031 in]
Mating Tab Thickness	.64 mm[.025 in]



Interface Plating	Silver (Ag)
-------------------	-------------

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.6 – 2.06 mm [.063 – .081 in]
Wire Size	.82 mm²
Wire Size Search	18 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F]
Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	SAE/USCAR-2 / USCAR-21
---	------------------------

Packaging Features

Packaging Quantity	7500
Packaging Method	Reel

Other

Customer Preferred Contact	Yes
Terminal Transmits	0 – 24 A (Low Power)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2035363-4
1X6 GENERATION Y ASSY KEYC CPA



TE Part # 3-1579007-6
GET EXTRACTION TOOL



TE Part # 2063291-1
PRO-C HT & DIE GEN Y



TE Part # 2063291-2
DIE GEN Y



TE Part # 2112857-1
3POS,0.64 GENER. Y,REC HSG,ASS

Also in the Series | Generation Y Connector System



Automotive Connector Caps & Covers
(16)



Automotive Housings(128)



Automotive Terminals(39)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(15)

Customers Also Bought



TE Part #2-1670916-1
2POS, MCON 1.2 LL REC SEALED



TE Part #184032-1
3 POS. PLUG ASSY, KEY A



TE Part #2-2138650-1
2POS MQS REC COD B



TE Part #1924879-2
GET, FEM TERM, AG, THIN, B-CRI



TE Part #4-1488991-1
3POS, MCON 1.2 CB REC 2p TL SEALED




TE Part #1587042-1
34P MALE CAP ASSY-KEY A




TE Part #2373227-1
CVTY PLUG,0.64 GENER. Y,CVTY DIA, MAT-SL



TE Part #1-1456570-3
SUB-ASSY,PLUG,2.8/6.3,38 WAY,ABS



TE Part #2-2035383-7
GET PCM 70 WAY Plug ASSY Key D



TE Part #638182-1
WIRE SHIELD 16 POSN TRANS.

Documents



Product Drawings

CONTACT,FEMALE, 0.64, 18 AWG, AG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1456968-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1456968-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1456968-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English