



Connectors > Automotive Connectors > Automotive Housings > AMP MCP, SEALED CONNECTOR HOUSING



Connector System: **Wire-to-Board, Wire-to-Device**
Number of Positions: **1**
Connector & Housing Type: **Housing for Female Terminals**
Sealable: **Yes**
Mating Tab Width: **2.8 mm [.11 in]**

[All AMP MCP, SEALED CONNECTOR HOUSING \(161\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector System	Wire-to-Board, Wire-to-Device
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	1
Number of Rows	1

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Size	2.8mm
Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]

Mechanical Attachment

--



Terminal Position Assurance	Yes
Strain Relief	Without
Mating Alignment Type	Polarized
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
------------------	-------

Dimensions

Connector Height	33 mm[1.299 in]
Product Width	24 mm[.945 in]
Product Length	22.6 mm[.89 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C, 145 °C, 150 °C, 155 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F][293 °F][302 °F][311 °F]
Operating Temperature Range	-40 – 155 °C

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP69K
----------------------	-------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB

Also in the Series | AMP MCP 2.8

Automotive Connector Caps & Covers (1)	Automotive Connector Locks & Position Assurance(5)	Automotive Housings(167)	Automotive Terminals(9)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(6)




Module Components(1)




PCB Headers & Receptacles(1)


Also in the Series | AMP MCP Connector System




Automotive Connector Caps & Covers (22)




Automotive Connector Locks & Position Assurance(6)




Automotive Housings(332)




Automotive Terminals(130)



Connector Seals & Cavity Plugs(7)



Insertion & Extraction Tools(13)



Other Automotive Connector Accessories(2)



PCB Headers & Receptacles(28)

Customers Also Bought



TE Part #1-1718624-2
2 POS HSG AMP MCP 2.8 ASSY



TE Part #2272164-1
MCON WIRE DRESS, 3P, STRAIGHT



TE Part #2272163-1
MCON WIRE DRESS, 4P, RIGHT ANGLE



TE Part #2310000-1
10POS,MQS,REC HSG ASSY,UNSLD, COD A



TE Part #2310399-1
REC CONN CVR,4POS,MCON 9.5



TE Part #2317368-1
2P MCON 9.5 PLUG ASSEMBLY, KEY A



TE Part #2317373-1
2P MCON 9.5 CAP HOUSING, KEY A



TE Part #2322231-5
40POS,HYBRID,REC HSG ASSY,SLD, COD A



Documents

Product Drawings

Plug Assembly, Sealed, 1 Posn,

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2098198-5_C_c-2098198-5-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2098198-5_C_c-2098198-5-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2098198-5_C_c-2098198-5-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English