





WiFi Antennas 2.4/5.8G FPC Antenna

The PCB & FPC WiFi antenna range offers customers a reliable and easy drop in solution for integrated WiFi communications.

The Antennas can be customized to your specifications for cable length and connector type. Bel has diverse communications experience of over 20 years and can also provide a fully integrated design solution, utilizing our portfolio of products.

Antennas come with an easy peel adhesive making it a simple solution for mounting to a case or existing PCB.

Key Features & Benefits

- 42 x 12 mm Antenna
- Connector types can be customized
- Cable lengths can be customized
- Ideal for Industrial applications
- 50 Ω Impedance
- 10 N of pull force
- Easy connection to existing PCBs
- Adhesive provides easy case mounting
- Provides robust reliability



Bel Modules 28 Turkey Court, Turkey Mill, Ashford Road Maidstone ME14 5PP UK

[1]

+44 1622 757 395 modulestechhelp@belf.com

belfuse.com

© 2020 Bel Power Solutions, Inc.

Rev A

WiFi Antennas

2.4 GHz / 5.8 GHz FPC Antenna

MODELS

PART NUMBER	TEMP RANGE	CONNECTION	MARKET
0804-WFAN-F2	-40 °C to +85 °C	IPEX (Customizable)	Worldwide

ELECTRICAL CHARACTERISTICS

SERIES OF MEASURE	VALUES
Fraguancy	2400 – 2500 MHz
Frequency	5000 – 5800 MHz
V C M D	2400 – 2483.5 MHz < 1.9
V.S.W.R	4900 – 5800 MHz < 1.9
Antenna Gain	2400 – 2483.5 MHz 2.0 ± 1.7 dBi
	4900 – 5800 MHz 2.0 ± 1.7 dBi
Polarization	Vertical
Impedance	50 Ω

MATERIAL & MECHANICAL INFORMATION

ITEM	DESCRIPTION
Material of Radiator	Copper
Connect Type	IPEX-Male
Weight	0.6 g

ENVIRONMENTAL

ITEM	DESCRIPTION
Operational Temperature	-40 °C to +80 °C
Storage Temperature	-40 °C to +85 °C

GAINS & EFFICIENCY

FREQUENCY	E TOTAL. dB	EFFICIENCY %
2400 MHz	1.85	73
2440 MHz	2.19	75
2483.5 MHz	2.02	71
4900 MHz	4.80	68
5400 MHz	4.33	63
5875 MHz	4.33	62



WiFi Antennas

2.4 GHz / 5.8 GHz FPC Antenna

MECHANICAL



