

Feb. 1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△ 1	RE-6-0909	LYJ	JHW	17.16.15	△ 1	RE-6-1554	PSG	JHW	19.10.07
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55℃ TO +85℃(note1)			STORAGE TEMPERATURE RANGE	-10℃ TO +60℃			
	VOLTAGE	30 V AC/DC			APPLICABLE CONNECTOR △	BM23PF0.8-20DP-0.35V(**)			
	CURRENT	△	SIGNAL CONTACT 0.3A POWER CONTACT 5.0A						
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			X	X
MARKING		CONFIRMED VISUALLY.						X	X
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		20mV AC OR LESS 1kHz, 1mA			SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX			X	-
INSULATION RESISTANCE		100V DC			50MΩ MIN			X	-
VOLTAGE PROOF		100V AC FOR 1min.			NO FLASHOVER OR BREAKDOWN			X	-
MECHANICAL CHARACTERISTICS									
MECHANICAL OPERATION		10 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.			X	-
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SHOCK		490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)			① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2℃, 90 TO 95%, 96h.			① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)			① CONTACT RESISTANCE: SIGNAL CONTACT : 90mΩ MAX POWER CONTACT : 30mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-
REFERENCE DRAWING									
REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT. Unless otherwise specified, refer to JIS C 5402 and IEC 60512				DRAWN S.H.JUNG 16.01.06	DESIGNED S.H.JUNG 16.01.06	CHECKED H.W.JO 16.01.06	APPROVED T.S.KANG 16.01.06	RELEASED ENG 17.10.07 DEPT	
Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST									
HIROSE KOREA CO.,LTD.				SPECIFICATION SHEET			PART NO. BM23PF0.8-20DS-0.35V(51)		
CODE NO.(OLD) CL		DRAWING NO. ELC4-632053-51		CODE NO. CL 6644-0061-9-051				1 1	