

### product type designation



### Antenna ANT795-6MP

ANT795-6MP WLAN antenna with omnidirectional characteristic incl. N-female connector: 5/7 dBi; IP65/67 (-40 - +80 °C); 2.4/5 GHz Wi-Fi compliance and national approvals to be observed; Mounting on wall or mast; compact instructions in German/English Scope of delivery: 1x ANT795-6MP, 1 x mounting aid

radio frequencies	
type of wireless network / is supported	WLAN
operating frequency	2.4 ... 2.5 GHz
<ul style="list-style-type: none"> <li>for WLAN in 2.4 GHz frequency band</li> <li>for WLAN in 5 GHz frequency band 1</li> </ul>	4.94 ... 5.925 GHz
electrical data	
impedance	50 Ω
polarization	linear vertical
radiation characteristic	omnidirectional
antenna gain compared to spherical radiator	5 dB
<ul style="list-style-type: none"> <li>of the WLAN antenna / in the 2.4 GHz frequency band</li> <li>of the WLAN antenna / in the 5 GHz frequency band</li> </ul>	7 dB
standing wave ratio (VSWR) / maximum	2
radiating angle of the antenna	360°
<ul style="list-style-type: none"> <li>in the 2.4 GHz frequency band / horizontal</li> <li>in the 2.4 GHz frequency band / vertical</li> <li>in the 5 GHz frequency band / horizontal</li> <li>in the 5 GHz frequency band / vertical</li> </ul>	25° 360° 15°; take the antenna diagram into account regarding the horizontal beam angle
number of electrical connections / of the antenna	1
type of electrical connection / of the antenna	N-Connector
design of plug-in connection	female
angle of inclination / downward / maximum	0°
mechanical data	
material	UV-resistant white plastic
<ul style="list-style-type: none"> <li>of outer shell</li> </ul>	
ambient conditions	
ambient temperature	-40 ... +80 °C
<ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> <li>during transport</li> </ul>	-40 ... +80 °C -40 ... +80 °C -40 ... +80 °C
protection class IP	IP65 / 67
wind load / maximum	19.6 N
resistance to salt-laden atmosphere / conformity acc. to EN 60068-2-52	Yes; Severity 1
design, dimensions and weights	

width	97 mm
height	367 mm; incl. bracket
depth	64 mm
diameter	28.6 mm
net weight	300 g
fastening method	
• mast mounting	Yes
• wall mounting	Yes
• roof mounting	No
• directly on the device	No
<b>product features, product functions, product components / general</b>	
product feature / silicon-free	Yes
<b>standards, specifications, approvals</b>	
certificate of suitability	
• RoHS conformity	Yes
product conformity	UL 94-HB
wireless approval	Current national approvals can be found on the Internet under <a href="http://www.siemens.com/funkzulassungen">www.siemens.com/funkzulassungen</a>
<b>further information / internet-Links</b>	
Internet-Link	
• to web page: selection aid TIA Selection Tool	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
• to website: Industrial communication	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>last modified:</b>	12/16/2020 