

Flavus GSM Snap-In Antenna

Product Specification

1 Features

- Designed for GSM applications [800/900/1800/1900 MHz]
- · Intended for Snap-In mounting
- · Supplied in trays

2 Description

The Flavus antenna is intended for use with all GSM applications. The antenna is a quarterwave type. The antenna uses plastic snap ins to attach to the PCB, no need for soldering.

3 Application

- · GSM modules
- · Cell phones
- · Vehicle tracking



Flavus GSM Snap-In Antenna




Contents

1 Features	1
2 Description	1
3 Application	1
4 Model name	3
5 General data	3
6 Electrical characteristics	3
7 Electrical performance	4
7.1 Voltage Standing Wave Ratio	4
7.2 Radiation patterns	4
8 Antenna Dimensions	5
9 Antenna Footprint	5
10 Electrical interface	6
10.1 Transmission line and matching	6
10.2 Test board dimensions	6
10.3 Test board matching	7
11 Reliability	7
11.1 Temperature and Humidity	7
11.2 Mechanical	7
11.3 Miscellaneous	8
11.4 Judgement standard	8
12 Hazardous Material Regulation Conformance	8
13 Application example	9
14 Packaging	10
14.1 Shelf storage recommendation	10
14.2 Packaging characteristics	10
14.3 Tray dimension	10
14.4 Box dimension	10
14.5 Label information	10



4 Model name



5 General data

Product Name	Flavus GSM
Article No.	1020B5812-0105
Frequency	880-960 MHz, 1710-1990 MHz
Polarization	Linear
Operating temperature	-40 to + 85 degC
Impedance	50 Ohm
Weight	0.6 gram
Antenna type	Snap-in

6 Electrical characteristics


	С	haracteristic	s	Conditions*
	GSM	DCS	PCS	Conditions
Efficiency	> 65%	> 68 %	> 77%	Measured in 3D chamber (near field)
VSWR	< 1:2.3	< 1:2.7	< 1:1.9	Measured in Network Analyzer

^{*}Note all data provided in this table are based on the Antenova reference board




7 Electrical performance

7.1 Voltage Standing Wave Ratio




7.2 Radiation patterns






8 Antenna Dimensions



L	W	W1	W2	Н	H1	F1	F2	T1	T2	Т3
Length	Width	Width	Width	Height	Height	Feed	Feed	PCB		
27.3 ±0.2	7.9 ±0.2	9.6±0.2	8.5±0.2	3.45±0.1	3.85±0.1	11.85±0.2	2.8±0.1	T1±0.05	1.35±0.2	1.3±0.1

Dimensions in millimeters

9 Antenna Footprint




F1	F2	F3	F4	S1	P1	P2	P3	P4	D1	D2	T*
Feed	Feed	Feed	Feed	Snap-In	Position	Position	Position	Position	Diameter	Diameter	PCB
11.85±0.1	2.8±0.1	2±0.05	2.25±0.05	5.6±0.1	4.5±0.1	11.5±0.1	0.3±0.1	5.9±0.1	3.05±0.1	1.75±0.1	0.8, 1.0, 1.2, 1.6, 1.8

Dimensions in millimeters




10 Electrical interface

10.1 Transmission line and matching




The matching network has to be individually designed using one, two or three components.



t, w = Unique dimensioning according to your PCB *

C = Inductor and capacitor values according to your specific device*

10.2 Test board dimensions




The testboard is designed for evaluation purposes for Flavus GSM antenna. The card has the same size as a typical PCMCIA card and is fitted with an SMA connector.

^{*} Antenova provides this service upon request



10.3 Test board matching



The testboard is matched with above specified component.

Note! The component value(s) will vary depending on size of PCB, surrounding components etc.

11 Reliability

11.1 Temperature and Humidity

Item	Standard	Low	High	Duration
Operating temperature	EN/IEC 60068-2-2, Test Bd: Dry heat	-30 degC	+90 degC	-
Temperature cycling	EN/IEC 60068-2-14, Test Na: Change of temperature	-30 degC	+90 degC	100cycles / 10min
Storage life Humidity	EN/IEC 60068-2-1, Test Ca: Damp heat	+40 degC	/ 93% RH	96 h
Storage life Low temperature	EN/IEC 60068-2-1, Test Ad: Cold	-25 degC	-	200 h
Storage life High temperature	EN/IEC 60068-2-2, Test Bb: Dry heat	-	+ 90 degC	1000 h

11.2 Mechanical

Item	Standard	Specification	Duration
Contact force		Antenna is mounted on reference board. and a pressure gauge is applied to antenna contact.	
Drop test		Dummy weight: 150g Height: 170cm	One drop at each side, total drops: 6
Vibration	EN/IEC 60068-2-6, Test Fc (sinusoidal)	Acceleration spectral density:10-1000Hz Acceleration: 20m/s2 Number of axes: 3 mutually perpendicular	5 cycles per axis



11.3 Miscellaneous

Item	Standard	Standard Specification		Duration
Contact pad Corrosion	ASTM B117	SO2 Concentration: Temperature : RH:	25 ppm 25 Deg C 93%	96 hours

11.4 Judgement standard

The judgement of the above tests should be made as follows:

- 1. Visual inspection Normal appearance with no obvious deformation
- 2. Electrical inspection The antenna satisfies the VSWR specification throughout the GSM band
- 3. Mechanical inspection Acceptable contact force min. 0.5 N

12 Hazardous Material Regulation Conformance

Cadmium and cadmium compound.

Lead and lead compound

Organic brominated compound (PBB, PBDE)

Mercury and mercury compound

Polychlorinated biphenyl (PCB) Sexivalent chrome compound

Polychlorinated naphthalene (PCN) Chlorinated paraffin (CP)


Organic tin compound Mirex


Asbestos Formaldehyde

Azo compound Tetra-bromo-bisphenol-A-bis (TBBP-A-bis)



13 Application example





1. Placement of antenna

The antenna shall preferably be placed at the edge of the PCB oriented as above. Other placements and orientations and size of groundplanes are possible, but will affect the performance. Avoid active components near the antenna.

2. Placement of GSM module or radio

To avoid losses the module shall be placed as close to the antenna as possible.

3. Strip line

The strip line must be dimensioned according to your specific PCB. (see Fig 1). No crossing strip lines are allowed between the strip line and its ground plane.

4. Via connections

To avoid spurious effects, via connections must be made to analogue ground.

5. Component matching

Component values are depending on antenna placement, PCB dimensions and location of other components.

6. DC Block

Might be needed depending on RF Module configuration.

7. Clearance area

Avoid components and parts close to the antenna.

8. Alternate positioning

The Flavus GSM antenna can placed horisontally to the groundplane, but this position is less favourable then the recommended vertical placement, and will cause a decrease in performance.

Note! Incorrect implementation of the antenna will affect the performance.

Contact Antenova for implementation services.



14 Packaging

14.1 Shelf storage recommendation

Temperature	-10 to +40 degree C
Humidity	Less than 75% RH
Shelf Life	12 Months
Storage place	Away from corrosive gas and direct sunlight


14.2 Packaging characteristics

Quantity	Number of trays	Tray quantity
840 pcs / box	6 / box	140 pcs

14.3 Tray dimension


Material: Anti static plastic tray

Width [mm] W: 290
Breadth [mm] B: 390
Height [mm] H: 14



14.4 Box dimension

Material: Paper
Width [mm] W: 296
Breadth [mm] B: 396
Height [mm] H: 75



14.5 Label information

antenova

Antenova Article number : XXXXAXXXX-XX
Description : Product name, Frequenzy Hz
Reel Quantity : XXXX Pcs.
Order No: Customer PO number
Date: YYMMDD



www.antenova.com

Corporate Headquarters

Antenova Ltd.

Far Field House Albert Road Stow-cum-Quy Cambridge CB9 5AR

Tel: +44 (0) 1223 810600 Fax: +44 (0) 1223 810650 Email: info@antenova.com

Asia Headquarters

Antenova Asia Ltd.

3F, No 10, Alley 6, Lane 45 Poa Shing Road Hsin Tien City Taipe County ROC 23145

Tel: +886 (0) 2 2917 6536 Fax: +886 (0) 2 2910 6546 Email: info@antenova.com

Sales Offices

Europe

Charlotta Olander

UK/EU Sales Manager

Tel: +46 702 913731

America

David Nuti

NA Sales Manager

Tel: +1 214 668 0357

Email: Lotta.Olander@antenova.com Email: David.Nuti@antenova.com

Asia

CL Lim

VP Sales Asia

Tel: +886 (0) 931 201 318 Email: CL.Lim@antenova.com



Certificate No: 4598/04