


SCHOTTKY BARRIER DIODE
FEATURES

- Small Surface Mount device
- Low power loss, high efficiency
- High temperature soldering guaranteed: 260°C/10 seconds at terminals
- Guard ring for over voltage protection
- For use in low voltage high frequency inverters, free wheeling, and polarity protection applications


SOD-123FL
MECHANICAL DATA







- Case: SOD-123FL
- Case Material: Molded Plastic. UL flammability
- Classification Rating: 94V-0
- Weight: 0.0155 grams (approximate)



MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Parameter	Symbol	SS32L	SS33L	SS34L	SS36L	SS38L	SS310L	SS312L	SS315L	SS320L	Unit
Repetitive peak reverse voltage	V _{RRM}	20	30	40	60	80	100	120	150	200	V
DC Reverse Voltage	V _R	20	30	40	60	80	100	120	150	200	V
RMS Reverse Voltage	V _{RMS}	14	21	28	42	56	70	100	105	140	V
Mean rectifying current	I _F	3.0									A
Non-Repetitive Peak Forward Surge Current @ t = 8.3 ms	I _{FSM}	80									A
Thermal Resistance	R _{θJA}	40									°C/W
Junction Temperature	T _J	-55~+125									°C
Storage Temperature	T _{STG}	-55 ~+150									°C


ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise specified)

Parameter	Symbol	SS32L	SS33L	SS34L	SS36L	SS38L	SS310L	SS312L	SS315L	SS320L	Unit	Conditions	
Forward voltage	V _F	0.55			0.70		0.85		0.95		V	I _F =3A	
Reverse current T=25°C	I _R	0.5			0.3							mA	V=V _R
Reverse current T=100°C	I _R	10			5							mA	
Junction capacitance	C _J	250			160							pF	V=4V,f=1MHz


SCHOTTKY BARRIER DIODE
Typical Characteristics
FIG.1 FORWARD CURRENT DERATING CURVE

FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT

FIG. 3 TYPICAL FORWARD CHARACTERISTICS

FIG. 4 TYPICAL REVERSE CHARACTERISTICS

FIG. 5 TYPICAL JUNCTION CAPACITANCE

FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE


SCHOTTKY BARRIER DIODE
SOD-123FL Package Outline Dimensions




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.75	0.95	0.029	0.037
B	1.60	2.00	0.063	0.079
C	2.60	3.00	0.103	0.119
D	0.90	1.20	0.036	0.047
E	0.12	0.22	0.005	0.009
F	0.8Typ		0.032Typ	
G	3.50	3.90	0.138	0.159

SOD-123FL Suggested Pad Layout

Note:

1. Controlling dimension: in millimeters
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purposes only

SCHOTTKY BARRIER DIODE
SOD-123FL Tape and Reel
SOD-123FL Embossed Carrier Tape


DIMENSIONS ARE IN MILLIMETER										
TYPE	A	B	C	d	E	F	P0	P	P1	W
SOD-123FL	2.10	4.00	1.25	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00
TOLERANCE	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1

SOD-123FL Tape Leader and Trailer

SOD-123FL Reel


DIMENSIONS ARE IN MILLIMETER								
REEL OPTION	D	D1	D2	G	H	I	W1	W2
7" DIA	Ø178	54.40	13.00	R78	R25.60	R6.50	9.50	12.30
TOLERANCE	±2	±1	±1	±1	±1	±1	±1	±1