




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Wire Size: **.05 – .15 mm²**

Features

Contact Features

Mating Tab Width	.64 mm[.025 in]
Mating Tab Thickness	.7 mm[.03 in]
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Base Material	Brass
Contact Current Rating (Max)	2 A

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Compatible Insulation Diameter Range	1 – 1.4 mm[.039 – .055 in]
Wire Size	.05 – .15 mm ²

Usage Conditions

Operating Temperature Range	-20 – 95 °C[-4 – 203 °F]
-----------------------------	--------------------------

Operation/Application

--



Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 172213-8
8P EI HSG PANEL-MOUNT



TE Part # 172211-4
EIS CAP HSG FREE HANG 4P NATUTURAL



TE Part # 172213-5
EIS CAP HSG PANEL MOUNT 5P NATUTURAL



TE Part # 172211-8
8P CAP HSG FREE HABG EI S CONN



 TE Part # 172213-3 EIS CAP HSG PANEL MOUNT 3P NATUTURAL	 TE Part # 172211-6 EIS CAP HSG FREE HANG 6P NATUTURAL	 TE Part # 172213-4 EIS CAP HSG PANEL MOUNT 4P NATUTURAL	 TE Part # 172213-2 EIS CAP HSG PANEL MOUNT 2P NATUTURAL
 TE Part # 172211-3 EIS CAP HSG FREE HANG 3P NATUTURAL	 TE Part # 172211-2 EIS CAP HSG FREE HANG 2P NATUTURAL	 TE Part # 1-172211-0 10P CAP HSG F/H EI S CONN.	 TE Part # 1-172211-2 12P CAP HSG F/H EI S CONN.
 TE Part # 172213-7 EIS CAP HSG PANEL MOUNT 7P NATUTURAL	 TE Part # 172211-5 EIS CAP HSG FREE HANG 5P NATUTURAL	 TE Part # 172213-6 EIS CAP HSG PANEL MOUNT 6P NATUTURAL	 TE Part # 91566-1 CCII EI SERIES PIN 26-20 ASSY
 TE Part # 724762-1 EI EXT TOOL	 TE Part # 172212-5 E.I. 5P CAP F.H.SONY TYPE	 TE Part # 172212-6 E.I. 6P CAP F.H.SONY TYPE	 TE Part # 172214-2 E.I. 2P CAP

Customers Also Bought

 TE Part #5749621-7 68 50S CABLE PLUG CONN/COV KIT	 TE Part #5750752-2 68 50SR BKSHLL KIT W/BOOT BULK	 TE Part #172211-4 EIS CAP HSG FREE HANG 4P NATUTURAL	 TE Part #171822-5 EIS REC. HSG 5P-NATURAL
--	---	---	--



TE Part #171826-2
2POS POST HEADER ASSY

TE Part #170204-1
EIS RECPT CONTACT

TE Part #1-171822-0
EIS REC. HSG 10P-NATURAL

TE Part #172211-3
EIS CAP HSG FREE HANG 3P
NATUTURAL

TE Part #171822-4
EIS REC. HSG 4P-NATURAL

TE Part #172211-2
EIS CAP HSG FREE HANG 2P
NATUTURAL

Documents

Product Drawings

EI PIN LP 170377-1 LP

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170430-1_C_c-170430-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170430-1_C_c-170430-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170430-1_C_c-170430-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773972-5_EIS_Connectors_Brochure

English

Product Specifications

Crimping of AMP EI Series Connector Contacts

Japanese

Application Specification

Japanese



Instruction Sheets

Instruction Sheet (non U.S.)

English

Extraction Tool For AMP EI Series Cap Housing

English

Instruction Sheet (non U.S.)

Japanese

INSTRUCTION SHEET(PEW12 HAND TOOL FOR EI TAB 170430)

Japanese