




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
----------------	--------



Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Retention	With
Mating Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Red
Housing Material	Nylon 6/6

Dimensions

Connector Height	9.65 mm
Product Length	13.02 mm

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 178496-1 UNIV. POWER HDR H ASSY 3P NAT.	 TE Part # 175156-2 U/P REC CONT L/P	 TE Part # 176976-1 AMP UNIVERSAL POWER PLG 3C PCB	 TE Part # 175155-1 UNIV POWER REC CONT L/P
 TE Part # 176283-1 AMP UNIVERSA POWR CAP 3P	 TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.	 TE Part # 175152-1 UNIVERSAL POWER REC	 TE Part # 175151-2 AMP UNIVE. POWER CONN REC CONT



TE Part # 175155-2
U/P REC CONT L/P

TE Part # 175156-1
UNIV POWER REC CONT L/P

TE Part # 6-176976-1
AMP UNIVERSAL POWER PLG 2C PCB

TE Part # 3-176976-1
AMP UNIVERSAL POWER PLG 2C PCB

TE Part # 176976-4
UNIV POWER HDR ASSY 3P YELLOW

TE Part # 3-176976-6
UNIV POWER HDR ASSY 3P BLUE

TE Part # 176283-2
AMP UNIVERSAL POWER CAP 3P

TE Part # 176293-1
UNIV POWER CAP HSG 3P P/MOUNT

TE Part # 3-176976-2
UNIV POWER HDR ASSY 3P RED

TE Part # 3-176976-4
UNIV.POWER HDR ASSY 3P

TE Part # 175152-2
AMP UNIV. POWER CONN REC CONT

TE Part # 175151-5
AMP UNIVERSAL POWER CONN.REC C

Also in the Series | AMP Universal Power

Connector Contacts(22)

Insertion & Extraction Tools(1)

Rectangular Power Connectors(163)


Customers Also Bought

TE Part #770018-1
03P UMNLII IN-LNE PLUG HSG KIT

TE Part #176271-1
AMP UNIVERSAL POWER PLUG 2P

TE Part #175152-1
UNIVERSAL POWER REC

TE Part #1123721-2
ECONOMY POWER CONN REC CONT



Documents

Product Drawings

AMP UNIVERSAL POWER PLUG 3P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_176272-2_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_176272-2_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_176272-2_G.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_176272-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_176272-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_176272-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Crimping of Universal Power Contact

English

Product Specification

Japanese

AMP Universal Power Connector



Japanese

Instruction Sheets
AMP UNIVERSAL POWER CONNECTOR SERIES

English
Instruction Sheet (non U.S.)

English

Agency Approvals
UL Report

English