



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Passive Component Dimensions: **54 x 8.5 mm**

Number of Terminations: **2**

Packaging Method: **Box**

Passive Component Tolerance: **5 %**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	750 V
Passive Component Tolerance	5 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	4.7K Ω
Power Rating	9 W

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

--	--



Number of Terminations	2
Termination Area Base Material	Copper

Dimensions

Passive Component Dimensions	54 x 8.5 mm
------------------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}\text{C}$
Temperature Coefficient	± 350 ppm/ $^{\circ}\text{C}$

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX9J4K7

4.7K Ω , Metal Oxide Film, General Purpose Resistor, 5 %, 54 x 8.5 mm, 2 Termination, Box, 9 W, $\pm$ 350 ppm/ $^{\circ}$ C, Copper Termination, Neohm ROX



TE Part # 2-1625892-1
3W SM M/OX 5% 1K0

TE Part # 4-1625886-1
1W SM M/OX 5% 820K

TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R

TE Part # 1625881-2
1W STD M/OX 2% 220R

TE Part # 1625893-5
5W SM M/OX 5% 47K

Also in the Series | Neohm ROX

Through-Hole Resistors(798)

Customers Also Bought

TE Part #4-640440-5
15P MTA100 CONN ASSY 22AWG RED

TE Part #640917-2
RECEPT,PIDG FASTON 22-18 187

TE Part #63067-1
250 FASTON TAB TPBR

TE Part #2-34144-1
PG R 22-16 COMM 22-18 MIL 6

TE Part #61907-1
187 FASTON TAB TPBR

TE Part #644753-3
03P MTA156 HDR ASSY RN STR F/L

TE Part #5206478-2
CLAMSHELL KIT W/RETAINER,SZ 2

TE Part #640919-2
RECEPT,PIDG FASTON 16-14 187



Documents

Product Drawings

9W STD M/OX 5% 4K7

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2176416-8_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2176416-8_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2176416-8_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English