



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.8 mm [.031 in]**

Terminal Transmits: **25 – 40 A (Power)**

Wire Size: **17 – 13 AWG**

[All TIMER, RECEPTACLE AND TAB \(330\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	30 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire



Dimensions

Compatible Insulation Diameter Range	2.7 – 4.1 mm[.106 – .161 in]
Wire Size	1 – 2.5 mm ²
Wire Size Search	13 AWG, 14 AWG, 15 AWG, 16 AWG, 17 AWG
Tab Length	18.8 mm[.74 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	3000
Packaging Method	Reel

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-T4827-CH8172 Timer Connector Housing	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 1-1579007-6 EXTRACTION TOOL	 TE Part # 1-967625-3 JUN-POW-TIM GEH 21P
 TE Part # 2151356-1 OCEAN_2.0_APPLICATOR-S-110F160F	 TE Part # 2151356-2 OCEAN_2.0_APPLICATOR-S-110F160F	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151356-1 OCEAN_2.0_APPLICATOR-S-110F160F
 TE Part # 7-2151356-2 OCEAN_2.0_APPLICATOR-S-110F160F	 TE Part # 7-2151356-7 OCEAN_2.0_SPARE_PART_KIT-110F160F	 TE Part # 2-967623-3 JUN-POW TIM GEH 15P	 TE Part # 3-967624-6 JUN-POW-TIM GEH 18P
 TE Part # 1-282539-3 5 POS. JPT HSG			

Also in the Series | Junior Power Timer



Automotive Connector Caps & Covers (4)



Automotive Housings(231)



Automotive Terminals(82)



Busbars & Terminals(1)



Connector Seals & Cavity Plugs(9)



Insertion & Extraction Tools(8)



Module Components(3)




Other Automotive Connector Accessories(1)


Customers Also Bought



TE Part #927775-3
JPT REC 2.8 Contact SRC Sn



TE Part #606713-1
600 MCM QUICK DISCONNECT



TE Part #183596-1
PRE-INSULATED SEALED SPLICE 22-18



TE Part #965972-1
PL 250 REC TERMINAL-FLAG 17-13 PTPB



TE Part #1-1803293-3
ANVIL, COMBINATION DEUTCH STYLE




TE Part #2295763-1
MICRORELAY HOLDER ASSEMBLY



TE Part #2424195-2
HSD CABLE ASSEMBLY



TE Part #2424195-5
HSD CABLE ASSEMBLY



TE Part #2424195-9
HSD CABLE ASSEMBLY



TE Part #142317-1
MIC TAB WITH LANCE VRAC

Documents



Product Drawings

JPT REC 2.8 Contact SRC Sn

English

CAD Files

Customer View Model

ENG_CVM_927773-3_A9.3d_igs.zip

English

Customer View Model

ENG_CVM_927773-3_A9.3d_stp.zip

English

Customer View Model

ENG_CVM_927773-3_A9.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Timer Interconnection System

English

Product Specifications

Application Specification

German

Application Specification

English