



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 7 Watt, 0.10-500 Ohm



Resistor Type: **Power Resistor**

Number of Terminations: **2**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

Element Type: **Wire Wound**

[All SMD Power Resistor: 7 Watt, 0.10-500 Ohm \(229\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	150 Ω
Power Rating	5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	6.8 mm[.268 in]
Product Length	13.5 mm[.531 in]



Product Width	7.3 mm[.287 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMW5150RJT

150 Ω , Wire Wound, Power Resistor, 5 %, 2 Termination, Taped & Reeled, 5 W, ± 200 ppm/ $^{\circ}\text{C}$, Solder, Height .268 in [6.8 mm], CGS SM





TE Part # CAT-C339-SM1
SMD Power Resistor: 7 Watt, 200-2M Ohm




TE Part # 1879233-9
SMW5 R22 5%


Also in the Series | CGS SM




Battery Holders(1)



Expanded Beam Fiber Optics(9)



LC Connectors(2)




RJ14 Connectors(1)




RJ22 Connectors(1)



RJ25 Connectors(1)



RJ45 Connectors(3)



SC Connectors(2)



Surface Mount Resistors(554)

Customers Also Bought



TE Part #1318384-4
025 40POS CAP ASSY H TIN



TE Part #6-440054-2
HPI 2.0MM,HDR,2POSVERTICAL,BLK



TE Part #2174803-2
PUSH-PUSH MICRO SIM CONNECTOR



TE Part #1825232-1
SLIDE SWITCH,SPDT,Right Angle

SMW5150RJT

150 Ω, Wire Wound, Power Resistor, 5 %, 2 Termination, Taped & Reeled, 5 W, ±200 ppm/°C, Solder, Height .268 in [6.8 mm], CGS SM



TE Part #2176177-5
CRGH0603 1% 330R 0.2W

TE Part #3-1879377-4
CRGH0805 5% 22R 0.33W

TE Part #2-2176346-1
CRGCQ 1210 2K2 5%

TE Part #2148999-2
RF CA,UMCC GEN1,1.13MM,L100MM STRIPPED

TE Part #BAT-HLD-001
Battery Holder 2032 2025 SMT Bulk Pack

Documents

Product Drawings

SMW5 150R 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1879233-7_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1879233-7_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1879233-7_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English