

# Data sheet

## 13908.4 PKB 1350/10/3,50 DG



Female socket block, Wire protection, No. of poles: 10, Width: 35 mm, Colour: Dark grey

### Business data

|                                            |                     |
|--------------------------------------------|---------------------|
| Article number                             | 13908.4             |
| Article name                               | PKB 1350/10/3,50 DG |
| GTIN (EAN)                                 | 4044211136154       |
| Connector version                          | Free connector      |
| Packaging unit                             | 50                  |
| Quantity unit                              | PC                  |
| Packaging type                             | Carton              |
| Type of banding                            | Without             |
| Weight per piece (not including packaging) | 5.63 g              |
| Weight per piece (including packaging)     | 6.33 g              |
| Unit of weight                             | G                   |
| Customs number                             | 85366930            |
| Country of origin                          | TN                  |
| Colour                                     | Dark grey           |

### Technical data

#### Dimensions

|             |         |
|-------------|---------|
| Length      | 9.5 mm  |
| Width       | 35 mm   |
| Width left  | 1.75 mm |
| Width right | 1.75 mm |
| Height      | 10 mm   |
| Pitch       | 3.5 mm  |

#### Ratings

|                       |                     |
|-----------------------|---------------------|
| Rated voltage         | 125 V               |
| Rated current         | 8 A                 |
| Rated cross-section   | 1.5 mm <sup>2</sup> |
| Rated impulse voltage | 2.5 kV              |
| Overvoltage category  | III                 |
| Contamination degree  | 3                   |

#### Connection data

|                                                          |                             |
|----------------------------------------------------------|-----------------------------|
| Connection principle                                     | Wire protection             |
| Angle of wire connection/contact                         | 270° (vertically downwards) |
| Number of plug-in rows                                   | 1                           |
| No. of poles                                             | 10                          |
| Contact version                                          | Female connector            |
| Wire cross-section single-core (rigid) / stranded, min.  | 0.08 mm <sup>2</sup>        |
| Wire cross-section single core (rigid)/stranded, max.    | 1.5 mm <sup>2</sup>         |
| Wire cross-section stranded, min.                        | 0.08 mm <sup>2</sup>        |
| Wire cross-section stranded, max.                        | 1.5 mm <sup>2</sup>         |
| Wire cross-section stranded with wire-end ferrules, min. | 0.14 mm <sup>2</sup>        |
| Wire cross-section stranded with wire-end ferrules, max. | 0.5 mm <sup>2</sup>         |
| Wire cross-section AWG, min.                             | 28                          |
| Wire cross-section AWG, max.                             | 16                          |
| Stripping length                                         | 5 mm                        |
| Screw threading                                          | M 2                         |
| Torque                                                   | 0.25 Nm                     |

### Technical data

#### Materials

|                           |                 |
|---------------------------|-----------------|
| Insulation housing        | Polyamide 6.6   |
| Flammability class UL 94  | V-0             |
| Working temperature, min. | -30 °C          |
| Working temperature, max. | 105 °C          |
| Clamping element          | Brass           |
| Contact spring            | Bronze          |
| Screws                    | Bronze          |
| Wire protection           | Stainless steel |

#### Further technical data

|                                                |                             |
|------------------------------------------------|-----------------------------|
| Storage temperature, min.                      | -40 °C                      |
| Storage temperature, max.                      | 105 °C                      |
| Insulation resistance                          | 1*10 <sup>13</sup> Ohm x cm |
| Creepage-current resistance                    | CTI 600                     |
| Glow wire flammability index GWFI              | GWFI 850                    |
| GWFI after-glow time                           | 30 Sek.                     |
| Glow wire ignition temperature GWIT            | GWIT 775 °C                 |
| GWIT exposure time                             | 5 Sek.                      |
| Connection cycles, in compliance with standard | 5                           |
| Plug-in cycles acc. to standard                | 100                         |

#### Environmental Product Compliance

|                                |            |
|--------------------------------|------------|
| REACH Conform                  | No         |
| REACH Reference date           | 2023-06-14 |
| REACH Candidate Substance Note | No         |
| REACH CAS 1 Substance          | LEAD       |
| REACH CAS 1 Percent minimal    | 0.1 %      |
| REACH CAS 1 Percent maximum    | 4 %        |
| REACH CAS 1 Number             | 7439-92-1  |
| RoHS Conform                   | yes        |
| RoHS Exception rule            | 6c         |

### Approvals

#### cUL Recognized

|                                                      |                 |
|------------------------------------------------------|-----------------|
| cUL approval                                         | CSA 22.2 No.158 |
| cUL Usegroup B: rated voltage                        | 150 V           |
| cUL Usegroup B: rated current                        | 9 A             |
| cUL wire cross-section single-core (rigid) AWG, min. | 28              |
| cUL wire cross-section single-core (rigid) AWG, max. | 16              |
| cUL wire cross-section stranded AWG, min.            | 28              |
| cUL wire cross-section stranded AWG, max.            | 16              |
| cUL torque                                           | 0.25 Nm         |
| cUL wire material                                    | Cu              |
| cUL Recognized                                       | 1               |

#### UL Recognized




|                                                     |            |
|-----------------------------------------------------|------------|
| UL approval                                         | UL 1059    |
| UL Usegroup B: rated voltage                        | 150 V      |
| UL Usegroup B: rated current                        | 9 A        |
| UL wire cross-section single-core (rigid) AWG, min. | 28         |
| UL wire cross-section single-core (rigid) AWG, max. | 16         |
| UL wire cross-section stranded AWG, min.            | 28         |
| UL wire cross-section stranded AWG, max.            | 16         |
| UL torque                                           | 2.21 Lb In |
| UL wire material                                    | Cu         |
| UL factory wiring                                   | 1          |
| UL field wiring                                     | 1          |
| UL Recognized                                       | 1          |

### Approvals

#### VDE approval

|                                                     |                     |
|-----------------------------------------------------|---------------------|
| VDE approval                                        | DIN EN 61984        |
| VDE approval granted                                | yes                 |
| VDE rated voltage                                   | 125 V               |
| VDE rated current                                   | 8 A                 |
| VDE rated current wire cross-section rigid, min.    | 4 A                 |
| VDE rated current wire cross-section rigid, max.    | 8 A                 |
| VDE rated current wire cross-section stranded, min. | 4 A                 |
| VDE rated current wire cross-section stranded, max. | 8 A                 |
| VDE rated impulse voltage                           | 2.5 kV              |
| VDE wire cross-section rigid, min.                  | 0.5 mm <sup>2</sup> |
| VDE wire cross-section rigid, max.                  | 1.5 mm <sup>2</sup> |
| VDE wire cross-section stranded, min.               | 0.5 mm <sup>2</sup> |
| VDE wire cross-section stranded, max.               | 1.5 mm <sup>2</sup> |
| VDE screw threading                                 | M 2                 |
| VDE torque                                          | 0.25 Nm             |
| VDE overvoltage category                            | III                 |
| VDE contamination degree                            | 3                   |

Media



---

**Accessories**

---