


# S-FM401 thru S-FM407

## Surface Mount Glass Passivated Junction Rectifiers Reverse Voltage 50 to 1000V Forward Current 1.0A

### FEATURES

- \* Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- \* High temperature metallurgically bonded construction
- \* Cavity-free glass passivated junction
- \* Capable of meeting environmental standards of MIL-S-19500
- \* 1.0 A operation at TL=100°C with no thermal runaway
- \* Typical IR less than 1.0 $\mu$ A
- \* High temperature soldering guaranteed: 260°C/10 seconds
- \* S- Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.



### Mechanical Data

**Case:** JEDEC DO-214AC, molded plastic over glass body

**Terminals:** Plated axial leads, solderable per MIL-STD-750, Method 2026

**Polarity:** Color band denotes cathode end

**Mounting Position:** Any

**Weight:** 0.0023 oz., 0.065 g

**Handling precaution:** None

### Electrical Characteristic

#### 1. Maximum & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

| Parameter Symbol   | symbol          | S-FM 401    | S-FM 402 | S-FM 403 | S-FM 404 | S-FM 405 | S-FM 406 | S-FM 407 | Unit |
|--|-----------------|-------------|----------|----------|----------|----------|----------|----------|------|
| Device marking code  |                 | M01         | M02      | M03      | M04      | M05      | M06      | M07      |      |
| Maximum repetitive peak reverse voltage  | $V_{RRM}$       | 50          | 100      | 200      | 400      | 600      | 800      | 1000     | V    |
| Maximum RMS voltage  | $V_{RMS}$       | 35          | 70       | 140      | 280      | 420      | 560      | 700      | V    |
| Maximum DC blocking voltage  | $V_{DC}$        | 50          | 100      | 200      | 400      | 600      | 800      | 1000     | V    |
| Maximum average forward rectified current TL = 75°C (See fig. 1)                                 | $I_{F(AV)}$     | 1.0         |          |          |          |          |          |          | A    |
| Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) | $I_{FSM}$       | 30          |          |          |          |          |          |          | A    |
| Typical thermal resistance (Note 1)  | $R_{\theta JA}$ | 150         |          |          |          |          |          |          | °C/W |
|  | $R_{\theta JL}$ | 35          |          |          |          |          |          |          | °C/W |
| Operating junction and storage temperature range   | $T_J, T_{STG}$  | -50 to +150 |          |          |          |          |          |          | °C   |

#### Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

| Parameter Symbol  | symbol | S-FM 401  | S-FM 402 | S-FM 403 | S-FM 404 | S-FM 405 | S-FM 406 | S-FM 407 | Unit          |
|---|--------|-----------|----------|----------|----------|----------|----------|----------|---------------|
| Maximum instantaneous forward voltage at 1.0A   | $V_F$  | 1.1       |          |          |          |          |          |          | V             |
| Maximum DC reverse current $T_A = 25^\circ\text{C}$<br>at rated DC blocking voltage $T_A = 125^\circ\text{C}$ | IR     | 5.0<br>50 |          |          |          |          |          |          | $\mu\text{A}$ |
| Typical junction capacitance at 4.0V, 1MHz  | CJ     | 8.0       |          |          |          |          |          |          | PF            |

NOTES:

1. 8.0mm<sup>2</sup> (.013mm thick) land areas

We declare that the material of product compliance with ROHS requirements

# S-FM401 thru S-FM407

## 2. Ratings and Characteristic Curves (TA = 25°C unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig 3. - Typical Instantaneous Forward Characteristics




Fig 4. - Typical Reverse Characteristics




Fig 5. - typical transient thermal impedance






Fig 6. - Typical Junction Capacitance



## S-FM401 thru S-FM407


### 2.Ratings and Characteristic Curves ( TA = 25°C unless otherwise noted )

Fig. 7 - Forward Current Derating Curve



## S-FM401 thru S-FM407

### 3. dimension:



## S-FM401 thru S-FM407

### 4. Update Record

| 版次 | 更新记录           | 更新作者 | 更新日期       |
|----|----------------|------|------------|
| 1  | 第一版            | 周杰   | 2013.11.01 |
| 2  | 增加TL热阻及电流降额曲线。 | 谭志伟  | 2018.10.24 |