



MMBD4148DW

Silicon Epitaxial Planar Switching Diode

Features

- Fast switching speed
- Ultra-small surface mount package
- For general purpose switching applications
- High conductance




1.Anode 2. Anode 3.Anode
4. Cathode 5. Cathode 6.Cathode
SOT-363 Plastic package
Marking Code : KA

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Peak Reverse Voltage	V_{RM}	100	V
Reverse Voltage	V_R	75	V
Average Rectified Forward Current	$I_{F(AV)}$	200	mA
Forward Continuous Current	I_{FM}	300	mA
Non-Repetitive Peak Forward Current $t = 1 \mu\text{s}$ $t = 1 \text{ s}$	I_{FSM}	2 1	A
Power Dissipation	P_{tot}	200	mW
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	625	$^\circ\text{C/W}$
Operating and Storage Temperature Range	T_j, T_{stg}	- 65 to + 150	$^\circ\text{C}$

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
Reverse Breakdown Voltage at $I_R = 100 \mu\text{A}$	$V_{(BR)R}$	75	-	V
Forward Voltage at $I_F = 1 \text{ mA}$ at $I_F = 10 \text{ mA}$ at $I_F = 50 \text{ mA}$ at $I_F = 150 \text{ mA}$	V_F	- - - -	0.715 0.855 1 1.25	V
Peak Reverse Current at $V_R = 20 \text{ V}$ at $V_R = 75 \text{ V}$ at $V_R = 25 \text{ V}, T_j = 150^\circ\text{C}$ at $V_R = 75 \text{ V}, T_j = 150^\circ\text{C}$	I_R	- - - -	25 1 30 50	nA μA μA μA
Total Capacitance at $V_R = 0 \text{ V}, f = 1 \text{ MHz}$	C_T	-	2	pF
Reverse Recovery Time at $I_F = 10 \text{ mA}, I_{rr} = 0.1 \times I_R, R_L = 100 \Omega, V_R = 6 \text{ V}$	t_{rr}	-	4	ns



Electrical Characteristics Curves

Fig 1. Power Dissipation vs. Temperature




Fig 2. Total Capacitance vs. Reverse Voltage




Fig 3. Reverse Current vs. Reverse Voltage







Fig 4. Forward Characteristics




Package Outline Dimensions (Units: mm)

SOT-363



Recommended Soldering Footprint



Packing information

Package	Tape Width (mm)	Pitch		Reel Size		Per Reel Packing Quantity
		mm	inch	mm	inch	
SOT-363	8	4 ± 0.1	0.157 ± 0.004	178	7	3,000

Marking information

" KA " = Part No.
" YM " = Date Code Marking
" Y " = Year
" M " = Month
Font type: Arial

