


# LBTP180Z4TZHG

## S-LBTP180Z4TZHG

PNP medium power transistors


### 1. FEATURES

- High current
- Low voltage
- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.



### 2. DEVICE MARKING AND ORDERING INFORMATION

Device	Marking	Shipping
LBTP180Z4TZHG	PB	1000/Tape&Reel



### 3. MAXIMUM RATINGS(Ta = 25°C)

Parameter	Symbol	Limits	Unit
Collector–Emitter Voltage	V <sub>CEO</sub>	-80	V
Collector–Base Voltage	V <sub>CBO</sub>	-100	V
Emitter–Base Voltage	V <sub>EBO</sub>	-5	V
Collector Current — Continuous	I <sub>C</sub>	-1	A
Peak Collector Current	I <sub>CM</sub>	-1.5	A
Base Current	I <sub>B</sub>	-0.1	A
Peak Base Current	I <sub>BM</sub>	-0.2	A
Junction and Storage temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 ~ +150	°C

### 4. THERMAL CHARACTERISTICS





Parameter	Symbol	Limits	Unit
Total Device Dissipation, FR-4 Board (Note 1) @ TA = 25°C	PD	833	mW
Thermal Resistance, Junction–to–Ambient(Note 1)	R <sub>θJA</sub>	150	°C/W

1. FR-4 = 30.0mm×25.0mm×1.6mm.





**5. ELECTRICAL CHARACTERISTICS (Ta= 25°C)**

Characteristic	Symbol	Min.	Typ.	Max.	Unit
Collector–Emitter Breakdown Voltage (IC = -1.0 mA, IB = 0)	VBR(CEO)	-80	-	-	V
Collector–Base Breakdown Voltage (IC = -100 μA, IE = 0)	VBR(CBO)	-100	-	-	V
Emitter–Base Breakdown Voltage (IE = -100 μA, IC = 0)	VBR(EBO)	-5	-	-	V
Collector Cutoff Current (IE = 0, VCB = -30 V) (IE = 0, VCB = -30 V, Tj = 125 °C)	ICBO	-	-	-100 -10	nA μA
Emitter CutOff Current (IC = 0, VEB = -5 V)	IEBO	-	-	-100	nA
Collector-Emitter cutoff Current (VCE= -80V,IB=0)	ICEO	-	-	-10	μA
DC Current Gain (IC = -5mA, VCE = -2V) (IC = -150mA, VCE = -2V) (IC = -500mA, VCE = -2V)	HFE	40 100 40	- - -	- 250 -	
Collector–Emitter Saturation Voltage (IC = -500 mA, IB = -50 mA)	VCE(sat)	-	-	-0.5	V
Base–Emitter Saturation Voltage (IC = -500 mA, IB = -50 mA)	VBE(sat)	-	-	-1	V
Base–Emitter Voltage (IC = -500 mA, VCE = -2 V)	VBE	-	-	-1	V
Transitional Frequency (IC = -10 mA, VCE = -5 V, f = 100 MHz)	fT	-	115	-	MHz
Output Capacitance (VCB=-5V,IE=0,f=1.0MHz)	Cobo	-	13.5	-	pF
Input Capacitance (VEB=-0.5V,IC=0,f=1.0MHz)	Cibo	-	85	-	pF

### 6.ELECTRICAL CHARACTERISTICS CURVES




**6.ELECTRICAL CHARACTERISTICS CURVES(Con.)**



## 7. OUTLINE AND DIMENSIONS

### SOT223




SOT223			
DIM	MIN	NOR	MAX
A	1.50	1.60	1.70
A1	0.00	0.05	0.10
A2	0.80	0.90	1.00
b1	2.90	3.02	3.10
b2	0.60	0.72	0.80
c	0.20	0.27	0.35
D	6.30	6.50	6.70
E	3.30	3.50	3.70
e	4.60BSC		
e1	2.30BSC		
HE	6.80	7.00	7.20
L	0.80	1.00	1.20
L1	1.75(REF)		
$\theta$	0°~8°		
$\theta$ 1	8°	10°	12°
All Dimensions in mm			

#### GENERAL NOTES

1. Top package surface finish  $Ra0.4 \pm 0.2 \mu m$
2. Bottom package surface finish  $Ra0.7 \pm 0.2 \mu m$
3. Side package surface finish  $Ra0.4 \pm 0.2 \mu m$
4. Protrusion or Gate Burrs shall not exceed 0.10mm per side.

## 8. SOLDERING FOOTPRINT



SOT223	
DIM	(mm)
X1	3.80
Y1	2.00
X2	1.20
Y2	2.00
C1	2.30
C2	6.30

## **DISCLAIMER**

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.