

RP73PF1E6R98BTDF

✓ ACTIVE

Holsworthy | Holsworthy RP73

TE Internal #: 4-2176308-7

6.98 Ω , Thin Film, Precision Resistor, .1 %, 2 Termination, 0402,
Taped & Reeled, .1 W, ± 25 ppm/ $^{\circ}\text{C}$, Solder, Height .012 in [.3 mm],
Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**
Number of Terminations: **2**
Package Size Code: **0402**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0402
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Passive Component Tolerance	.1 %
Resistance Class	Up to 1k Ω
Resistance Value	6.98 Ω
Power Rating	.1 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RP73PF1E6R98BTDF

6.98 Ω , Thin Film, Precision Resistor, .1 %, 2 Termination, 0402, Taped & Reeled, .1 W, ± 25 ppm/ $^{\circ}\text{C}$, Solder, Height .012 in [.3 mm], Holsworthy RP73



TE Part # 7-2176308-8
RP 1E 0.1W 6R98 0.1% 25PPM 5K RL

Also in the Series | Holsworthy RP73

Surface Mount Resistors(4556)

Customers Also Bought

TE Part #6609929-4
PE0SXDHXA=C2218

TE Part #DPP201Z000
PMOD_TSYS01

TE Part #1-2176307-0
RP 1E 0.1W 15K4 0.1% 25PPM 5K RL

TE Part #2-2176306-1
RP 1E 0.1W 1K87 0.1% 25PPM 5K RL

TE Part #6-2176306-9
RP 1E 0.1W 5K9 0.1% 25PPM 5K RL

TE Part #9-2176451-0
CPF 0201 422R 0.1% 25ppm 1K RL

TE Part #2176452-4
CPF 0201 576R 0.1% 25ppm 1K RL

TE Part #4-2176308-8
RP 1E 0.1W 7R15 0.1% 25PPM 1K RL

TE Part #1-2176373-5
RQ 0805 14R 0.1% 10PPM 1K RL

TE Part #7-1437142-2
FSN-22A-8=NOMEX FS STD



Documents

Product Drawings

RP 1E 0.1W 6R98 0.1% 25PPM 1K RL

English

Datasheets & Catalog Pages

RP73-0915

English