




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Gang Wire Seal**
Primary Product Material: **Silicone Rubber**
Primary Product Color: **Blue**
Compatible Insulation Diameter Range: **1.27 – 2.11 mm [.05 – .083 in]**
Operating Temperature (Max): **90 °C [194 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Gang Wire Seal
----------------------------	----------------

Body Features

Primary Product Material	Silicone Rubber
Primary Product Color	Blue

Dimensions

Wire Size	.12 – .8 mm ²
Compatible Insulation Diameter Range	1.27 – 2.11 mm[.05 – .083 in]

Usage Conditions

Operating Temperature (Max)	90 °C[194 °F]
Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]

Packaging Features

Packaging Quantity	1200
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-1586362-6
16P MINI UMNL SEAL, DIE CUT



TE Part # 794758-1
MINI UMNL WIRE SEAL, 18-26AWG



TE Part # 794824-1
16P MINI UMNL PLUG HSG



TE Part # 794370-1
08P MINI UMNL STR RELIEF HNGD

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)	Connector Contacts(92)	Connector Hardware(4)	Connector Seals & Cavity Plugs(17)
Connector Strain Relief(2)	Insertion & Extraction Tools(1)	PCB Headers & Receptacles(1)	Rectangular Power Connectors(197)

Customers Also Bought

TE Part #206061-2 CPC RECPT ASSEMBLY SIZE 11-4	TE Part #788154-2 SLD CPC RCPT ASSY,11-4,REV SEX	TE Part #745254-7 20 DF PIN CONT L.P.	TE Part #794895-1 6 CIR MINI UMNL RND WIRE HOLES
TE Part #794772-6 06P MINI UMNL SEAL,DIE CUT	TE Part #794772-8 08P MINI UMNL SEAL,DIE CUT	TE Part #1586359-4 04P MINIMUMNL GANG WIRE SEAL DR	TE Part #794772-4 04P MINI UMNL SEAL,DIE CUT
TE Part #1-967239-1 JPT GEH KPL GEH 2P	TE Part #455830-1 INSERTION TOOL		

Documents



Product Drawings

16P MINIUMNL GANG WIRE SEAL DR

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1586359-6_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1586359-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1586359-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English