Data sheet | Item number: 2092-1410

THT male header; 1.4 mm Ø solder pin; straight; Pin spacing 5 mm; 10-pole; light gray



www.wago.com/2092-1410



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



Dimensions in mm

L = (pole no. x pin spacing) + 2.2 mm

A = 3.6 mm THT solder pin

A = 2.4 mm THR solder pin

Item description

- Assembly of female connectors without loss of poles, allowing different functions to be divided within one male header
- Coding pins inserted into the header interface prevent mismating, allowing subsequent coding in panel feedthrough applications
- The female connector is fully shrouded by the male header's housing, providing vibration resistance up to 20 g

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



Data Notes

Safety information 1	The picoMAX[®] Pluggable Connection System includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected /disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/.	Direct marking

Electrical data

Approvals per	UL 1059
Rated voltage UL (Use Group B)	300 V
Rated current UL (Use Group B)	15A
Rated voltage UL (Use Group D)	300 V
Rated current UL (Use Group D)	10 A
Ratings per	IEC/EN 60664-1
Nominal voltage (III/3)	250 V
Rated surge voltage (III/3)	4 kV
Rated voltage (III/2)	320 V
Rated surge voltage (III/2)	4 kV
Nominal voltage (II/2)	630 V
Rated surge voltage (II/2)	4 kV
Rated current	16 A
Legend (ratings)	(III / 2) ≙ Overvoltage category III / Pollution degree 2

Connection data

Total number of potentials	10
Number of connection types	1
Number of levels	1
Pole No.	10

Physical data

Pin spacing	5 mm / 0.197 inch
Width	52.2 mm / 2.055 inch
Height	23.1 mm / 0.909 inch

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG	Do you have any questions about our products?
Hansastr. 27	We are always happy to take your call at +49 (571) 887-44222.
32423 Minden	
Phone: +49571 887-0 Fax: +49571 887-169	
Email: info.de@wago.com Web: www.wago.com	

Data sheet | Item number: 2092-1410

www.wago.com/2092-1410



Height from the surface	19.5 mm / 0.768 inch
Depth	14.4 mm / 0.567 inch
Solder pin length	3.6 mm
Solder pin diameter	1.4 mm
Drilled hole diameter with tolerance	1.6 ^(+0.1) mm

Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	No
Mating direction to the PCB	90°
Locking of plug-in connection	Locking latch

PCB contact

THT

Material data

Material groupIInsulation materialPolyphthalamide (PPA GF)Flammability class per UL94V0Contact materialElectrolytic copper (E _{Cu})Contact platingtin-platedFire load0.107 MJWeight5.7 g	Color	light gray
Flammability class per UL94 V0 Contact material Electrolytic copper (E _{Cu}) Contact plating tin-plated Fire load 0.107 MJ	Material group	1
Contact material Electrolytic copper (E _{Cu}) Contact plating tin-plated Fire load 0.107 MJ	Insulation material	Polyphthalamide (PPA GF)
Contact plating tin-plated Fire load 0.107 MJ	Flammability class per UL94	Vo
Fire load 0.107 MJ	Contact material	Electrolytic copper (E _{Cu})
	Contact plating	tin-plated
Weight 5.7 g	Fire load	0.107 MJ
· · ·	Weight	5.7 g

Environmental requirements

Limit temperature range	-60 +100 °C	
-------------------------	-------------	--

Commercial data

Product Group	26 (picoMAX)
PU (SPU)	100 Stück
Packaging type	box
Country of origin	DE
GTIN	4050821163893

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KGDo you have any questions about our products?Hansastr. 27We are always happy to take your call at +49 (571) 887-44222.32423 MindenPhone: +49571 887-0 | Fax: +49571 887-169Email: info.de@wago.com | Web: www.wago.comEmail: info.de@wago.com | Web: www.wago.com

www.wago.com/2092-1410



Customs tariff number

85366990990

Approvals / Certificates

Country specific Approvals

Approval	Additional Approval Text	Certificate name
CB DEKRA Certification B.V.	IEC 61984	NL-49737 /A1
CSA DEKRA Certification B.V.	C22.2	2362521
CSA DEKRA Certification B.V.	C22.2 No. 158	2362521
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71- 102261 REV.1
Approval	Additional Approval Text	Certificate name
cURus Underwriters Laboratories Inc.	UL 1059	E45172
UL Underwriters Laboratories Inc.	UL 1977	E45171
	CB DEKRA Certification B.V. CSA DEKRA Certification B.V. CSA DEKRA Certification B.V. KEMA/KEUR DEKRA Certification B.V. KEMA/KEUR DEKRA Certification B.V. Gubble DEKRA Certification B.V. LUL	CB DEKRA Certification B.V.IEC 61984CSA DEKRA Certification B.V.C22.2CSA DEKRA Certification B.V.C22.2 No. 158KEMA/KEUR DEKRA Certification B.V.EN 61984KEMA/KEUR DEKRA Certification B.V.UI 1059Underwriters Laboratories Inc.UL 1977

Counterpart

Item no.2092-1130www.w1-conductor female connector; push-button; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm; 10-pole;www.w2,50 mm²; light gray1130	-
Jitem no.2092-1110/000-5000	www.wago.com/2092-
1-conductor female connector: push-button: Push-in CAGE CLAMP®: 2.5 mm ² : Pin spacing 5 mm: 10-pole:	000-5000
Gripping plate; direct marking; 2,50 mm²; light gray	1110/000-5000
Jitem no.2092-1110/000-1000	

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



	1-conductor female connector; push-but Gripping plate; direct marking; 2,50 mm²;	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm; light gray	:10-pole;	www.wago.com/2092 1110/000-1000	
6Å	Item no.2092-1110 1-conductor female connector; push-but Gripping plate; 2,50 mm²; light gray	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm;	:10-pole;	www.wago.com/2092 1110	
	Item no.2092-1110/002-000 1-conductor female connector; push-but Gripping plate sliding connector release; 2	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm; 2,50 mm²; light gray	10-pole;	www.wago.com/2092 1110/002-000	
Contraction of the second	Item no.2092-1130/000-1000 1-conductor female connector; push-but direct marking; 2,50 mm²; light gray	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm;	10-pole;	www.wago.com/2092- 1130/000-1000	
đ	Item no.2092-1110/002-1000 1-conductor female connector; push-but Gripping plate sliding connector release; o	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm; direct marking; 2,50 mm²; light gray	: 10-pole;	www.wago.com/2092 1110/002-1000	
STATE	Item no.2092-1130/000-5000 1-conductor female connector; push-but direct marking; 2,50 mm²; light gray	ton; Push-in CAGE CLAMP®; 2.5 mm²; Pin spacing 5 mm;	10-pole;	www.wago.com/209 bole; 1130/000-5000	
Downloads Document					
Additional In Technical ex		Apr 3, 2019	pdf 2.0 M	Download IB	
CAD/CAE-	Data				
CAD data					
2D/3D Mode	els 2092-1410		URL	Download	
PCB Design					
Symbol and	Footprint 2092-1410		URL	Download	
	your PCB design, consisting of "schematic tegration of the WAGO component into you				
Supported f	ormats:				
Acce	el EDA 14 & 15				
Altiu	m 6 to current version				
Cade	ence Allegro				
Desi	gnSpark				
_ Subject to ch	anges. Please also observe the further prod	uct documentation!			
WAGO Konta Hansastr. 27 32423 Minde	ıkttechnik GmbH & Co. KG	Do you have any questions about our p We are always happy to take your call a		887-44222.	

www.wago.com/2092-1410

- Eagle Libraries
- KiCad
- Mentor Graphics BoardStation
- Mentor Graphics Design Architect
- Mentor Graphics Design Expedition 99 and 2000
- OrCAD 9.X PCB and Capture
- PADS PowerPCB 3, 3.5, 4.X, and 5.X
- PADS PowerPCB and PowerLogic 3.0
- PCAD 2000, 2001, 2002, 2004, and 2006
- Pulsonix 8.5 or newer
- STL
- 3D STEP
- TARGET 3001!
- View Logic ViewDraw
- Quadcept
- Zuken CadStar 3 and 4
- Zuken CR-5000 and CR-8000

PCB Component Libraries (EDA), PCB CAD Library Ultra Librarian

ZUKEN Portal 2092-1410	URL	Download
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 2092-1410	URL	Download
THT male header; 1.4 mm Ø solder pin; straight; Pin spacing 5 mm; 10-pole; light gray		

Installation Notes

Coding

CAE data

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



Data sheet | Item number: 2092-1410 www.wago.com/2092-1410





Coding a male header (via coding key carrier and two keys for male header, see symbol).

Product family

<i>picoMAX</i>[®] 5.0 Show all products from the family

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com