


TECHNICAL CHARACTERISTICS :

Female screw locks: brass, tin

Compensating washer: steel , tin

Nuts : steel , tin

Corrosion resistance : 24 hours .



NOTE:RoHS INFORMATIONS


- The "LF" products meet European union Directives and other country regulations as described in GS-22-008.
- Plating Sn (pure bright) over copper
- Packaging spec: see GS-14-920

Core range	
PART NUMBER	863001060TLF PACKAGING: per 100 pieces

mat'l. code				surface	tolerance	projection	product family	
-				ISO 1302	ISO 406 ISO 1101		D-SUB	
lfr	ecn no	dr	date	tolerances unless otherwise specified			title	
K	ELX-48600	ACJ	26-06-2023	angles	linear	.0±0.1	FEMALE SCREW LOCK	
						.00±0.1	D-SUB ACCESSORIES	
				0°±2°		scale		
				dr	JOUBERT	28-01-1996		
				engr	JOUBERT	28-01-1996		
				chr	ABHILASH	25-01-2011		
				appd	SUDHIR	25-01-2011		
sheet	revision	K						
index	sheet	1						

TECHNICAL CHARACTERISTICS

FEMALE SCREW LOCKS	: BRASS, TIN
COMPENSATING WASHER	: STEEL, TIN
NUTS	: STEEL, TIN
CORROSION RESISTANCE	: 24HOURS



NOTE: RoHS INFORMATIONS

- The "LF" products meet European union Directives and other country regulations as described in GS-22-008.
- Plating Sn (pure bright) over copper
- Packaging spec: see GS-14-920

Core range													
LEAD FREE NUMBER		86552029TLF				PACKAGING: per 1000 pieces							
mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302		✓ ISO 406 ISO 1101				D-SUB			
lfr	ecn no	dr	date	tolerances unless otherwise specified						title			
H	111-0022	AMR	25-01-2011	angles		linear		mm		FEMALE SCREW LOCK			
				0°±2°		.00±0.1				D-SUB ACCESSORIES			
				dr		JOURBERT		28-01-1996		dwg no			
				engr		JOURBERT		28-01-1996		sheet 2 of 2			
				chr		ABHILASH		25-01-2011		C01-8655-0697			
				appd		SUDHIR		25-01-2011		size			
sheet		revision		H						type			
index		sheet		2						Product Customer Drawing			